



PRODUCT-DETAILS

3GBA101510-BSVCN

No Description Available

General Information											
Product ID							3GBA101510-BSVCN				
ABB Type Designation							M2BAK100LA2				
Catalog Description							No Description Available				
Additional Information											
ABB Type Designation							M2BAK100LA2				
Altitude							1000 m				
Ambient Temperature							40 °C				
Bearing							6206-2Z/C3				
Bearing NDE							6206-2Z/C3				
Country of Origin							China (CN)				
Customs Tariff Number							85015100				
Direction of Rotation							Both sides				
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	D	--	50 Hz	220 V	3.00 kW	2915 r/min	10.16 A	0.870	89.00 %	9.83 N·m	91.41
	Y	--	50 Hz	380 V	3.00 kW	2915 r/min	5.88 A	0.870	89.00 %	9.83 N·m	52.85
Frame Size											100
Gross Weight											47 kg
IC Class											IC411
IE Class Data (50 Hz)											IE Class IE4 Full Load (100%) 89.1 % Partial Load (75%) 89.6 % Partial Load (50%) 89.0 %
IE Class Data (60 Hz)											IE Class NA
IM Class											IMB5 IM3001
Insulation Class											ICLF
IP Class											IP55
Made To Order											No
Minimum Order Quantity											1 piece
Number of Poles (High)											2

Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor
Product Net Weight	47 kg
Product Type	CBK4__M2BAK_IE4_CI
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S