




PRODUCT-DETAILS

3GBA093520-BSD

IE3 Premium Efficiency Cast Iron Motors, 1.1 kW, 400 V (3GBA093520-BSD)



General Information	
Product ID	3GBA093520-BSD
ABB Type Designation	M2BAX 90LB 6
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 1.1 kW, 400 V (3GBA093520-BSD)

Ordering	
ABB Type Designation	M2BAX 90LB 6
Invoice Description	M2BAX 90LB 6
Product Name	3-Phase squirrel cage motor
Product Type	EBA3_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany Shanghai, China
Medium Description	1.1kW, 6 Poles, Frame Size 90, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GBA093520-BSD)
Short Description	1.1kW, 6P, Frame Size 90, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.10 kW	946 r/min	2.97 A	0.660	81.00 %	11.01 N·m	5.40
D	--	50 Hz	230 V	1.10 kW	946 r/min	5.17 A	0.660	81.00 %	11.01 N·m	5.40
Y	--	50 Hz	380 V	1.10 kW	939 r/min	2.95 A	0.700	81.00 %	11.09 N·m	5.10
D	--	50 Hz	220 V	1.10 kW	939 r/min	5.09 A	0.700	81.00 %	11.09 N·m	5.10
Y	--	50 Hz	415 V	1.10 kW	950 r/min	3.00 A	0.630	81.00 %	10.95 N·m	5.60
Connection Configuration										Y
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										1.1 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 81.0 % Partial Load (75%) 79.5 % Partial Load (50%) 75.8 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										6
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Cast Iron
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	386 mm
Product Net Height	217 mm
Product Net Width	170 mm
Product Net Weight	30 kg
Gross Weight	33 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors	

