



PRODUCT-DETAILS

# 3GBA093520-BSXPMAA

## No Description Available

General Information	
Product ID	3GBA093520-BSXPMAA
ABB Type Designation	M2BAXPM 90LB 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BAXPM 90LB 6
Altitude	1000 m
Ambient Temperature	40 °C
Country of Origin	China (CN)
Customs Tariff Number	85015100

Electrical Data					
Conn	Temp Class	Freq	Voltage	Power	Speed
Y	--	150 Hz	380 V	7.50 kW	3000 r/min

Frame Material	Cast Iron
Frame Size	90
Gross Weight	10 kg
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	10 kg
Product Type	CBA2__M2BAX_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online

Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S