



PRODUCT-DETAILS

3GBA102510-ASVCN

No Description Available

General Information

Product ID	3GBA102510-ASVCN
ABB Type Designation	M2BAK100LA4
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M2BAK100LA4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6206-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	2.20 kW	1450 r/min	8.06 A	0.790	89.20 %	14.49 N·m	68.54
Y	--	50 Hz	380 V	2.20 kW	1450 r/min	4.67 A	0.790	89.20 %	14.49 N·m	39.62

Frame Size	100
Gross Weight	46 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE4 Full Load (100%) 89.5 % Partial Load (75%) 89.8 % Partial Load (50%) 89.2 %
IE Class Data (60 Hz)	IE Class NA
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor
Product Net Weight	46 kg
Product Type	CBK4 M2BAK IE4 CI
Quote Only	No

Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class	--
Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S