



PRODUCT-DETAILS

3GBA102510-BSCCN
(3GBA102510-BSCCN)



General Information

Product ID	3GBA102510-BSCCN
ABB Type Designation	M2BAX 100LA 4
Catalog Description	(3GBA102510-BSCCN)

Ordering

ABB Type Designation	M2BAX 100LA 4
Invoice Description	M2BAX 100LA 4
Product Name	3-Phase squirrel cage motor
Product Type	CBA2_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Shanghai, China Guangzhou, China China

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	2.20 kW	1446 r/min	4.96 A	0.770	84.30 %	14.54 N·m	7.40
D	--	50 Hz	230 V	2.20 kW	1446 r/min	8.59 A	0.770	84.30 %	14.54 N·m	7.40
Y	--	50 Hz	380 V	2.20 kW	1439 r/min	4.94 A	0.810	84.30 %	14.50 N·m	7.00
D	--	50 Hz	220 V	2.20 kW	1439 r/min	8.56 A	0.810	84.30 %	14.50 N·m	7.00
Y	--	60 Hz	440 V	2.20 kW	1747 r/min	4.27 A	0.790	83.00 %	12.02 N·m	8.40
Y	--	60 Hz	460 V	2.20 kW	1752 r/min	4.37 A	0.750	83.00 %	11.99 N·m	8.70

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 84.3 % Partial Load (75%) 83.6 % Partial Load (50%) 81.4 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 83.0 % Partial Load (75%) 81.2 % Partial Load (50%) 77.6 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Cast Iron
Frame Size	100
Bearing	6206-2Z/C3
Bearing NDE	6206-2Z/C3
Lubrication	For life
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	31 kg
Gross Weight	36 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Cast Iron Motors

