



PRODUCT-DETAILS

3GBA101510-ASCCNKA  
M2BAX 100LA2

| General Information        |                             |            |       |         |         |
|----------------------------|-----------------------------|------------|-------|---------|---------|
| Product ID                 | 3GBA101510-ASCCNKA          |            |       |         |         |
| ABB Type Designation       | M2BAX 100LA 2               |            |       |         |         |
| Catalog Description        | M2BAX 100LA2                |            |       |         |         |
|                            |                             |            |       |         |         |
| Additional Information     |                             |            |       |         |         |
| ABB Type Designation       | M2BAX 100LA 2               |            |       |         |         |
| Altitude                   | 1000 m                      |            |       |         |         |
| Ambient Temperature        | 40 °C                       |            |       |         |         |
| Country of Origin          | China (CN)                  |            |       |         |         |
| Customs Tariff Number      | 85015100                    |            |       |         |         |
| Direction of Rotation      | Both sides                  |            |       |         |         |
| Electrical Data            |                             |            |       |         |         |
|                            | Conn                        | Temp Class | Freq  | Voltage | Power   |
|                            | Y                           | --         | 50 Hz | 380 V   | 3.00 kW |
|                            |                             |            |       |         |         |
| Frame Size                 | 100                         |            |       |         |         |
| IC Class                   | IC411                       |            |       |         |         |
| IM Class                   | IMB3 IM1001                 |            |       |         |         |
| Insulation Class           | ICLF                        |            |       |         |         |
| Invoice Description        | M2BAX 100LA2                |            |       |         |         |
| IP Class                   | IP55                        |            |       |         |         |
| Made To Order              | No                          |            |       |         |         |
| Minimum Order Quantity     | 1 piece                     |            |       |         |         |
| Number of Poles (High)     | 2                           |            |       |         |         |
| Order Multiple             | 1 piece                     |            |       |         |         |
| Package Level 1 Units      | 0 carton                    |            |       |         |         |
| Product Name               | 3-Phase squirrel cage motor |            |       |         |         |
| Product Type               | CBA2__M2BAX_CI              |            |       |         |         |
| Quote Only                 | No                          |            |       |         |         |
| Selling Unit of Measure    | piece                       |            |       |         |         |
| Standards                  | IEC 60034-1                 |            |       |         |         |
| Starting of Motor          | Direct Online               |            |       |         |         |
| Stocked At<br>(Warehouses) | Shanghai, China             |            |       |         |         |

|                         |  |
|-------------------------|--|
| Temperature Class       | --   |
| Default                 |  |
| Terminator Box Location | D-End top  |
| Two Speed Motor         | No   |
| Type of Duty            | S1   |
| UNSPSC                  | 26101100   |
| Voltage Code            | S  |
| WEEE Category           | 5. Small Equipment (No External Dimension More Than 50 cm) |