



## PRODUCT-DETAILS

# 3GBA102213-ASBCN

## No Description Available

### General Information

Product ID	3GBA102213-ASBCN
ABB Type Designation	M2BA 100LC 4
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	M2BA 100LC 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6206-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

#### Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	2.20 kW	1445 r/min	8.00 A	0.830	86.10 %	14.50 N·m	6.00
Y	--	50 Hz	380 V	2.20 kW	1445 r/min	4.60 A	0.830	86.10 %	14.50 N·m	6.00
D	--	50 Hz	230 V	2.20 kW	1450 r/min	8.10 A	0.780	85.90 %	14.40 N·m	6.40

Frame Size	100
Gross Weight	36 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 85.9 % Partial Load (75%) 85.1 % Partial Load (50%) 83.4 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 87.6 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton

Product Name	3-Phase squirrel cage motor
Product Net Weight	36 kg
Product Type	2BA2_M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class	--
Default	
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)