



PRODUCT-DETAILS

3GBA103810-ASD

IE3 Premium Efficiency Cast Iron Motors, 1.5 kW, 400 V (3GBA103810-ASD)



General Information	
Product ID	3GBA103810-ASD
ABB Type Designation	M2BAX 100LKA 6
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 1.5 kW, 400 V (3GBA103810-ASD)

Ordering	
ABB Type Designation	M2BAX 100LKA 6
Invoice Description	M2BAX 100LKA 6
Product Name	3-Phase squirrel cage motor
Product Type	EBA3__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany Shanghai, China
Medium Description	1.5kW, 6 Poles, Frame Size 100, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GBA103810-ASD)
Short Description	1.5kW, 6P, Frame Size 100, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.50 kW	952 r/min	3.64 A	0.720	82.50 %	15.05 N·m	5.60
D	--	50 Hz	230 V	1.50 kW	952 r/min	6.34 A	0.720	82.50 %	15.06 N·m	5.60
Y	--	50 Hz	380 V	1.50 kW	945 r/min	3.68 A	0.750	82.50 %	15.16 N·m	5.20
D	--	50 Hz	220 V	1.50 kW	945 r/min	6.36 A	0.750	82.50 %	15.15 N·m	5.20
Y	--	50 Hz	415 V	1.50 kW	956 r/min	3.67 A	0.690	82.50 %	14.99 N·m	5.80
Connection Configuration										Y
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										1.5 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 82.5 % Partial Load (75%) 81.8 % Partial Load (50%) 79.0 %
IE Class Data (60 Hz)										IE Class IE2 Full Load (100%) 86.5 % Partial Load (75%) 85.5 % Partial Load (50%) 83.0 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										6
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Cast Iron
Frame Size	100
Bearing	6206-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	411 mm
Product Net Height	240 mm
Product Net Width	200 mm
Product Net Weight	37 kg

Gross Weight	42 kg
--------------	-------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

