



PRODUCT-DETAILS

3GBA102510-ADCCNHA
M2BAX 100LA4

General Information

| | |
|----------------------|--------------------|
| Product ID | 3GBA102510-ADCCNHA |
| ABB Type Designation | M2BAX 100LA4 |
| Catalog Description | M2BAX 100LA4 |

Additional Information

| | |
|-----------------------|----------------|
| ABB Type Designation | M2BAX 100LA4 |
| Altitude | 1000 m |
| Ambient Temperature | 40 °C |
| Bearing | 6306-2RS1/C3WT |
| Bearing NDE | 6305-2RS1/C3WT |
| Country of Origin | China (CN) |
| Customs Tariff Number | 85015100 |
| Direction of Rotation | Both sides |

Electrical Data

| Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor | Efficiency | Torque | IS/IN |
|------|------------|-------|---------|---------|------------|---------|--------------|------------|-----------|-------|
| D | -- | 50 Hz | 380 V | 2.20 kW | 1437 r/min | 4.84 A | 0.820 | 84.30 % | 14.50 N·m | 6.70 |
| D | -- | 50 Hz | 400 V | 2.20 kW | 1437 r/min | 4.84 A | 0.820 | 84.30 % | 14.50 N·m | 6.70 |

| | |
|------------------------|---|
| Frame Size | 100 |
| Gross Weight | 31 kg |
| IC Class | IC411 |
| IE Class Data (50 Hz) | IE Class IE2 Full Load (100%) 84.3 % Partial Load (75%) 84.1 % Partial Load (50%) 82.9 % |
| IM Class | IMB3 IM1001 |
| Insulation Class | ICLF |
| Invoice Description | M2BAX 100LA4 |
| IP Class | IP55 |
| Lubrication | For life |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Number of Poles (High) | 4 |
| Order Multiple | 1 piece |
| Package Level 1 Units | 0 carton |
| Product Name | 3-Phase squirrel cage motor |
| Product Net Weight | 31 kg |

| | |
|------------------------------|--|
| Product Type | CBA2_M2BAX_CI |
| Quote Only | No |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Starting of Motor | Direct Online |
| Stocked At (Warehouses) | Shanghai, China Guangzhou, China |
| Temperature Class Default | -- |
| Temperature Rise | 80 K |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | D |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |