



PRODUCT-DETAILS

3GBA102510-HSVCN

No Description Available

General Information	
Product ID	3GBA102510-HSVCN
ABB Type Designation	M2BAK100LA4
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BAK100LA4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6206-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	2.20 kW	1450 r/min	8.06 A	0.790	89.20 %	14.49 N·m	68.54
Y	--	50 Hz	380 V	2.20 kW	1450 r/min	4.67 A	0.790	89.20 %	14.49 N·m	39.62

Frame Material	Cast Iron
Frame Size	100
Gross Weight	46 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE4 Full Load (100%) 89.2 % Partial Load (75%) 89.8 % Partial Load (50%) 89.2 %
IM Class	IMB35 IM2001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4

Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor
Product Net Weight	46 kg
Product Type	CBK4__M2BAK_IE4_CI
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S