



PRODUCT-DETAILS

3GBA103510-BSVCN

No Description Available

General Information	
Product ID	3GBA103510-BSVCN
ABB Type Designation	M2BAK100LA6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BAK100LA6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6206-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	1.50 kW	955 r/min	6.45 A	0.710	85.20 %	15.00 N-m	45.18
Y	--	50 Hz	380 V	1.50 kW	955 r/min	3.74 A	0.710	85.20 %	15.00 N-m	26.18

Frame Size	100
Gross Weight	46 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE4
	Full Load (100%) 85.9 %
	Partial Load (75%) 86.3 %
	Partial Load (50%) 85.2 %
IE Class Data (60 Hz)	IE Class NA
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor

Product Net Weight	46 kg
Product Type	CBK4__M2BAK_IE4_CI
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S