



PRODUCT-DETAILS

3GBA103520-BSEIN  
M2BAX 100LB 6

General Information

Product ID	3GBA103520-BSEIN
ABB Type Designation	M2BAX 100LB 6
Catalog Description	M2BAX 100LB 6

Additional Information

ABB Type Designation	M2BAX 100LB 6
Altitude	1000 m
Ambient Temperature	50 °C
Bearing	6206-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	India (IN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.50 kW	946 r/min	4.00 A	0.720	76.00 %	15.00 N·m	4.70
Y	--	50 Hz	415 V	1.50 kW	950 r/min	3.90 A	0.710	76.00 %	15.00 N·m	5.00

Frame Material	Cast Iron
Frame Size	100
Gross Weight	38 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE1 Full Load (100%) 76.0 % Partial Load (75%) 75.3 % Partial Load (50%) 71.2 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
Invoice Description	M2BAX 100LB 6
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	33 kg

Product Type	IBA1_M2BAX_IE1_CI
Quote Only	No
Selling Unit of Measure	piece
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S