



PRODUCT-DETAILS

# 3GBA104442-HGB

## No Description Available

General Information	
Product ID	3GBA104442-HGB
ABB Type Designation	M2BA 100 LB 8
EAN	3GBA104442-HGB
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 100 LB 8
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6206-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	Spain (ES) India (IN) China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
EAN	3GBA104442-HGB
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
Y	--	50 Hz	415 V	0.75 kW	710 r/min	2.10 A	0.650

Frame Size	100
Gross Weight	35 kg
IC Class	IC411
IM Class	IMB35 IM2001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	8
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	34 kg

Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	G
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)