

PRODUCT-DETAILS

3GBA112410-BDD

IE3 Premium Efficiency Cast Iron Motors, 4 kW, 400 V (3GBA112410-BDD)



General Information	
Product ID	3GBA112410-BDD
ABB Type Designation	M2BAX 112MLA 4
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 4 kW, 400 V (3GBA112410-BDD)

Ordering	
ABB Type Designation	M2BAX 112MLA 4
Invoice Description	M2BAX 112MLA 4
Product Name	3-Phase squirrel cage motor
Product Type	EBA3__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany
Medium Description	4kW, 4 Poles, Frame Size 112, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GBA112410-BDD)
Short Description	4kW, 4P, Frame Size 112, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	4.00 kW	1449 r/min	4.72 A	0.800	88.60 %	26.47 N·m	9.70
D	--	50 Hz	400 V	4.00 kW	1449 r/min	8.15 A	0.800	88.60 %	26.47 N·m	9.70
Y	--	50 Hz	660 V	4.00 kW	1443 r/min	4.76 A	0.830	88.60 %	26.59 N·m	8.90
D	--	50 Hz	380 V	4.00 kW	1443 r/min	8.26 A	0.830	88.60 %	26.59 N·m	8.90

Connection Configuration	D
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	4 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 88.6 % Partial Load (75%) 88.7 % Partial Load (50%) 87.9 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 89.5 % Partial Load (75%) 89.0 % Partial Load (50%) 87.3 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Cast Iron
Frame Size	112
Bearing	6206-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	456 mm
Product Net Height	252 mm

Product Net Width	230 mm
Product Net Weight	50 kg
Gross Weight	55 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

