

PRODUCT-DETAILS

3GBA112410-BDDCN

(3GBA112410-BDDCN)



General Information	
Product ID	3GBA112410-BDDCN
ABB Type Designation	M2BAX 112MLA 4
Catalog Description	(3GBA112410-BDDCN)

Ordering	
ABB Type Designation	M2BAX 112MLA 4
Invoice Description	M2BAX112MLA4
Product Name	3-Phase squirrel cage motor
Product Type	CBA3_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Shanghai, China

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	4.00 kW	1443 r/min	4.70 A	0.810	88.60 %	26.53 N·m	9.40
Y	--	50 Hz	690 V	4.00 kW	1443 r/min	4.70 A	0.810	88.60 %	26.53 N·m	9.40
D	--	50 Hz	400 V	4.00 kW	1443 r/min	8.11 A	0.810	88.60 %	26.53 N·m	9.40
D	--	50 Hz	400 V	4.00 kW	1443 r/min	8.11 A	0.810	88.60 %	26.53 N·m	9.40
Y	--	50 Hz	660 V	4.00 kW	1436 r/min	4.75 A	0.830	88.60 %	26.72 N·m	8.70
Y	--	50 Hz	660 V	4.00 kW	1436 r/min	4.75 A	0.830	88.60 %	26.72 N·m	8.70
D	--	50 Hz	380 V	4.00 kW	1436 r/min	8.25 A	0.830	88.60 %	26.72 N·m	8.70
D	--	50 Hz	380 V	4.00 kW	1436 r/min	8.25 A	0.830	88.60 %	26.72 N·m	8.70
D	--	60 Hz	440 V	4.00 kW	1746 r/min	7.09 A	0.820	89.50 %	21.98 N·m	10.40
D	--	60 Hz	440 V	4.00 kW	1746 r/min	7.09 A	0.820	89.50 %	21.98 N·m	10.40
D	--	60 Hz	460 V	4.00 kW	1751 r/min	6.87 A	0.810	89.50 %	21.92 N·m	11.30
D	--	60 Hz	460 V	4.00 kW	1751 r/min	6.87 A	0.810	89.50 %	21.92 N·m	11.30
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 88.6 % Partial Load (75%) 88.9 % Partial Load (50%) 88.1 %
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 89.5 % Partial Load (75%) 89.6 % Partial Load (50%) 88.5 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Cast Iron
Frame Size	112
Bearing	6206-2Z/C3
Bearing NDE	6205-2Z/C3
Lubrication	For life
IM Class	IMB5 IM3001

Terminator Box Location

D-End top

Dimensions	
Package Level 1 Units	0 carton
Product Net Weight	50 kg
Gross Weight	55 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Classifications	
Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

