



PRODUCT-DETAILS

3GBA111320-HDYCN  
M2BAK 112MA2

General Information	
Product ID	3GBA111320-HDYCN
ABB Type Designation	M2BAK 112MA2
Catalog Description	M2BAK 112MA2

Additional Information	
ABB Type Designation	M2BAK 112MA2
Altitude	1000 m
Ambient Temperature	40 °C
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data				
Conn	Temp Class	Freq	Voltage	Power
D	--	50 Hz	380 V	4.00 kW

Frame Size	112
Gross Weight	42 kg
IC Class	IC411
IM Class	IMB35 IM2001
Insulation Class	ICLF
Invoice Description	M2BAK 112MA2
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	42 kg
Product Type	CBK3__M2BAK_IE3_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online

Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D