



PRODUCT-DETAILS

3GBA112212-BSBCN

No Description Available

General Information	
Product ID	3GBA112212-BSBCN
ABB Type Designation	M2BA 112MB 4
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 112MB 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6206-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Torque	IS/IN
D	--	50 Hz	220 V	4.00 kW	1420 r/min	14.50 A	0.850	26.80 N·m	6.10
Y	--	50 Hz	380 V	4.00 kW	1420 r/min	8.40 A	0.850	26.80 N·m	6.10
D	--	50 Hz	230 V	4.00 kW	1440 r/min	14.20 A	0.810	26.50 N·m	7.00

Frame Size	112
Gross Weight	44 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2
	Full Load (100%) 86.6 %
	Partial Load (75%) 87.7 %
IE Class Data (60 Hz)	IE Class IE2
	Full Load (100%) 87.7 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece

Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	44 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)