



PRODUCT-DETAILS

# 3GBA113310-ASVCN

## No Description Available

General Information	
Product ID	3GBA113310-ASVCN
ABB Type Designation	M2BAK112MA6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BAK112MA6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6206-2Z/C3
Bearing NDE	6206-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	2.20 kW	960 r/min	9.30 A	0.710	87.20 %	21.88 N·m	65.13
Y	--	50 Hz	380 V	2.20 kW	960 r/min	5.39 A	0.710	87.20 %	21.88 N·m	37.73

Frame Size	112
Gross Weight	58 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE4
	Full Load (100%) 87.4 %
	Partial Load (75%) 88.1 %
	Partial Load (50%) 87.2 %
IE Class Data (60 Hz)	IE Class NA
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor

Product Net Weight	58 kg
Product Type	CBK4__M2BAK_IE4_CI
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S