



PRODUCT-DETAILS

3GBA132410-ASD

IE3 Premium Efficiency Cast Iron Motors, 7.5 kW, 400 V (3GBA132410-ASD)



General Information

Product ID	3GBA132410-ASD
ABB Type Designation	M2BAX 132MLA 4
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 7.5 kW, 400 V (3GBA132410-ASD)

Ordering

ABB Type Designation	M2BAX 132MLA 4
Invoice Description	M2BAX 132MLA 4
Product Name	3-Phase squirrel cage motor
Product Type	EBA3_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220
Replaced Product ID (OLD)	3GBA132250-ASD
Stocked At (Warehouses)	Menden, Germany Shanghai, China
Medium Description	7.5kW, 4 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GBA132410-ASD)
Short Description	7.5kW, 4P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	7.50 kW	1461 r/min	13.90 A	0.860	90.40 %	49.07 N·m	7.90
D	--	50 Hz	230 V	7.50 kW	1461 r/min	24.20 A	0.860	90.40 %	49.09 N·m	7.90
Y	--	50 Hz	380 V	7.50 kW	1456 r/min	14.30 A	0.880	90.40 %	49.25 N·m	7.20
D	--	50 Hz	220 V	7.50 kW	1456 r/min	24.70 A	0.880	90.40 %	49.24 N·m	7.20

Connection Configuration	Y
Temperature Class	--
Default	
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	7.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 90.4 % Partial Load (75%) 91.0 % Partial Load (50%) 90.9 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 91.7 % Partial Load (75%) 91.7 % Partial Load (50%) 90.9 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Cast Iron
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	586 mm
Product Net Height	302 mm
Product Net Width	262 mm
Product Net Weight	84 kg
Gross Weight	89 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

