


PRODUCT-DETAILS

3GBA133110-BDT

M2BAX 132SA 6



General Information	
Product ID	3GBA133110-BDT
ABB Type Designation	M2BAX 132SA 6
Catalog Description	M2BAX 132SA 6

Ordering	
ABB Type Designation	M2BAX 132SA 6
Invoice Description	M2BAX 132SA 6
Product Name	3-Phase squirrel cage motor
Product Type	EBA1__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	3.00 kW	966 r/min	4.69 A	0.640	79.70 %	29.43 N-m	5.50
D	--	50 Hz	400 V	3.00 kW	966 r/min	8.09 A	0.640	79.70 %	29.43 N-m	5.50
Y	--	50 Hz	660 V	3.00 kW	962 r/min	4.62 A	0.680	79.70 %	29.55 N-m	5.30
D	--	50 Hz	380 V	3.00 kW	962 r/min	8.03 A	0.680	79.70 %	29.55 N-m	5.30
D	--	60 Hz	440 V	3.00 kW	1167 r/min	7.36 A	0.630	83.50 %	24.36 N-m	5.90
D	--	60 Hz	460 V	3.00 kW	1170 r/min	7.46 A	0.590	83.50 %	24.30 N-m	6.10

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE1 Full Load (100%) 79.7 % Partial Load (75%) 78.8 % Partial Load (50%) 76.6 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 83.5 % Partial Load (75%) 82.0 % Partial Load (50%) 79.1 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Cast Iron
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	57 kg
Gross Weight	62 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE1 Standard Efficiency Cast Iron Motors

