



PRODUCT-DETAILS

# 3GBA133214-ASBCN

## No Description Available

General Information	
Product ID	3GBA133214-ASBCN
ABB Type Designation	M2BA 132SMF 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 132SMF 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Torque	IS/IN
D	--	50 Hz	220 V	5.50 kW	960 r/min	22.60 A	0.750	54.70 N·m	4.80
Y	--	50 Hz	380 V	5.50 kW	960 r/min	12.90 A	0.750	54.70 N·m	4.80
D	--	50 Hz	230 V	5.50 kW	965 r/min	22.30 A	0.710	54.40 N·m	5.10

Frame Size	132
Gross Weight	86 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 86.0 % Partial Load (75%) 86.6 % Partial Load (50%) 85.5 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	86 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)