



PRODUCT-DETAILS

3GBA133214-JDB

No Description Available

General Information											
Product ID	3GBA133214-JDB										
ABB Type Designation	M2BA 132SMF 6										
Catalog Description	No Description Available										
Additional Information											
ABB Type Designation	M2BA 132SMF 6										
Altitude	1000 m										
Ambient Temperature	40 °C										
Bearing	6208-2Z/C3										
Bearing NDE	6208-2Z/C3										
Country of Origin	India (IN) China (CN)										
Customs Tariff Number	85015220										
Direction of Rotation	Both sides										
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	Y	--	50 Hz	690 V	5.50 kW	965 r/min	7.40 A	0.710	86.10 %	54.40 N·m	5.10
	D	--	50 Hz	400 V	5.50 kW	965 r/min	12.90 A	0.710	86.10 %	54.40 N·m	5.10
	D	--	60 Hz	460 V	5.50 kW	1170 r/min	11.20 A	0.700	87.50 %	44.80 N·m	5.70
Frame Size	132										
Gross Weight	89 kg										
IC Class	IC411										
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 86.1 % Partial Load (75%) 86.6 % Partial Load (50%) 85.5 %										
IM Class	IMB34 IM2101										
Insulation Class	ICLF										
IP Class	IP55										
Lubrication	For life										
Made To Order	No										
Minimum Order Quantity	1 piece										
Number of Poles (High)	6										
Package Level 1 Units	0 carton										
Product Name	3-Phase squirrel cage motor										
Product Net Weight	86 kg										

Product Type	2BA2 _ M2BA _ IE2 _ CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)