



PRODUCT-DETAILS

3GBA131214-ADB

No Description Available

| General Information | | | | | | | | | | |
|------------------------|------------|-------|---------|---------|------------|---------|---|------------|-----------|-------|
| Product ID | | | | | | | 3GBA131214-ADB | | | |
| ABB Type Designation | | | | | | | M2BA 132SMC 2 | | | |
| Catalog Description | | | | | | | No Description Available | | | |
| Additional Information | | | | | | | | | | |
| ABB Type Designation | | | | | | | M2BA 132SMC 2 | | | |
| Altitude | | | | | | | 1000 m | | | |
| Ambient Temperature | | | | | | | 40 °C | | | |
| Bearing | | | | | | | 6208-2Z/C3 | | | |
| Bearing NDE | | | | | | | 6208-2Z/C3 | | | |
| Country of Origin | | | | | | | India (IN) China (CN) Poland (PL) | | | |
| Customs Tariff Number | | | | | | | 85015220 | | | |
| Electrical Data | | | | | | | | | | |
| Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor | Efficiency | Torque | IS/IN |
| Y | -- | 50 Hz | 690 V | 7.50 kW | 2890 r/min | 8.30 A | 0.890 | 88.20 % | 24.90 N·m | 7.30 |
| D | -- | 50 Hz | 400 V | 7.50 kW | 2890 r/min | 13.70 A | 0.890 | 88.20 % | 24.90 N·m | 7.30 |
| D | -- | 60 Hz | 460 V | 7.50 kW | 3505 r/min | 12.10 A | 0.880 | 89.50 % | 20.48 N·m | 8.30 |
| Frame Size | | | | | | | 132 | | | |
| Gross Weight | | | | | | | 75 kg | | | |
| IC Class | | | | | | | IC411 | | | |
| IE Class Data (50 Hz) | | | | | | | IE Class IE2 Full Load (100%) 88.2 % Partial Load (75%) 88.8 % Partial Load (50%) 87.6 % | | | |
| IE Class Data (60 Hz) | | | | | | | IE Class IE2 Full Load (100%) 89.5 % | | | |
| IM Class | | | | | | | IMB3 IM1001 | | | |
| Insulation Class | | | | | | | ICLF | | | |
| IP Class | | | | | | | IP55 | | | |
| Lubrication | | | | | | | For life | | | |
| Made To Order | | | | | | | No | | | |
| Minimum Order Quantity | | | | | | | 1 piece | | | |
| Number of Poles (High) | | | | | | | 2 | | | |
| Package Level 1 Units | | | | | | | 0 carton | | | |
| Product Name | | | | | | | 3-Phase squirrel cage motor | | | |

| | |
|------------------------------|--|
| Product Net Weight | 70 kg |
| Product Type | 2BA2_M2BA_IE2_CI |
| Quote Only | No |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Starting of Motor | Direct Online |
| Stocked At (Warehouses) | Shanghai, China |
| Temperature Class Default | -- |
| Terminator Box Location | Top |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | D |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |