



PRODUCT-DETAILS

3GBA161041-ASG

No Description Available

"No longer for sale" replaced by 3GBA161044-

General Information

Product ID	3GBA161041-ASG
ABB Type Designation	M2BA 160MLA 2
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M2BA 160MLA 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6209-2Z/C3
Bearing NDE	6209-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	230 V	11.00 kW	2921 r/min	35.10 A	0.890
Y	--	50 Hz	400 V	11.00 kW	2921 r/min	20.20 A	0.890
Y	--	50 Hz	415 V	11.00 kW	2927 r/min	19.80 A	0.870
Y	--	60 Hz	460 V	11.00 kW	3533 r/min	17.50 A	0.890

Frame Size	160
Gross Weight	118 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Moment of Inertia	0.00000 kg/m³
Number of Poles (High)	2
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor
Product Net Weight	118 kg
Product Type	2BA1__M2BA_IE1_CI
Quote Only	No
Replaced Product ID (OLD)	3GAA161111-ASA

Replacement Product ID (NEW)	3GBA161044-ASG
Selling Unit of Measure	piece
Service Factor	0.00
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S