

PRODUCT-DETAILS

# 3GBA132210-ASD

## IE3 Premium Efficiency Cast Iron Motors, 5.5 kW, 400 V (3GBA132210-ASD)



General Information	
Product ID	3GBA132210-ASD
ABB Type Designation	M2BAX 132SMA 4
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 5.5 kW, 400 V (3GBA132210-ASD)

Ordering	
ABB Type Designation	M2BAX 132SMA 4
Invoice Description	M2BAX 132SMA 4
Product Name	3-Phase squirrel cage motor
Product Type	EBA3__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany Shanghai, China
Medium Description	5.5kW, 4 Poles, Frame Size 132, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GBA132210-ASD)
Short Description	5.5kW, 4P, Frame Size 132, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
Y	--	50 Hz	400 V	5.50 kW	1461 r/min	11.10 A	0.800	89.60 %	35.99 N-m	7.20	
D	--	50 Hz	230 V	5.50 kW	1461 r/min	19.30 A	0.800	89.60 %	36.00 N-m	7.20	
Y	--	50 Hz	380 V	5.50 kW	1456 r/min	11.40 A	0.820	89.60 %	36.11 N-m	6.60	
D	--	50 Hz	220 V	5.50 kW	1456 r/min	19.60 A	0.820	89.60 %	36.10 N-m	6.60	
Connection Configuration										Y	
Temperature Class Default										--	
Input Voltage (U <sub>in</sub> )										400 V	
Frequency (f)										50 Hz	
Output Power										5.5 kW	
Altitude										1000 m	
Ambient Temperature										40 °C	
IC Class										IC411	
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 89.6 % Partial Load (75%) 90.1 % Partial Load (50%) 89.8 %	
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 91.7 % Partial Load (75%) 91.4 % Partial Load (50%) 90.4 %	
IP Class										IP55	
Insulation Class										ICLF	
Direction of Rotation										Both sides	
Number of Poles (High)										4	
Two Speed Motor										No	
Type of Duty										S1	
Voltage Code										S	

Mechanical

Frame Material	Cast Iron
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	521 mm
Product Net Height	302 mm

Product Net Width	262 mm
Product Net Weight	67 kg
Gross Weight	72 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

