



PRODUCT-DETAILS

# 3GBA132310-BDCCN

## (3GBA132310-BDCCN)



General Information	
Product ID	3GBA132310-BDCCN
ABB Type Designation	M2BAX 132MA 4
Catalog Description	(3GBA132310-BDCCN)

Ordering	
ABB Type Designation	M2BAX 132MA 4
Invoice Description	M2BAX 132MA 4
Product Name	3-Phase squirrel cage motor
Product Type	CBA2__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Shanghai, China Guangzhou, China China

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	7.50 kW	1457 r/min	9.27 A	0.770	88.70 %	49.06 N·m	7.20
D	--	50 Hz	400 V	7.50 kW	1457 r/min	16.00 A	0.770	88.70 %	49.10 N·m	7.20
Y	--	50 Hz	660 V	7.50 kW	1453 r/min	9.31 A	0.800	88.70 %	49.10 N·m	6.80
D	--	50 Hz	380 V	7.50 kW	1453 r/min	16.20 A	0.800	88.70 %	49.10 N·m	6.80
D	--	60 Hz	440 V	7.50 kW	1759 r/min	14.30 A	0.770	89.50 %	40.53 N·m	7.80
D	--	60 Hz	460 V	7.50 kW	1762 r/min	14.20 A	0.750	89.50 %	40.44 N·m	8.30

Temperature Class Default	--
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 88.7 % Partial Load (75%) 88.6 % Partial Load (50%) 87.4 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 89.5 % Partial Load (75%) 88.8 % Partial Load (50%) 87.1 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Cast Iron
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Lubrication	For life
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	70 kg
Gross Weight	75 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Classifications	
Standards	IEC 60034-1
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Cast Iron Motors

