




PRODUCT-DETAILS

3GBA161410-BDC

IE2 High Efficiency Cast Iron Motors, 11 kW, 400 V (3GBA161410-BDC)



General Information

Product ID	3GBA161410-BDC
ABB Type Designation	M2BAX 160MLA 2
Catalog Description	IE2 High Efficiency Cast Iron Motors, 11 kW, 400 V (3GBA161410-BDC)

Ordering

ABB Type Designation	M2BAX 160MLA 2
Invoice Description	M2BAX 160MLA 2
Product Name	3-Phase squirrel cage motor
Product Type	EBA2_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Poland (PL)
Customs Tariff Number	85015230
Stocked At (Warehouses)	Menden, Germany
Medium Description	11kW, 2 Poles, Frame Size 160, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GBA161410-BDC)
Short Description	11kW, 2P, Frame Size 160, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	11.00 kW	2931 r/min	12.00 A	0.860	89.40 %	35.87 N·m	6.60
D	--	50 Hz	400 V	11.00 kW	2931 r/min	20.70 A	0.860	89.40 %	35.87 N·m	6.60
Y	--	50 Hz	660 V	11.00 kW	2919 r/min	12.30 A	0.880	89.40 %	35.90 N·m	6.20
D	--	50 Hz	380 V	11.00 kW	2919 r/min	21.30 A	0.880	89.40 %	35.87 N·m	6.20
D	--	60 Hz	440 V	11.00 kW	3529 r/min	17.90 A	0.900	90.20 %	29.68 N·m	7.40
D	--	60 Hz	460 V	11.00 kW	3535 r/min	18.20 A	0.850	90.20 %	29.63 N·m	7.70
Connection Configuration										D
Temperature Class										--
Default										
Input Voltage (U <sub>in</sub> )										400 V
Frequency (f)										50 Hz
Output Power										11 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2
										Full Load (100%) 89.4 %
										Partial Load (75%) 89.4 %
										Partial Load (50%) 88.3 %
IE Class Data (60 Hz)										IE Class IE2
										Full Load (100%) 90.2 %
										Partial Load (75%) 89.7 %
										Partial Load (50%) 88.0 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Cast Iron
Frame Size	160
Bearing	6209-2Z/C3
Bearing NDE	6209-2Z/C3
Lubrication	For life
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	586.5 mm
Product Net Height	414 mm
Product Net Width	338 mm
Product Net Weight	103 kg
Gross Weight	113 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications

Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Cast Iron Motors

