



PRODUCT-DETAILS

3GBA133310-ADCCNGA
M2BAX 132MA6

| General Information | | | | | | | | | | | |
|------------------------|---|------------|-------|---------|---------|-----------|---------|--------------|------------|-----------|-------|
| Product ID | 3GBA133310-ADCCNGA | | | | | | | | | | |
| ABB Type Designation | M2BAX 132MA6 | | | | | | | | | | |
| Catalog Description | M2BAX 132MA6 | | | | | | | | | | |
| | | | | | | | | | | | |
| Additional Information | | | | | | | | | | | |
| ABB Type Designation | M2BAX 132MA6 | | | | | | | | | | |
| Altitude | 1000 m | | | | | | | | | | |
| Ambient Temperature | 40 °C | | | | | | | | | | |
| Bearing | 6208-2Z/C3 | | | | | | | | | | |
| Bearing NDE | 6208-2Z/C3 | | | | | | | | | | |
| Country of Origin | China (CN) | | | | | | | | | | |
| Customs Tariff Number | 85015100 | | | | | | | | | | |
| Direction of Rotation | Both sides | | | | | | | | | | |
| Electrical Data | | | | | | | | | | | |
| | Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor | Efficiency | Torque | IS/IN |
| | D | -- | 50 Hz | 380 V | 4.00 kW | 959 r/min | 9.71 A | 0.740 | 84.60 % | 39.96 N·m | 6.00 |
| | D | -- | 50 Hz | 400 V | 4.00 kW | 965 r/min | 9.75 A | 0.700 | 84.60 % | 39.96 N·m | 5.70 |
| | Y | -- | 50 Hz | 660 V | 4.00 kW | 959 r/min | 5.59 A | 0.740 | 84.60 % | 39.96 N·m | 6.00 |
| Frame Size | 132 | | | | | | | | | | |
| Gross Weight | 63 kg | | | | | | | | | | |
| IC Class | IC411 | | | | | | | | | | |
| IE Class Data (50 Hz) | IE Class IE2 Full Load (100%) 84.6 % Partial Load (75%) 84.2 % Partial Load (50%) 82.4 % | | | | | | | | | | |
| IM Class | IMB3 IM1001 | | | | | | | | | | |
| Insulation Class | ICLF | | | | | | | | | | |
| Invoice Description | M2BAX 132MA6 | | | | | | | | | | |
| IP Class | IP55 | | | | | | | | | | |
| Lubrication | For life | | | | | | | | | | |
| Made To Order | No | | | | | | | | | | |
| Minimum Order Quantity | 1 piece | | | | | | | | | | |
| Number of Poles (High) | 6 | | | | | | | | | | |

| | |
|------------------------------|--|
| Order Multiple | 1 piece |
| Package Level 1 Units | 0 carton |
| Product Name | 3-Phase squirrel cage motor |
| Product Net Weight | 63 kg |
| Product Type | CBA2__M2BAX_CI |
| Quote Only | No |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Starting of Motor | Frequency Converter |
| Stocked At (Warehouses) | Shanghai, China Guangzhou, China |
| Temperature Class Default | -- |
| Temperature Rise | 105 K |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | D |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |