

PRODUCT-DETAILS

3GBA133320-ADCCN (3GBA133320-ADCCN)



General Information

Product ID	3GBA133320-ADCCN
ABB Type Designation	M2BAX 132MB 6
Catalog Description	(3GBA133320-ADCCN)

Ordering

ABB Type Designation	M2BAX 132MB 6
Invoice Description	M2BAX 132MB 6
Product Name	3-Phase squirrel cage motor
Product Type	CBA2_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Shanghai, China Guangzhou, China China

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	5.50 kW	962 r/min	6.95 A	0.770	86.00 %	54.60 N·m	6.30
D	--	50 Hz	400 V	5.50 kW	962 r/min	12.00 A	0.770	86.00 %	54.57 N·m	6.30
Y	--	50 Hz	660 V	5.50 kW	958 r/min	7.08 A	0.790	86.00 %	54.84 N·m	5.70
D	--	50 Hz	380 V	5.50 kW	957 r/min	12.30 A	0.790	86.00 %	54.86 N·m	5.70
D	--	60 Hz	440 V	5.50 kW	1164 r/min	10.60 A	0.790	86.40 %	45.13 N·m	6.00
D	--	60 Hz	460 V	5.50 kW	1167 r/min	10.40 A	0.770	86.60 %	44.99 N·m	6.40

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 86.0 % Partial Load (75%) 87.6 % Partial Load (50%) 87.5 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 86.4 % Partial Load (75%) 88.1 % Partial Load (50%) 88.3 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Cast Iron
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Lubrication	For life
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	79 kg
Gross Weight	84 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

Standards	IEC 60034-1
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Cast Iron Motors

