



PRODUCT-DETAILS

3GBA161430-ADFCNKA
M2BAX 160MLC 2

General Information	
Product ID	3GBA161430-ADFCNKA
ABB Type Designation	M2BAX 160MLC 2
Catalog Description	M2BAX 160MLC 2

Additional Information	
ABB Type Designation	M2BAX 160MLC 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6209-2Z/C3
Bearing NDE	6209-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power
D	--	50 Hz	380 V	18.50 kW

Frame Size	160
Gross Weight	162 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
Invoice Description	M2BAX 160MLC 2
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor
Product Net Weight	152 kg
Product Type	CBA3_M2BAX_CI
Quote Only	No
Selling Unit of Measure	piece

Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)