



PRODUCT-DETAILS

3GBA161430-ADUCN
M2BAK 160MLC2

General Information

Product ID	3GBA161430-ADUCN
ABB Type Designation	M2BAK 160MLC2
Catalog Description	M2BAK 160MLC2

Additional Information

ABB Type Designation	M2BAK 160MLC2
Altitude	1000 m
Ambient Temperature	40 °C
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power
D	--	50 Hz	380 V	18.50 kW

Frame Size	160
Gross Weight	140 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
Invoice Description	M2BAK 160MLC2
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	140 kg
Product Type	CBK2 M2BAK IE2 CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class	--

Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)