



PRODUCT-DETAILS

3GBA161510-HDVCN

No Description Available

General Information	
Product ID	3GBA161510-HDVCN
ABB Type Designation	M2BAK160LA2
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BAK160LA2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6309-2Z/C3
Bearing NDE	6309-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	660 V	18.50 kW	2945 r/min	19.41 A	0.890	93.60 %	59.99 N·m	174.66
D	--	50 Hz	380 V	18.50 kW	2945 r/min	33.70 A	0.890	93.60 %	59.99 N·m	302.12

Frame Material	Cast Iron
Frame Size	160
Gross Weight	168 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE4 Full Load (100%) 93.6 % Partial Load (75%) 94.1 % Partial Load (50%) 93.6 %
IM Class	IMB35 IM2001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	2

Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor
Product Net Weight	168 kg
Product Type	CBK4__M2BAK_IE4_CI
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D