



PRODUCT-DETAILS

3GBA162410-ADFCN

IE3 Premium Efficiency Cast Iron Motors, 11 kW, 400 V (3GBA162410-ADFCN)



General Information	
Product ID	3GBA162410-ADFCN
ABB Type Designation	M2BAX 160MLA 4
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 11 kW, 400 V (3GBA162410-ADFCN)

Ordering	
ABB Type Designation	M2BAX 160MLA 4
Invoice Description	M2BAX 160MLA 4
Product Name	3-Phase squirrel cage motor
Product Type	CBA3__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015230
Medium Description	11kW, 4 Poles, Frame Size 160, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GBA162410-ADFCN)
Short Description	11kW, 4P, Frame Size 160, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	11.00 kW	1474 r/min	12.40 A	0.810	91.40 %	71.23 N·m	8.50
D	--	50 Hz	400 V	11.00 kW	1474 r/min	21.40 A	0.810	91.40 %	71.22 N·m	8.50
Y	--	50 Hz	660 V	11.00 kW	1471 r/min	12.70 A	0.830	91.40 %	71.36 N·m	7.80
D	--	50 Hz	380 V	11.00 kW	1471 r/min	22.00 A	0.830	91.40 %	71.37 N·m	7.90
D	--	60 Hz	440 V	11.00 kW	1775 r/min	19.30 A	0.810	92.40 %	59.16 N·m	9.20
D	--	60 Hz	460 V	11.00 kW	1777 r/min	18.90 A	0.790	92.40 %	59.09 N·m	9.90
Connection Configuration										D
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										11 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 91.4 % Partial Load (75%) 91.7 % Partial Load (50%) 91.2 %
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 92.4 % Partial Load (75%) 92.3 % Partial Load (50%) 91.4 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Cast Iron
Frame Size	160
Bearing	6309-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth /	626.5 mm

Length	
Product Net Height	413 mm
Product Net Width	338 mm
Product Net Weight	136 kg
Gross Weight	146 kg

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors	

