




PRODUCT-DETAILS

3GBA162410-HDF

IE3 Premium Efficiency Cast Iron Motors, 11 kW, 400 V (3GBA162410-HDF)



General Information

Product ID	3GBA162410-HDF
ABB Type Designation	M2BAX 160MLA 4
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 11 kW, 400 V (3GBA162410-HDF)

Ordering

ABB Type Designation	M2BAX 160MLA 4
Invoice Description	M2BAX 160MLA 4
Product Name	3-Phase squirrel cage motor
Product Type	EBA3__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Poland (PL)
Customs Tariff Number	85015230
Medium Description	11kW, 4 Poles, Frame Size 160, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB35/IM2001 Mounting (3GBA162410-HDF)
Short Description	11kW, 4P, Frame Size 160, 3PH, 400V, 50Hz, IP55, IMB35/IM2001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	11.00 kW	1477 r/min	12.20 A	0.820	91.40 %	71.27 N·m	7.60
D	--	50 Hz	400 V	11.00 kW	1477 r/min	21.10 A	0.820	91.40 %	71.27 N·m	7.60
Y	--	50 Hz	660 V	11.00 kW	1474 r/min	12.70 A	0.830	91.40 %	71.46 N·m	6.90
D	--	50 Hz	380 V	11.00 kW	1474 r/min	21.90 A	0.830	91.40 %	71.46 N·m	6.90

Connection Configuration	D
Temperature Class	--
Default	
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	11 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 91.4 % Partial Load (75%) 91.8 % Partial Load (50%) 91.1 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 92.4 % Partial Load (75%) 92.2 % Partial Load (50%) 90.9 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Cast Iron
Frame Size	160
Bearing	6209-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB35 IM2001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	626.5 mm
Product Net Height	413 mm
Product Net Width	310 mm
Product Net Weight	136 kg
Gross Weight	146 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

