



PRODUCT-DETAILS

3GBA162420-ADCCNCA
M2BAX 160MLB4

General Information											
Product ID	3GBA162420-ADCCNCA										
ABB Type Designation	M2BAX 160MLB 4										
Catalog Description	M2BAX 160MLB4										
Additional Information											
ABB Type Designation	M2BAX 160MLB 4										
Altitude	1000 m										
Ambient Temperature	40 °C										
Bearing	6209-2Z/C3										
Bearing NDE	6209-2Z/C3										
Country of Origin	China (CN)										
Customs Tariff Number	85015100										
Direction of Rotation	Both sides										
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	D	--	50 Hz	380 V	15.00 kW	1463 r/min	29.90 A	0.840	90.60 %	97.70 N·m	7.40
	Y	--	50 Hz	660 V	15.00 kW	1463 r/min	17.20 A	0.840	90.60 %	97.70 N·m	7.40
	D	--	50 Hz	400 V	15.00 kW	1468 r/min	29.10 A	0.820	90.60 %	97.70 N·m	8.00
Frame Size	160										
Gross Weight	125 kg										
IC Class	IC411										
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 90.6 % Partial Load (75%) 91.1 % Partial Load (50%) 90.5 %										
IM Class	IMB35 IM2001										
Insulation Class	ICLF										
Invoice Description	M2BAX 160MLB4										
IP Class	IP55										
Lubrication	For life										
Made To Order	No										

Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	125 kg
Product Type	CBA2__M2BAX_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Temperature Rise	80 K
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)