



PRODUCT-DETAILS

3GBA162420-BDFCNKA
M2BAX 160MLB 4

General Information					
Product ID	3GBA162420-BDFCNKA				
ABB Type Designation	M2BAX 160MLB 4				
Catalog Description	M2BAX 160MLB 4				
Additional Information					
ABB Type Designation	M2BAX 160MLB 4				
Altitude	1000 m				
Ambient Temperature	40 °C				
Bearing	6209-2Z/C3				
Bearing NDE	6209-2Z/C3				
Country of Origin	China (CN)				
Customs Tariff Number	85015100				
Direction of Rotation	Both sides				
Electrical Data					
	Conn	Temp Class	Freq	Voltage	Power
	D	--	50 Hz	380 V	15.00 kW
Frame Size	160				
Gross Weight	181 kg				
IC Class	IC411				
IM Class	IMB5 IM3001				
Insulation Class	ICLF				
Invoice Description	M2BAX 160MLB 4				
IP Class	IP55				
Made To Order	No				
Minimum Order Quantity	1 piece				
Number of Poles (High)	4				
Order Multiple	1 piece				
Package Level 1 Units	0 pallet (lift)				
Product Name	3-Phase squirrel cage motor				
Product Net Weight	171 kg				
Product Type	CBA3__M2BAX_CI				
Quote Only	No				
Selling Unit of Measure	piece				

Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)