



PRODUCT-DETAILS

3GBA163410-AST  
M2BAX 160MLA 6



General Information	
Product ID	3GBA163410-AST
ABB Type Designation	M2BAX 160MLA 6
Catalog Description	M2BAX 160MLA 6

Ordering	
ABB Type Designation	M2BAX 160MLA 6
Invoice Description	M2BAX 160MLA 6
Product Name	3-Phase squirrel cage motor
Product Type	EBA1__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	7.50 kW	977 r/min	16.30 A	0.750	84.70 %	73.19 N·m	6.40
D	--	50 Hz	230 V	7.50 kW	977 r/min	28.30 A	0.750	84.70 %	73.19 N·m	6.40
Y	--	50 Hz	380 V	7.50 kW	974 r/min	16.60 A	0.780	84.70 %	73.42 N·m	6.00
D	--	50 Hz	220 V	7.50 kW	974 r/min	28.60 A	0.780	84.70 %	73.42 N·m	6.00
Y	--	60 Hz	440 V	7.50 kW	1177 r/min	14.50 A	0.760	86.00 %	60.71 N·m	7.40
Y	--	60 Hz	460 V	7.50 kW	1180 r/min	14.40 A	0.730	86.00 %	60.60 N·m	7.30

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE1 Full Load (100%) 84.7 % Partial Load (75%) 85.0 % Partial Load (50%) 84.3 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 86.0 % Partial Load (75%) 85.4 % Partial Load (50%) 83.7 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Cast Iron
Frame Size	160
Bearing	6209-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Weight	114 kg
Gross Weight	124 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Classifications

UNSPSC	26101100
--------	----------

---

## Categories

---

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE1 Standard Efficiency Cast Iron Motors

