

TY28M-6



CABLE TIE 50LB 14IN BLUE NYLON



General Information

Extended Product Type	TY28M-6
Product ID	7TAG009270R0025
EAN	5414363075295
Catalog Description	CABLE TIE 50LB 14IN BLUE NYLON
Long Description	High Performance Cable Tie for Indoor Applications, Blue Color Nylon 6.6, Length of 361mm (14.2 Inches) for Bundle Diameter up to 102mm (4 Inches), Width of 4.67mm (0.184 Inch), Tensile Strength Rating of 220 Newtons (50 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Military Specified (MIL-SPEC MS3367-2-6), Bulk Pack

Ordering

EAN	5414363075295
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.005 lb
	2.268 g

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	14 in
	356 mm
Package Level 1 Depth / Length	20 in
	508 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	9.89 in
	251 mm
Package Level 2 Height	12 in
	305 mm
Package Level 2 Depth / Length	20.1 in
	511 mm

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	4 in

	101.6 mm
Color	Blue
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Standard
Special Functions	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standards	UL E49405
Surface Finishing	Untreated
Tensile Strength	50 lb 222 N
UPC	786210845104

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY28M-6
Instructions and Manuals	TY28M-6

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

