

# Commercial



PROSECCO PRIVE'  
SAN VENDEMIANO (TV)  
APPLICATION OF HITACHI VRF SET FREE

In the market of air conditioning for modern retail buildings, we are witnessing an increase in demand for comprehensive systems, fixtures able to simultaneously deliver cooling and heating, to adapt to the unfolding seasons and maintain the desired temperature in every area. The clientèle also need to save time, money and space in installing air conditioning systems and rightly expect the utmost flexibility to adapt them to any future modification of their needs.

We are also obviously witnessing an increase in the demand for ecologically sustainable systems that can be easily managed in order to avoid wasting energy as a consequence of room over-heating or over-cooling, as well as incorrect settings by the final user.

Utopia and VRF Set Free by HITACHI are the answer to all these requirements, and any other needs that might arise in the future.



## Indoor units



WALL	76
WALL with remote expansion valve	80
4-WAY MINI CASSETTE	82
HIGH EFFICIENCY RCI 4-WAY CASSETTE	84
SERIES k 4-WAY CASSETTE	86
SERIES i 4-WAY CASSETTE	88
2-WAY CASSETTE	90
HIGH EFFICIENCY CEILING	92
CEILING	94
MINI DUCTED	96
DUCTED Low Static Pressure	98
DUCTED Medium Static Pressure	100
DUCTED High Static Pressure	102
FLOOR	104
DX KIT	106
	108



## Ventilation

KPI - SERIES E and H	110
KPI - SERIES X	112



## Commercial Outdoor Units

Retail solutions	114
UTOPIA ES	116
UTOPIA RASC IX	118
UTOPIA IX STANDARD AND PREMIUM	124
UTOPIA IX STANDARD	130
UTOPIA IX PREMIUM	132
	144



## VRF Set Free

SET FREE Features and advantages	154
SET FREE MINI	162
SET FREE SIDE FLOW	164
SET FREE FSXN 2 & 3 PIPES	166
SET FREE FSXN1E 2 & 3 PIPES	170
SET FREE FSXNH 2 & 3 PIPES	174





# System Free Indoor Units

System Free indoor units afford the widest freedom of choice in designing air conditioning systems.

All indoor units are interchangeable and may be connected to any outdoor Commercial or Set Free unit.

Control is centralised, via the HITACHI H-Link II communication bus.

Combining different types of indoor units for an optimal air conditioning concept, this is the freedom afforded by System Free.

## Indoor units

### Utopia Range

**Utopia ES** ( Simultaneous Indoor Unit Operation)

**Utopia IVX STANDARD** ( Independent Indoor Unit Operation)

**Utopia IVX PREMIUM** ( Independent Indoor Units)

**Utopia RASC IVX** ( Independent Indoor Unit Operation)

Compatible with the same remote controllers

### Set Free Range

**FSVN2E & FSNY2E**

**FSNM VRF Side Flow**

**FSXN VRF 2 or 3 Pipes**































































































































**FSXN1E VRF 2 or 3 Pipes**

**FSXNH VRF 2 or 3 Pipes** high efficiency

Compatible with the same remote controllers



## Indoor units

		Power (HP)															
		NEW															
		0.6	0.8	1.0	1.3	1.5	1.8	2.0	2.3	2.5	3.0	4.0	5.0	6.0	8.0	10.0	
Wall	RPK																
4-Way Mini Cassette	RCIM																
4-Way Mini Cassette High Efficiency	RCI																
4-Way Mini Cassette series k	RCI Ek																
Series i 4-Way Cassette	RCI Ei																
2-Way Mini Cassette	RCD																
Ceiling High Efficiency	RPC																
Ceiling	RPC																
Mini Ducted	RPIM																
LP Ducted	RPI																
SP Ducted	RPI																
HP Ducted	RPI																
Floor	RPF																
Recessed Floor	RPFI																
KIT Expansion Valve	DX KIT																

■ Available Hitachi capacity

■ Capacity obtained with micro-switch modification

■ Possibility of adjustment in decrease only

## Air exchange

Unit for energy recovery	Air flow [m³/h]					
	250	500	800	1000	1500	2000
Celluloid Exchanger	■	■	■	■	■	■
Aluminium Exchanger		■	■	■	■	■
Celluloid Exchanger & direct expansion Battery		■	■	■		





# System Free Indoor Units

## Capacity adjustment of each unit using DIP switches

In certain situations, it is convenient to be able to adjust the capacity of indoor units, adapting the power yield to the actual installation needs. The power of each FREE

system indoor unit in the range can be precisely adjusted with a DIP switch located on the internal electronic circuit. The DIP switch allows precise adjustments, even af-

ter installation, during start up or at any time, optimising overall system performance.


Power (HP)		0.6		0.8		1.3		1.8		2.3	
Power Variation		0.6	← 0.8	0.8	← 1.0	1.3	← 1.5	1.8	← 2.0	2.3	← 2.5
Power Cooling	Kw	1.7		2.2		3.8		5.2		6.7	
Power High efficiency	Kw	1.9		2.5		4.2		5.6		7.5	
Change via Dip Switch		0.6HP	0.8HP	0.8HP	1.0HP	1.3HP	1.5HP	1.8HP	2.0HP	2.3HP	2.5HP
		Reduced set-up	Standard set-up	Reduced set-up	Standard set-up	Reduced set-up	Standard set-up	Reduced set-up	Standard set-up	Reduced set-up	Standard set-up

## Maximum compatibility – System Free


Design in new dimensions with our System Free concept. You will find the optimal solution for your customers' needs with the wide modular range of HITACHI indoor and outdoor units.

Our 63 indoor units may be combined in any way you wish. We are able to offer independently adjusted air conditioning but, if required, we can offer solutions that differentiate between rooms. Whether you choose

HITACHI commercial outdoor units in the Utopia series or VRF Set Free outdoor units, our System Free indoor units will always be perfectly matched!



# System Free Indoor Units



AEV TERRAGLIO - MESTRE - APPLICATION OF HITACHI VRF SET FREE





# System Free Indoor Units

## Wall



RPK 0.6FSN3M  
RPK 0.8FSN3M  
RPK 1.0FSN3M  
RPK 1.5FSN3M



BUILT-IN INFRA RED RECEIVER

OPTIONAL INPUTS/OUTPUTS

RPK 2.0FSN3M  
RPK 2.5FSN3M  
RPK 3.0FSN3M  
RPK 4.0FSN3M



### ELEGANT DESIGN

This line of indoor units has been developed with aesthetically pleasing front panels in order to meet today's ever increasing architecture and design needs. Special attention was paid to the smaller power units in the range.

These have in fact been totally redesigned and today feature new and elegant aesthetics.

### COMPACT AND LIGHT

Thanks to the high quality of the materials they have been constructed in and to the care taken in designing them, the new wall indoor units are

extremely small and light for easy and convenient installation.

### REMOTE OR INFRA RED CONTROLLER

The standard accessories of these indoor units include a kit for signal reception from the infra red remote controller.

the wired remote controller can also be used in any case (PC-ARF, PC-ART, PC-ARH).

# System Free Indoor Units



## TECHNICAL DATA OF INDOOR WALL UNIT - RPK

CODE		<b>NEW</b> RPK- 0.6FSN3M (4)	RPK- 0.8FSN3M	RPK- 1.0FSN3M	RPK- 1.5FSN3M	RPK- 2.0FSN3M	RPK- 2.5FSN3M	RPK- 3.0FSN3M	RPK- 4.0FSN3M
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	-	2.0	2.5	3.6	5.0	5.6	7.1	10.0
Nominal capacity in heating mode with UTOPIA systems (2)	kW	-	2.2	2.8	4	5.6	6.3	8.0	11.2
Nominal capacity in cooling mode with SETFREE systems (1)	kW	1.7	2.2	2.8	4	5.6	7.1	8.0	11.2
Nominal capacity in heating mode with SETFREE systems (2)	kW	1.9	2.5	3.2	4.8	6.3	8.5	9.0	12.5
Power Supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Input power	W	20	20	20	50	40	70	70	80
Dimensions (HxLxD)	mm	300x790x230	300x790x230	300x790x230	300x900x230	333x1150x245	333x1150x245	333x1150x245	333x1150x245
Weight	kg	10	10	10	11	17	18	18	18
Sound Pressure (L/M/H/H2) (3)	dB(A)	29/31/32/35	30/32/35/39	30/32/35/39	33/36/40/46	33/38/40/42	36/40/43/49	36/40/43/49	41/46/49/51
Sound power level at nominal output	dB(A)	49	53	53	58	57	59	59	64
Air flow (L/M/H/H2)	m³/h	360/420/ 450/480	390/420/ 480/600	390/420/ 480/600	450/540/ 660/840	600/780/ 840/900	720/840/ 1020/1140	720/840/ 1020/1140	900/1020/ 1140/1320
Piping section	mm	6.35/12.7	6.35/12.7	6.35/12.7	6.35/12.7	6.35/15.88	9.52/15.88	9.52/15.88	9.52/15.88
	inch.	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level measured at 1 metre below the unit and 1 metre from the air inlet deflector (measured in anechoic room)

(4) 0.6HP indoor units are only compatible with FSXNH and FSXN1E systems

Connectible with:



PC LH3B

PC ALHZF

PC ARH

PC ART

PC ARF

The infra red receiver is already fitted on the indoor unit (factory mounted).  
Should a wall receiver be required, use: PC ALHZF.





## System Free Indoor Units

# Wall (remote expansion valve)



RPK 0.6FSNH3M  
RPK 0.8FSNH3M  
RPK 1.0FSNH3M  
RPK 1.5FSNH3M



BUILT-IN INFRA RED RECEIVER

EXTREMELY QUIET

SUITABLE FOR HOTEL USE

OPTIONAL INPUTS/OUTPUTS

### ELEGANT DESIGN

In order to address today's ever increasing architecture and design needs, the new line of RPK indoor units with remote expansion valve has been totally restyled to give the machine a new, very pleasant and elegant appearance.

### COMPACT AND LIGHT

Thanks to the high quality of the materials they have been constructed in and to the care taken in designing them, the new wall indoor units are extremely small and light for easy and convenient installation.

### EXTREMELY LOW NOISE LEVEL

The new structure of the unit and remote expansion valve afford extremely low noise levels able to assure a highly comfortable environment.

### REMOTE OR INFRA RED CONTROLLER

The standard accessories of these indoor units include a kit for signal reception from the infra red remote controller.

the wired remote controller can also be used in any case (PC-ARF, PC-ART, PC-ARH).

EV-1.5N1 (remote expansion valve)



# System Free Indoor Units



## TECHNICAL DATA OF INDOOR WALL UNIT - RPK

CODE			NEW RPK-0.6FSNH3M (4)	RPK-0.8FSNH3M	RPK-1.0FSNH3M	RPK-1.5FSNH3M
Nominal capacity in cooling mode with UTOPIA systems (1)		kW	-	2.0	2.5	3.6
Nominal capacity in heating mode with UTOPIA systems (2)		kW	-	2.2	2.8	4
Nominal capacity in cooling mode with SETFREE systems (1)		kW	1.7	2.2	2.8	4
Nominal capacity in heating mode with SETFREE systems (2)		kW	1.9	2.5	3.2	4.8
Power Supply		V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Input power		W	20	20	20	50
Dimensions (H×L×D)		mm	300x790x230	300x790x230	300x790x230	300x900x230
Weight		kg	10	10	10	11
Sound Pressure (L/M/H/H2) (3)		dB(A)	29/31/32/35	30/32/35/39	30/32/35/39	33/36/40/46
Sound power level at nominal output		dB(A)	49	53	53	58
Air flow (L/M/H/H2)		m³/h	360/420/450/480	390/420/480/600	390/420/480/600	450/540/660/840
Piping section	Liquid line from IU to expansion valve	mm (inch.)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)
	Liquid line from expansion valve to system	mm (inch.)	6.35 (1/4)	6.35 (1/4)	6.35 (1/4)	6.35 (1/4)
	Gas line	mm (inch.)	12.7 (1/2)	12.7 (1/2)	12.7 (1/2)	12.7 (1/2)

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level measured at 1 metre below the unit and 1 metre from the air inlet deflector (measured in anechoic room)

(4) 0.6HP indoor units are only compatible with FSXNH and FSXN1E systems

Connectible with:



PC LH3B

PC ALHZF

PC ARH

PC ART

PC ARF

The infra red receiver is already fitted on the indoor unit (factory mounted).  
Should a wall receiver be required, use: PC ALHZF.





# System Free Indoor Units

## 4-Way mini cassette



RCIM 0.6FSN3 (P-N23WAM panel)  
 RCIM 0.8FSN3 (P-N23WAM panel)  
 RCIM 1.0FSN3 (P-N23WAM panel)  
 RCIM 1.5FSN3 (P-N23WAM panel)  
 RCIM 2.0FSN3 (P-N23WAM panel)



DC INVERTER MOTOR  
 STANDARD 60X60 GRILLE  
 CONDENSATE DRAIN PUMP  
 OPTIONAL INPUTS/OUTPUTS

The 4-way RCIM mini cassette indoor units are extremely quiet and compact and have a series of features that make installation easier.

Among these, height adaptability to installation, compact size, lightness and consistency of panel shape and installation positions stand out, which make connecting pipes easier.

### LOW NOISE LEVEL

The following table shows the sound levels of RCIM indoor units.

Operation sound levels dB(A)			
Model	Low	Average	High
RCIM 0.6FSN3	28	32	34
RCIM 0.8FSN3	28	34	36
RCIM 1.0FSN3	28	34	36
RCIM 1.5FSN3	33	35	38
RCIM-2.0FSN3	37	39	42

### DC MOTOR WITH REDUCED INPUT AND NOISE

Compared to traditional AC motors, DC motors feature higher efficiency and lower noise level. They are also 50% more compact and lighter than traditional motors.

### EASE OF INSTALLATION AND MAINTENANCE

With a height of just 295 mm and weight of just 17 kg, these units are easy to install also in very small spaces such as false ceilings. The square shape of the front panel, standardised with a 700 mm side, makes installation easier in 600x600 mm standard European pattern false ceilings. The suspension tie rods are located at the corners of the unit's body, which is square, and have 530 mm centre distance to change fixture orientation to match connection position with incoming piping.

The electrical panel is located inside the grille for

# System Free Indoor Units




easy access to electrical parts with no need to remove the false ceiling panels.

A compartment on each corner of the panel allows the fixture's height to be adjusted without needing to remove the panel.

## BUILT-IN CONDENSATE PUMP

The drainage system, equipped with a controlled pump depending on condensate level, is able to lift the condensate up to 600 mm above the ceiling surface.



## ADAPTABLE FOR HIGH CEILING INSTALLATIONS

Thanks to the possibility of increasing speed, (when required), the motors used give to these fixtures the required flexibility to install them in rooms with especially high ceilings (3.5 or 3.9 m).

Speed setting	Room Height	
	RCIM 1.5FSN3	RCIM 2.0FSN3
Standard	Lower than 2.5 m	Lower than 2.7 m
Speed (1)	2.5 - 2.9 m	2.7 - 3.1 m
Speed (2)	2.9 - 3.9 m	3.1 - 3.5 m

## TECHNICAL DATA OF 4-WAY MINICASSETTE UNIT - RCIM

CODE		NEW				
		RCIM-0.6FSN3 (4)	RCIM-0.8FSN3	RCIM-1.0FSN3	RCIM-1.5FSN3	RCIM-2.0FSN3 (5)
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	-	2.0	2.5	3.6	5.0
Nominal capacity in heating mode with UTOPIA systems (2)	kW	-	2.2	2.8	4.0	5.6
Nominal capacity in cooling mode with SETFREE systems (1)	kW	1.7	2.2	2.8	4.0	5.6
Nominal capacity in heating mode with SETFREE systems (2)	kW	1.9	2.5	3.2	4.8	6.3
Power Supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Input power	W	50	60	60	70	70
Dimensions (HxLxD)	mm	295x570x570	295x570x570	295x570x570	295x570x570	295x570x570
Weight	kg	17	17	17	17	17
Sound Pressure (L/M/H) (3)	dB(A)	28/32/34	28/34/36	28/34/36	33/35/38	37/39/42
Sound power level at nominal output	dB(A)	54	56	56	58	60
Air flow (L/M/H)	m³/h	600/660/720	600/720/780	600/720/780	720/810/900	720/840/960
Condensate drain pump lift	mm	650mm from the lower edge of the unit				
Piping section	mm	6.35/12.7	6.35/12.7	6.35/12.7	6.35/12.7	6.35/15.88
	inch.	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 5/8

## PANEL FOR CASSETTE

CODE	code	P-N23WAM	P-N23WAM	P-N23WAM	P-N23WAM	P-N23WAM
Dimensions (HxLxD)	mm	35x700x700	35x700x700	35x700x700	35x700x700	35x700x700
Weight	kg	3.5	3.5	3.5	3.5	3.5

- (1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.  
 (2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.  
 (3) Sound pressure level measured at 1.5 metres below the unit (measured in anechoic room with no reflection)  
 (4) 0.6HP indoor units are only compatible with FSXNH and FSXN1E systems  
 (5) The combination of MONO with Utopia IVX Standard and Premium is not allowed

Connectible with:



PC LH3A

PC ALHC

PC ALHZ

PC ARH

PC ART

PC ARF




# System Free Indoor Units

## High efficiency RCI 4-way cassette




RCI 1.0~6.0FSN3  
(PAP160NA1 panel  
PAP160NAE optional)



- DC INVERTER MOTOR
- INDEPENDENT FLAPS
- DC CONDENSATE DRAIN PUMP
- MOTION SENSOR
- OPTIONAL INPUTS/OUTPUTS

### EXTREMELY HIGH ENERGY EFFICIENCY

Thanks to a new heat exchanger, completely re-designed and consisting in piping of just 5 mm diameter, a new turbo fan with 3D curve blades and the condensate drain pump with DC motor, the energy efficiency of 4-way cassette indoor units has significantly increased. The already high energy is further increased by the new optional panel with built-in motion sensor (P AP160NAE). In fact, thanks to its ability to




analyse people's activity in the room, the indoor unit is able to modify its operation and adapt the temperature setting, fan speed and air flow direction. This adjusts operation to the actual activity, improves comfort and reduces energy

consumption.

### IDEAL COMFORT

The air flow louvers have been completely re-designed to prevent any discomfort due to any output temperature unevenness and cold air drafts. Each of the four louvers can also be individually controlled.



### ADAPTABILITY TO HIGH CEILINGS

The possibility to increase motor speed makes these units especially flexible and able to be installed in premises with very high ceilings such as shops and shopping centres.

### ANTI-BACTERIAL CONDENSATE DRAIN

Silver ion anti-bacterial tabs have been inserted inside the condensate drain pan in order to prevent the formation of mould and bacteria.

Speed Setting	Room Height	
	(1.0-3.0) HP	(4.0-6.0) HP
Standard	Lower than 2.7m	Lower than 3.2m
Speed (1)	2.7 - 3.0m	3.2 - 3.6
Speed (2)	3.0 - 3.5m	3.6 - 4.2

### CONNECTION FLEXIBILITY

The drainage system, equipped with a controlled pump depending on condensate level, is able to lift the condensate up to 850 mm above the ceiling surface.



# System Free Indoor Units



## INSIDE UNIT WITH 4-WAY CASSETTE 90X90 - RCI

Code		RCI-1.0FSN3EK	RCI-1.5FSN3EK	RCI-2.0FSN3EK	RCI-2.5FSN3EK	RCI-3.0FSN3EK	RCI-4.0FSN3EK	RCI-5.0FSN3EK	RCI-6.0FSN3EK
Nominal cooling capacity with UTOPIA (1) systems	kW	-	3,6	5,0	6,3	7,1	10,	12,5	14,0
Nominal heating capacity with UTOPIA (2) systems	kW	-	4,0	5,6	7,0	8,0	11,2	14,0	16,0
Nominal cooling capacity with SETFREE (1) systems	kW	2,8	4,0	5,6	7,1	8,0	11,2	14,0	16,0
Nominal heating capacity with SETFREE (2) systems	kW	3,2	4,8	6,3	8,5	9,0	12,5	16,0	18,0
Power supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Power consumption	W	57	57	57	57	57	127	127	127
Dimensions (H x L x D)	mm	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840
Weight	kg	20	21	21	22	26	26	26	26
Sound Pressure (High/Medium/Low) (3)	dB(A)	30/28/27	31/30/27	32/30/27	36/32/28	36/32/28	43/39/33	45/40/35	46/41/37
Sound Pressure nominal output (Cool./Heat.)	dB(A)	ND	ND	ND	ND	ND	ND	ND	ND
Air flow rate (High/Medium/Low)	m³/h	780/660/540	1020/840/660	1020/840/660	1380/1080/840	1380/1080/840	1860/1440/1200	1980/1560/1260	2100/1680/1320
Level difference of pump condensate discharge	mm	850mm from lower edge of unit							
Piping section	mm	6,35/12,7	6,35/12,7	6,35/15,88	9,53/15,88	9,53/15,88	9,53/15,88	9,53-15,88	9,53-15,88
	poll.	1/4 - 1/2	1/4 - 1/2	1/4 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8

### PANEL FOR CASSETTES

Code	cod.	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1
Dimensions (H x L x D)	mm	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950
Weight	kg	ND	ND	ND	ND	ND	ND	ND	ND

### PANEL FOR CASSETTES WITH SENSOR

Code	cod.	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE
Dimensions (H x L x D)	mm	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950
Weight	kg	ND	ND	ND	ND	ND	ND	ND	ND

- (1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.  
 (2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.  
 (3) Sound pressure level measured at 1.5 metres below the unit (measured in anechoic room)

The use of the P-AP160NAE motion sensor requires using the PC-ARF wired controller

With PC-ART 4<sup>th</sup> speed operation is not possible  
 Connectible with:



PC LH3B

PC ALH3

PC ALH3F

PC ARH

PC ART

PC ARF



# System Free Indoor Units

## Series k 4-Way Cassette



**NEW**

**RCI 1.0~6.0FSN3**  
(PAP160NA1 panel  
PAP160NAE optional)




DC INVERTER MOTOR  
INDEPENDENT FLAPS  
MOTION SENSOR  
OPTIONAL INPUTS/OUTPUTS

HITACHI is pleased to introduce the new 4-way cassette 90x90 series K line, featuring a wealth of technological innovations and able to assure extremely high performance, low consumption and optimal comfort.

### NEW DESIGNER PANEL WITH INDEPENDENT LOUVRE CONTROL

The new ice-white designer panel allows the four louvers to be adjusted independently, thus adjusting air distribution to the needs of the people living on the premises.

Asymmetrical louver rotation around one non-baricentric axis makes it possible to give a well-defined direction to the air flow, thus preventing any annoying cold draft.



### MOTION SENSOR

Thanks to the use of the optional designer panel, fitted with motion sensor, energy consumption is reduced up to 14% (the percentage is variable depending on the type of application). Furthermore, by means of the local PC ARF control of the sensor's operating conditions may

be set at will in terms of:

- Sensor activation
- Unit behaviour in case of absence of persons on the premises: Stop unit, Thermo- off and Running
- Time interval selection: five possible settings in the interval 30 ÷ 180 minutes

Motion sensor activation will adapt the unit's set-point increasing it by 1°C every 10 minutes elapsed (30 minute setting) until going back to full functionality when the premises are occupied again.

# System Free Indoor Units



## INSIDE UNIT WITH 4-WAY CASSETTE 90X90 - RCI

Code		RCI-1.0FSN3E	RCI-1.5FSN3	RCI-2.0FSN3	RCI-2.5FSN3	RCI-3.0FSN3	RCI-4.0FSN3	RCI-5.0FSN3	RCI-6.0FSN3
Nominal cooling capacity with UTOPIA (1) systems	kW	-	3,6	5,0	6,3	7,1	10,	12,5	14,0
Nominal heating capacity with UTOPIA (2) systems	kW	-	4,0	5,6	7,0	8,0	11,2	14,0	16,0
Nominal cooling capacity with SETFREE (1) systems	kW	2,8	4,0	5,6	7,1	8,0	11,2	14,0	16,0
Nominal heating capacity with SETFREE (2) systems	kW	3,2	4,8	6,3	8,5	9,0	12,5	16,0	18,0
Power supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Power consumption	W	57	57	57	57	57	127	127	127
Dimensions (H x L x D)	mm	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840
Weight	kg	20	21	21	22	26	26	26	26
Sound Pressure (High/Medium/Low) (3)	dB(A)	30/28/27	31/30/27	32/30/27	36/32/28	36/32/28	43/39/33	45/40/35	46/41/37
Sound Pressure nominal output (Cool./Heat.)	dB(A)	ND	ND	ND	ND	ND	ND	ND	ND
Air flow rate (High/Medium/Low)	m³/h	780/660/540	1020/840/660	1020/840/660	1380/1080/840	1380/1080/840	1860/1440/1200	1980/1560/1260	2100/1680/1320
Level difference of pump condensate discharge	mm	850mm from lower edge of unit							
Piping section	mm	6,35/12,7	6,35/12,7	6,35/15,88	9,53/15,88	9,53/15,88	9,53/15,88	9,53-15,88	9,53-15,88
	poll.	1/4 - 1/2	1/4 - 1/2	1/4 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8

### PANEL FOR CASSETTES

Code	cod.	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1	P-AP160NA1
Dimensions (H x L x D)	mm	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950
Weight	kg	ND	ND	ND	ND	ND	ND	ND	ND

### PANEL FOR CASSETTES WITH SENSOR

Code	cod.	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE	P-AP160NAE
Dimensions (H x L x D)	mm	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950	47x950x950
Weight	kg	ND	ND	ND	ND	ND	ND	ND	ND

- (1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.  
 (2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.  
 (3) Sound pressure level measured at 1.5 metres below the unit (measured in anechoic room)

The use of the P-AP160NAE motion sensor requires using the PC- ARF wired controller

With PC-ART 4<sup>th</sup> speed operation is not possible  
 Connectable with:



PC LH3B



PC ALH3



PC ALH3F



PC ARH



PC ART



PC ARF





## System Free Indoor Units

# Series I 4-Way Cassette



RCI 1.0~6.0FSN3Ei  
(P-N23NA panel)



90X90 PANEL

CONDENSATE DRAIN PUMP

DC INVERTER MOTOR

OPTIONAL INPUTS/OUTPUTS

The RCI Ei 4-way Cassette units are extremely quiet and compact. The main features that afford convenient installation are adaptability of the installation height, compactness, lightness and design consistency.

### QUIET OPERATION

Thanks to the use of the Super-High-Stream turbo fan, with 3D curve blades, ventilation efficiency is increased by 20% and the sound level of some of these units is reduced up to 28 dB(A).

### ELECTRICAL ABSORPTION, LOW NOISE DC MOTOR

Unlike conventional AC motors, DC motors increase efficiency and significantly reduce electromagnetic interference. Thanks to ferrite magnetic surface rotors and a special winding

system, power consumption is considerably reduced. Efficiency is thus considerably improved as well as affording 50% gains in compactness and lightness.


### EASE OF INSTALLATION AND MAINTENANCE

Required ceiling opening between 860-910 mm, 298 mm height and a weight of just 29 kg, make these units easy to install even in the constrained space of false ceilings. The square panel shape, standardised with a 900 mm side, makes it suitable to replace lower power fixtures. The suspension tie rods located at the corners of the unit's square body have 760 mm centre distance so orientation can be changed to conveniently match connections with incoming piping. A compartment on each corner of the panel allows the fixture's height to be adjusted without

needing to remove the panel.

### CONNECTION FLEXIBILITY

The drainage system, equipped with a controlled pump depending on condensate level, is able to lift the condensate up to 850 mm above the ceiling surface.



# System Free Indoor Units



## ADAPTABILITY TO PREMISES WITH HIGH CEILINGS

The motors offer the option of increasing speed thus lending to these fixtures the required flexibility to be installed in premises with especially high ceilings (4.2 m). This feature thus makes them suitable to be used in shops and shopping centres.

Speed Setting	Room height	
	(1.0-2.5) HP	(3.0-6.0) HP
Standard	Lower than 2.7m	Lower than 3.2m
Speed (1)	2.7 - 3.0m	3.2 - 3.6
Speed (2)	3.0 - 3.5m	3.6 - 4.2

## 4-WAY CASSETTE INDOOR UNIT - RCI Ei

CODE		RCI-1.0FSN3Ei	RCI-1.5FSN3Ei	RCI-2.0FSN3Ei	RCI-2.5FSN3Ei	RCI-3.0FSN3Ei	RCI-4.0FSN3Ei	RCI-5.0FSN3Ei	RCI-6.0FSN3Ei
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	2.5	3.6	5.0	5.6	7.1	10	12.5	14.0
Nominal capacity in heating mode with UTOPIA systems (2)	kW	2.8	4.0	5.6	6.3	8.0	11.2	14.0	16.0
Nominal capacity in cooling mode with SETFREE systems (1)	kW	2.8	4.0	5.6	7.1	8.0	11.2	14.0	16.0
Nominal capacity in heating mode with SETFREE systems (2)	kW	3.2	4.8	6.3	8.5	9.0	12.5	16.0	18.0
Power Supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Input power	W	40	50	50	60	90	110	140	180
Dimensions (HxLxD)	mm	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840	248x840x840
Weight	kg	29	29	30	30	32	35	35	35
Sound Pressure (L/M/H) (3)	dB(A)	28/30/32	28/30/32	28/30/32	28/30/32	30/32/34	33/35/38	35/37/39	36/40/42
Sound power level at nominal output	dB(A)	54	54	54	54	56	60	61	64
Air flow (L/M/H)	m³/h	660/720/780	720/840/900	720/840/960	900/1020/1200	1200/1380/1560	1440/1680/1920	1500/1740/2040	1620/1920/2220
Condensate drain pump lift	mm	850mm from the lower edge of the unit							
Piping section	mm	6.35/12.7	6.35/12.7	6.35/15.88	9.52/15.88	9.53/15.88	9.53/15.88	9.53-15.88	9.53-15.88
	inch.	1/4 - 1/2	1/4 - 1/2	1/4 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8

### PANEL FOR CASSETTE

CODE	code	P-N23NA	P-N23NA	P-N23NA	P-N23NA	P-N23NA	P-N23NA	P-N23NA	P-N23NA
Dimensions (HxLxD)	mm	37x950x950	37x950x950	37x950x950	37x950x950	37x950x950	37x950x950	37x950x950	37x950x950
Weight	kg	6	6	6	6	6	6	6	6

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level measured at 1.5 metres below the unit (measured in anechoic room)

Connectible with:



PC LH3A

PC ALHC

PC ALHZ

PC ARH

PC ART

PC ARF




# System Free Indoor Units

## 2-Way cassette



RCD 1.0~5.0FSN2 (P-N23-46DNA panel)



CONDENSATE DRAIN PUMP  
OPTIONAL INPUTS/OUTPUTS

The 2-way RCD Cassette units are extremely quiet and the vertical profile has been reduced by an innovative front panel.


### QUIET OPERATION

Thanks to the use of the Super-High-Stream turbo fan, with 3D curve blades and wide intake mouth, ventilation efficiency has increased by 20% and the sound level has been reduced up to 30 dB(A), making these fixtures ideal for all applications where quietness represents an absolute must.

### COMPACT VERTICAL PROFILE


The special compact size of the turbofan employed has simplified structural issues, thus making it possible to contain fixture height in just 298 mm.

This makes installation easier in the constrained space typical of false ceilings.




### CONNECTION FLEXIBILITY

The drainage system, equipped with a controlled pump depending on condensate level, is able to lift the condensate up to 850 mm above the ceiling surface.





# System Free Indoor Units



## A FRONT PANEL IDEAL FOR ANY CEILING

These units blend in with the ceiling, from which they protrude by just 30 mm, thus making the use of ad hoc panelling possible to harmonise with any architectural setting.

## ADAPTABILITY TO PREMISES WITH HIGH CEILINGS

Thanks to the possibility of increasing speed (when required), the motor used gives to these fixtures the required flexibility to be installed in premises with especially high ceilings such as shops and shopping centres.

Speed Setting	Room Height		
	1.5~2.5 hp	3.0/4.0 hp	5 hp
Standard	2.4 m.	2.7 m.	2.9 m.
Speed (1)	2.7 m.	3.0 m.	3.2 m.
Speed (2)	2.9 m.	3.2 m.	3.4 m.

## 2-WAY CASSETTE INDOOR UNIT - RCD

CODE		RCD-1.0FSN2	RCD-1.5FSN2	RCD-2.0FSN2	RCD-2.5FSN2	RCD-3.0FSN2	RCD-4.0FSN2	RCD-5.0FSN2
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	2.5	3.6	5.0	5.6	7.1	10.0	12.5
Nominal capacity in heating mode with UTOPIA systems (2)	kW	2.8	4.0	5.6	6.3	8.0	11.2	14.0
Nominal capacity in cooling mode with SETFREE systems (1)	kW	2.8	4.0	5.6	7.1	8.0	11.2	14.0
Nominal capacity in heating mode with SETFREE systems (2)	kW	3.2	4.8	6.3	8.5	9.0	12.5	16.0
Power Supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Input power	W	60	80	80	110	110	140	200
Dimensions (H×L×D)	mm	298x860x620	298x860x620	298x860x620	298x860x620	298x860x620	298x1420x620	298x1420x620
Weight	kg	27	27	27	30	30	48	48
Sound Pressure (L/M/H) (3)	dB(A)	30/32/34	30/32/35	30/32/35	31/34/38	31/34/38	33/36/40	36/40/43
Sound power level at nominal output	dB(A)	55	56	56	59	59	60	62
Air flow (L/M/H)	m³/h	480/540/600	540/660/780	660/780/900	840/960/1140	840/960/1140	1260/1440/1740	1500/1740/2040
Condensate drain pump lift	mm	600mm from the lower edge of the unit						
Piping section	mm	6.35/12.7	6.35/12.7	6.35/15.88	9.53/15.88	9.53/15.88	9.53/15.88	9.53/15.88
	inch.	1/4 - 1/2	1/4 - 1/2	1/4 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8

## PANEL FOR CASSETTE

CODE	code	P-N23DNA	P-N23DNA	P-N23DNA	P-N23DNA	P-N23DNA	P-N46DNA	P-N46DNA
Dimensions (H×L×D)	mm	30x1100x710	30x1100x710	30x1100x710	30x1100x710	30x1100x710	30x1100x710	30x1100x710
Weight	kg	6	6	6	6	6	6	6

- (1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.  
 (2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.  
 (3) Sound pressure level measured at 1.5 metres below the unit (measured in anechoic room)

Connectible with:



PC LH3A

PC ALHD

PC ALHZ

PC ARH

PC ART

PC ARF



## System Free Indoor Units

# High efficiency ceiling



NEW

RPC 1.5-6.0FSN3



COMPACT SIZE

OPTIONAL INPUTS/OUTPUTS

### EXTREMELY HIGH ENERGY EFFICIENCY

Thanks to the use of the completely re-designed heat exchanger and the new fan with DC inverter motor, the energy efficiency of ceiling indoor units has significantly increased.

The already high efficiency and comfort are further improved by the optional motion sensor, which is able to analyse the activity of the people on the premises and to consequently modify indoor unit operation parameters such as

temperature setting, fan speed and output air flow direction.

### IDEAL COMFORT

the large output louvre has been designed to eliminate possible discomfort from uneven room temperature and cold draft effects.

Furthermore, a completely re-designed output fan achieves a very low sound level.

### ADAPTABILITY TO HIGH CEILINGS

The possibility to increase motor speed makes these units especially flexible and able to be installed in premises with very high ceilings such as shops and shopping centres.

# System Free Indoor Units



## INDOOR CEILING UNIT - RPC


CODE		RPC-1.5FSN3	RPC-2.0FSN3	RPC-2.5FSN3	RPC-3.0FSN3	RPC-4.0FSN3	RPC-5.0FSN3	RPC-6.0FSN3
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	3.6	5.0	5.6	7.1	10.0	12.5	14
Nominal capacity in heating mode with UTOPIA systems (2)	kW	4.0	5.6	6.3	8.0	11.2	14.0	16
Nominal capacity in cooling mode with SETFREE systems (1)	kW	4.0	5.6	7.1	8.0	11.2	14.0	16
Nominal capacity in heating mode with SETFREE systems (2)	kW	4.8	6.3	8.5	9.0	12.5	16.0	18
Power Supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Input power	W	40	50	50	60	100	160	190
Dimensions (HxLxD)	mm	235x960 x690	235x960 x690	235x960 x690	235x960 x690	235x1580 x690	235x1580 x690	235x1580 x690
Weight	kg	26	27	35	35	41	41	41
Sound Pressure (L/M/H) (3)	dB(A)	28/31/35/37	28/31/35/38	28/31/35/38	29/33/37/40	32/37/42/44	35/41/45/48	36/42/47/49
Sound power level at nominal output	dB(A)	53	54	54	56	60	64	65
Air flow (L/M/H/H2)	m³/h	540/660/ 780/900	540/660/ 780/900	690/840/ 990/1140	750/930/ 1110/1260	1020/1320/ 1590/1800	1200/1530/ 1860/2100	1260/1620/ 1950/2220
Piping section	mm	6.35/12.7	6.35/15.88	9.52/15.88	9.53/15.88	9.53/15.88	9.53/15.88	9.53/15.88
	inch.	1/4 - 1/2	1/4 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level measured at 1 metre below the unit and 1 metre from the air inlet deflector (measured in anechoic room)

Connectible with:



PC-LH3B

SOR-NEP

PC-ALHP1

PC ARH

PC ART

PC ARF





# System Free Indoor Units

## Ceiling



RPC 2.0~6.0FSN2E



COMPACT SIZE


OPTIONAL INPUTS/OUTPUTS

RPC ceiling indoor units are easily installed. They feature elegant design, automatic motion output deflector and especially quiet operation.

### ELEGANT DESIGN


The use of a fan and heat exchanger constructed with an innovative concept has led to producing these extremely modern, extra-flat units.

Fully adjustable suspension brackets mean they can be inserted in false ceilings, from which they only protrude by 150 mm.



### EASE AND FLEXIBILITY OF INSTALLATION

In order to increase installation and positioning options, these units offer the possibility to connect the drainage line in two different positions and to connect refrigerant lines on the right or left side or rear.



### AUTOMATIC MOTION DEFLECTOR

The combination of multi-blade centrifugal fan and automatic motion output deflector creates a powerful and quiet air flow, which is evenly distributed throughout the premises assuring comfort and low noise level.

# System Free Indoor Units



## INDOOR CEILING UNIT - RPC

CODE		RPC-2.0FSN3E	RPC-2.5FSN3E	RPC-3.0FSN3E	RPC-4.0FSN3E	RPC-5.0FSN3E	RPC-6.0FSN3E
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	5.0	5.6	7.1	10.0	12.5	14.0
Nominal capacity in heating mode with UTOPIA systems (2)	kW	5.6	6.3	8.0	11.2	14.0	16.0
Nominal capacity in cooling mode with SETFREE systems (1)	kW	5.6	7.1	8.0	11.2	14.0	16.0
Nominal capacity in heating mode with SETFREE systems (2)	kW	6.3	8.5	9.0	12.5	16.0	18.0
Power Supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Input power	W	130	130	180	180	230	230
Dimensions (H×L×D)	mm	163x1314x625	163x1314x625	225x1314x625	225x1314x625	225x1574x625	225x1574x625
Weight	kg	31	31	35	35	41	41
Sound Pressure (L/M/H) (3)	dB(A)	41/43/46	42/45/48	39/45/49	39/45/49	41/46/49	44/48/50
Sound Power level at nominal output	dB(A)	60	60	65	65	65	66
Air flow (L/M/H)	m³/h	720/960/1080	900/1020/1260	960/1260/1620	1140/1440/1800	1260/1680/2100	1620/1920/2220
Piping section	mm	6.35/15.88	9.53/15.88	9.53/15.88	9.53/15.88	9.53/15.88	9.53/15.88
	inch.	1/4 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level measured at 1 metre below the unit and 1 metre from the air inlet deflector (measured in anechoic room)

Connectible with:



PC LH3A

PC ALHZ

PC ARH

PC ART

PC ARF



# System Free Indoor Units

## Mini Ducted



RPIM 0.6-1.5FSN4E



DC INVERTER MOTOR

CONDENSATE DRAIN PUMP

VARIABLE STATIC PRESSURE

OPTIONAL INPUTS/OUTPUTS

### EFFICIENT AND QUIET

HITACHI is pleased to introduce the new ducted mini indoor unit, RPIM, with DC Inverter control motor.

Thanks to this new technology, the indoor unit can reduce its electrical consumption up to 70% compared to the previous model and always assures correct air output to the premises with very low sound level. This translates into an improvement of the overall air conditioning system efficiency and greater comfort for the end user.



Finer speed control is possible thanks to the inverter control, by exploiting the fan feature with low external static pressure.

### SMALL SIZE AND EASY INSTALLATION

RPIM Mini ducted indoor units have been designed to adapt to small spaces, thanks to a special position of piping and wiring.

Access for easy maintenance is assured through the intake mouth.

Consequently, easy maintenance, very compact size and low noise level make mini ducted indoor units ideal for installation in hotel rooms.






# System Free Indoor Units



## CONDENSATE DRAIN

Condensate drain connection can be easily performed on the unit's intake side.

Indoor units are available in the version with built-in condensate drain pump (RPIM FSN4E-DU) or without (RPIM FSN4E).



MINI - RPIM DUCTED INDOOR UNIT									
CODE		NEW RPIM-0.6FSN4E (4)	RPIM-0.8FSN4E	RPIM-1.0FSN4E	RPIM-1.5FSN4E	RPIM-0.6FSN4E-DU (4)	RPIM-0.8FSN4E-DU	RPIM-1.0FSN4E-DU	RPIM-1.5FSN4E-DU
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	-	2.0	2.5	3.6	-	2.0	2.5	3.6
Nominal capacity in heating mode with UTOPIA systems (2)	kW	-	2.2	2.8	4	-	2.2	2.8	4
Nominal capacity in cooling mode with SETFREE systems (1)	kW	1.7	2.2	2.8	4	1.7	2.2	2.8	4
Nominal capacity in heating mode with SETFREE systems (2)	kW	1.9	2.5	3.2	4.8	1.9	2.5	3.2	4.8
Power Supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Input power	W	20	20	20	30	20	20	20	30
Dimensions (H×L×D)	mm	275x702x600	275x702x600	275x702x600	275x702x600	275x702x600	275x702x600	275x702x600	275x702x600
Weight	kg	26	26	26	26	26	26	26	26
Sound Pressure (L/M/H) (3)	dB(A)	25/28/28	27/29/29	27/29/29	28/30/33	25/28/28	27/29/29	27/29/29	28/30/33
Sound Power level at nominal output	dB(A)	49	50	50	51	49	50	50	51
Air flow (L/M/H)	m³/h	330/372/420	330/408/480	330/408/480	480/540/600	330/372/420	330/408/480	330/408/480	480/540/600
Nominal external static pressure (5) (min-max)	Pa	20 (0-35)	32 (0-50)	32 (0-50)	27 (0-58)	20 (0-35)	32 (0-50)	32 (0-50)	27 (0-58)
Condensate drain pump lift	mm	no pump				850mm from the lower edge of the unit			
Piping section	mm	6.35/12.7	6.35/12.7	6.35/12.7	6.35/12.7	6.35/12.7	6.35/12.7	6.35/12.7	6.35/12.7
	inch.	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level measured at 1.5 metres below the unit (measured in anechoic room)

(4) 0.6HP indoor units are only compatible with FSXNH and FSXN1E systems

(5) Measured at nominal air flow rate

Connectible with:



PC LH3A

PC ALHZ

PC ARH

PC ART

PC ARF




## System Free Indoor Units

# Ductable Low Static Pressure



RPI 0.6-1.5FSN4E



DC INVERTER MOTOR

CONDENSATE DRAIN PUMP

VARIABLE STATIC PRESSURE

OPTIONAL INPUTS/OUTPUTS

### EFFICIENT AND QUIET

The low pressure head ducted unit, available in 3 different power levels, 0.8, 1.0, 1.5 HP, is today completely renewed and, thanks to the new DC Inverter control fan motor, it is even more efficient.

This new technology affords electrical consumption reduction up to 40% compared to the previous model and always assures the correct air output to the premises with extremely low sound level. This translates into an improvement of the overall air conditioning

system efficiency and greater comfort for the end user.

Finer speed control is possible thanks to adopting the inverter, by exploiting the fan feature with low external static pressure.

### COMPACT SIZE

With height less than 200 mm, this unit may be inserted into any existing false ceiling without the need for complicated and costly modifications.


Furthermore, by modifying the position of the

rear cover, the air intake direction can be modified very easily.


The RPI low pressure head ducted units are equipped with a standard air filter on the intake side.

### CONDENSATE DRAIN PUMP


All power levels are fitted with automatic drain pump to eliminate the accumulated condensate in the pan.



Rear cover



Changing sides of the rear cover



# System Free Indoor Units



## DUCTABLE LOW STATIC PRESSURE INDOOR UNITS - RPI

CODE		<b>NEW</b> RPI-0.6FSN4E (4)	RPI-0.8FSN4E	RPI-1.0FSN4E	RPI-1.5FSN4E
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	-	2.0	2.5	3.6
Nominal capacity in heating mode with UTOPIA systems (2)	kW	-	2.2	2.8	4
Nominal capacity in cooling mode with SETFREE systems (1)	kW	1.7	2.2	2.8	4
Nominal capacity in heating mode with SETFREE systems (2)	kW	1.9	2.5	3.2	4.8
Power Supply	V	220V-50Hz	220V-50Hz	220V-50Hz	220V-50Hz
Input power	W	30	30	30	40
Dimensions (H×L×D)	mm	197x1084x600	197x1084x600	197x1084x600	197x1084x600
Weight	kg	29	29	29	30
Sound Pressure (L/M/H) (3) (SP-00) (6)	dB(A)	27/30/32	29/31/33	29/31/33	29/31/34
Sound Power at nominal output (SP-00) (6)	dB(A)	50	52	52	53
Air flow (L/M/H) (SP-00) (6)	m³/h	330/372/420	378/432/480	378/432/480	480/540/600
Nominal external static pressure (5) (min-max)	Pa	20 (0-30)	32 (0-50)	32 (0-50)	27 (0-50)
Condensate drain pump lift	mm	850mm from the lower edge of the unit			
Piping section	mm	6.35/12.7	6.35/12.7	6.35/12.7	6.35/12.7
	inch.	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2	1/4 - 1/2

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level measured at 1.5 metres below the unit (measured in anechoic room)

(4) 0.6HP indoor units are only compatible with FSXNH and FSXN1E systems

(5) Measured at nominal air flow rate

(6) SP: Static pressure (Setting by means of optional features "C5" of the remote controller: 01=High external static pressure, 00=Standard and 02=Low external static pressure)

Connectible with:



PC LH3A



PC ALHZ



PC ARH



PC ART



PC ARF





## System Free Indoor Units

# Ductable Medium Static Pressure



RESTAURANT PIZZERIA "IL CROCCIO" MILAN - APPLICATION OF HITACHI VRF SET FREE

RPI 2.0~6.0FSN4E



DC INVERTER MOTOR

CONDENSATE DRAIN PUMP

VARIABLE STATIC PRESSURE

OPTIONAL INPUTS/OUTPUTS

### EFFICIENT AND QUIET

The medium head pressure ducted unit is today completely renewed and, thanks to the new DC Inverter control fan motor, it is even more efficient.

This new technology affords electrical consumption reduction up to 40% compared to the previous model and always assures the correct air output to the premises with extremely low sound level. This translates into an improvement of the overall air conditioning system efficiency and greater comfort for the

end user.

Finer speed control is possible thanks to use of the inverter, by exploiting the fan feature with low external static pressure.

### COMPACT SIZE

With height less than 200 mm for all power levels, this unit may be inserted into any existing false ceiling without the need for complicated and costly modifications.


Furthermore, by modifying the position of the rear cover, the air intake direction can be

modified very easily.


The RPI medium pressure head ducted units are equipped with a standard air filter on the intake side.

### CONDENSATE DRAIN PUMP


All power levels are fitted with automatic drain pump to eliminate the accumulated condensate in the pan.



Rear cover



Changing sides of the rear cover



(Drain line slope)

# System Free Indoor Units



## DUCTABLE MEDIUM STATIC PRESSURE INDOOR UNITS - RPI

CODE		RPI-2.0FSN4E	RPI-2.5FSN4E	RPI-3.0FSN4E	RPI-4.0FSN4E	RPI-5.0FSN4E	RPI-6.0FSN4E
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	5.0	5.6	7.1	10.0	12.5	14.0
Nominal capacity in heating mode with UTOPIA systems (2)	kW	5.6	6.3	8.0	11.2	14.0	16.0
Nominal capacity in cooling mode with SETFREE systems (1)	kW	5.6	7.1	8.0	11.2	14.0	16.0
Nominal capacity in heating mode with SETFREE systems (2)	kW	6.3	8.5	9.0	12.5	16.0	18.0
Power Supply	V	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz
Input power	W	40	80	110	160	200	220
Dimensions (HxLxD)	mm	275x1084x600	275x1084x600	275x1084x600	275x1474x600	275x1474x600	275x1474x600
Weight	kg	35	36	36	48	48	48
Sound Pressure (L/M/H) (3) (SP-02) (5)	dB(A)	27/29/29	28/30/30	29/31/31	32/35/37 (SP-00) (5)	33/35/38 (SP-01) (5)	33/36/39 (SP-01) (5)
Sound Power at nominal output (SP-02) (5)	dB(A)	55	56	57	62 (SP-00) (5)	65 (SP-01) (5)	66 (SP-01) (5)
Air flow (L/M/H) (SP-02) (5)	m³/h	600/750/960	1140/960/780	960/1140/1320	1500/1680/1800	1680/1920/2100	1740/1980/2160
Nominal external static pressure (4) (min-max)	Pa	30 (0-120)	30 (0-125)	30 (0-125)	45 (0-120)	50 (0-140)	50 (0-140)
Condensate drain pump lift	mm	850mm from the lower edge of the unit					
Piping section	mm	6.35/15.88	9.53/15.88	9.53/15.88	9.53/15.88	9.53/15.88	9.53/15.88
	inch.	1/4 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8	3/8 - 5/8

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level measured at 1.5 metres below the unit (measured in anechoic room)

(4) Measured at nominal air flow rate

(5) SP: Static pressure (Setting by means of optional features "C5" of the remote controller: 01=High external static pressure, 00=Standard and 02=Low external static pressure)

Connectible with:



PC LH3A

PC ALHZ

PC ARH

PC ART


PC ARF

## ECONOFRESH KIT

The ECONOFRESH Kit is an accessory to be matched to RPI 4 to 6HP ducted indoor units to provide free-cooling and considerable energy savings.

It is especially suited to applications where a fixed fresh air percentage must be assured (adaptable to the specific case) such as Data Centres, Shops, Gyms, Meeting rooms.

The ECONOFRESH Kit can also be interfaced with optional enthalpic and CO2 sensors.



Code	Compatibility	Dimensions HxLxD	Weight
		mm	Kg
EF-456NE	RPI-4.0FSN4E RPI-5.0FSN4E RPI-6.0FSN4E	254x1350x310	12.5




# System Free Indoor Units

## Ductable High Static Pressure



IMG CINEMAS MESTRE - APPLICATION HITACHI UTOPIA AND VRF SET FREE

RPI 8.0~10.0FSN3E




OPTIONAL INPUTS/OUTPUTS

### HIGH USEFUL PRESSURE HEAD

The RPI units are fitted with a static pressure adjustment system on two levels, depending on installation requirements: Low Static Pressure and High Static Pressure (factory setting), they can be selected directly and easily from the electrical panel on the unit.

### CONDENSATE DRAINAGE

Drainage takes place by gravity only and therefore the drainage line must have continuous slope from the low plane of the unit in the direction of the flow between 1 and 4%.





# System Free Indoor Units



## HIGH HEAD DUCTABLE INDOOR UNIT - RPI

CODE			RPI-8.0FSN3E	RPI-10.0FSN3E
Nominal capacity in cooling mode with UTOPIA systems (1)		kW	20.0	25.0
Nominal capacity in heating mode with UTOPIA systems (2)		kW	22.4	28.0
Nominal capacity in cooling mode with SETFREE systems (1)		kW	22.4	28.0
Nominal capacity in heating mode with SETFREE systems (2)		kW	25.0	31.0
Power Supply		V	220V 50Hz	220V 50Hz
Input power		W	970	1060
Dimensions (H×L×D)		mm	423x1592x600	423x1592x600
Weight		kg	85	87
Sound Pressure (L/M/H) (3)		dB(A)	51/54/54	52/55/55
Sound Power level at nominal output		dB(A)	77	78
Air flow rate	HSP mode (4) (min-max)	m³/h	3600-3960	4110-4500
	LSP mode (5) (min-max)	m³/h	3570-3960	4050-4500
Static pressure	HSP mode (4) (min-max)	Pa	180-220	180-220
	LSP mode (5) (min-max)	Pa	180-140	180-140
Piping section		mm	9.53/19.05	9.53/22.2
		inch.	3/8 - 3/4	3/8 - 7/8

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level measured at 1.5 metres below the unit (measured in anechoic room)

(4) HSP: High static pressure

(5) LSP: Low static pressure; factory setting

Connectible with:



PC LH3A

PC ALHZ

PC ARH

PC ART

PC ARF



# System Free Indoor Units

## Floor



RPF 1.0~2.5FSN2E



### VISIBLE FLOOR

#### THIN AND COMPACT PROFILE

The thin and compact design of these units, featuring a depth of just 220 mm, means they can be installed without affecting the décor of the premises.

#### INTELLIGENT USE OF SPACE

Installation underneath windows is never inconvenient: height is just 630 mm.

#### OPTIONAL REMOTE CONTROLLER HOUSING

The PC-ART can be housed under the plastic cover, inside the unit.

RPFI 1.0~2.5FSN2E



### RECESSED FLOOR

#### COMPACT DESIGN

These units have been designed paying special attention to their compatibility with indoor architecture.


Featuring 620 mm height and 220 mm depth, these units can be perfectly installed in the area underneath windows.

#### AIRFLOW DIRECTION



The airflow direction can be easily adjusted by re-positioning the rear panel for a greater range of installation options.

### OPTIONAL INPUTS/OUTPUTS

CONTROLLER HOUSING



AIRFLOW DIRECTION



# System Free Indoor Units



## VISIBLE FLOOR INDOOR UNIT - RPF

CODE		RPF-1.0FSN2E	RPF-1.5FSN2E	RPF-2.0FSN2E	RPF-2.5FSN2E
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	2.5	3.6	5	5.6
Nominal capacity in heating mode with UTOPIA systems (2)	kW	2.8	4	5.6	6.3
Nominal capacity in cooling mode with SETFREE systems (1)	kW	2.8	4	5.6	7.1
Nominal capacity in heating mode with SETFREE systems (2)	kW	3.2	4.8	6.3	8.5
Power Supply	V	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz
Input power	W	40	50	90	90
Dimensions (H×L×D)	mm	630x1045x220	630x1170x220	630x1420x220	630x1420x220
Weight	kg	25	28	33	34
Sound Pressure (L/M/H) (3)	dB(A)	29/32/35	31/35/38	32/36/39	34/38/42
Sound Power level at nominal output	dB(A)	57	60	60	64
Air flow (L/M/H)	m³/h	360/420/510	540/600/720	660/840/960	660/840/960
Piping section	mm	6.35/12.7	6.35/12.7	6.35/15.88	9.53/15.88
	inch.	1/4 - 1/2	1/4 - 1/2	1/4 - 5/8	3/8 - 5/8

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level taken at a height of 1 metre from the floor and at a distance of 1 metre from the front of the unit (measured in an anechoic chamber)

## RECESSED FLOOR INDOOR UNIT - RPFI

CODE		RPFI-1.0FSN2E	RPFI-1.5FSN2E	RPFI-2.0FSN2E	RPFI-2.5FSN2E
Nominal capacity in cooling mode with UTOPIA systems (1)	kW	2.5	3.6	5	5.6
Nominal capacity in heating mode with UTOPIA systems (2)	kW	2.8	4	5.6	6.3
Nominal capacity in cooling mode with SETFREE systems (1)	kW	2.8	4	5.6	7.1
Nominal capacity in heating mode with SETFREE systems (2)	kW	3.2	4.8	6.3	8.5
Power Supply	V	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz
Input power	W	40	50	90	90
Dimensions (H×L×D)	mm	630x1045x220	630x1170x220	630x1420x220	630x1420x220
Weight	kg	19	23	27	28
Sound Pressure (L/M/H) (3)	dB(A)	29/32/35	31/35/38	32/36/39	34/38/42
Sound Power level at nominal output	dB(A)	57	60	60	64
Air flow (L/M/H)	m³/h	360/420/510	540/600/720	660/840/960	660/840/960
Piping section	mm	6.35/12.7	6.35/12.7	6.35/15.88	9.53/15.88
	inch.	1/4 - 1/2	1/4 - 1/2	1/4 - 5/8	3/8 - 5/8

(1) Cooling: indoor ambient temp. 27°C (19°C BU) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; lift 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C BU); refrigerant piping length 7.5m; lift 0m.

(3) Sound pressure level taken at a height of 1 metre from the floor and at a distance of 1 metre from the front of the unit (measured in an anechoic chamber)

Connectible with:



PC LH3A

PC ALHZ

PC ARH

PC ART

PC ARF





# System Free Indoor Units

## DX KIT



EXPANSION VALVE BOX



CONTROL BOX



PAM DC INVERTER CONTROL

AUTOMATIC RESTART

AC 220-230V 1PH 50 HZ

OUTDOOR UNIT POWER SUPPLY

R410A

AUTO FUNCTION

Air exchange in buildings is normally provided and recommended to improve working conditions and prevent important pathologies such as those arising from dry eyes and respiratory tract.

Presently, the fresh air is input through independent treatment units made to measure. These units, supplied by third parties, pre-treat the outside air to adapt it approximately to that of the air conditioned room.


The Direct Expansion Kit electronic interface (DX Kit) makes it possible to connect one third party air treatment unit with one HITACHI outdoor unit to input fresh air of the air conditioned rooms (see table on following page for

compatibility).

#### Features:

- DX-KIT assures protection degree IP 66
- Available operative modes are COOLING and HEATING
- The DX-KIT consists of two sections:
  - CONTROL BOX - EXPANSION VALVE BOX
- COOLING & HEATING performance is defined based on the temperature set on the control panel and the temperature measured by the ambient air intake probe
- The DX-KIT can be interfaced with Optional inputs/outputs (standard solution of HITACHI)

# System Free Indoor Units



REF.	DESCRIPTION
1	HITACHI Outdoor Unit
2	Interface kit DX EXV-(2.0-10.0)E1
3	CONTROL BOX
4	EXPANSION VALVE BOX
5	Remote Controller Accessory (PC ART)
6	Air Treatment unit with heat exchanger
7	RX- Heat exchanger with finned battery
8	Liquid Pipeline
9	Gas Pipeline
10	Bus Communication H-Link
11	Power supply
12	Expansion valve control cable
13	Remote control connection cable
14	Air flow direction
15	Input air Thermistor Probe
16	Output air Thermistor Probe
17	Liquid pipeline Thermistor Probe
18	Gas pipeline Thermistor Probe



\* PC - ART controller is compulsory

## DX KIT TECHNICAL SPECIFICATIONS

DX KIT			EXV-2.0E1	EXV-2.5E1	EXV-3.0E1	EXV-4.0E1	EXV-5.0E1	EXV-6.0E1	EXV-8.0E1	EXV-10.0E1
Control electronics	Power Supply	V/Ph/Hz	220V/50Hz	220V/50Hz	220V/50Hz	220V/50Hz	220V/50Hz	220V/50Hz	220V/50Hz	220V/50Hz
	Cooling capacity	kW	5.0	6.0	7.1	10.0	12.5	14.0	20.0	25.0
	heating capacity	kW	5.6	7.0	8.0	11.2	14.0	16.0	22.4	28.0
	Allowed Fan Current (A)	A	2.5	2.5	2.5	2.5	2.5	2.5	15	15
	Dimensions (HxLxD)	mm	291/241/87	291/241/87	291/241/87	291/241/87	291/241/87	291/241/87	291/241/87	291/241/87
	Weight	kg	3.2	3.2	3.2	3.2	3.2	3.2	3.5	3.5
Expansion valve	IN Liquid Line	mm/inch	6.35 - 1/4	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8
	OUT Liquid Line	mm/inch	6.35 - 1/4	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8
	HP Gas line	mm/inch	12.7 - 1/2	12.7 - 1/2	15.88 - 5/8	15.88 - 5/8	15.88 - 5/8	15.88 - 5/8	25.4 - 1	25.4 - 1
	Dimensions (HxLxD)	mm	431x199 x103	431x199 x103	431x199 x103	431x199 x103	431x199 x103	431x199 x103	431x199 x103	431x199 x103
	Weight	kg	2.7	2.7	2.7	2.7	2.7	2.7	4.5	4.5

## COMBINATION OPTIONS

Outdoor unit	Control mode		
	Air input (1*)	Air output	Reference
UTOPIA	■	■ (2*)	■ (2*)
VRF SET FREE	■	■ (3*)	■ (3*)

### NOTE

(1\*) In case of installations with air treatment units, the point just before the DX exchanger is considered as input air.

(2\*) only the MONO combination is allowed.

(3\*) Limited control based on overall operative conditions of the system.

(4\*) Should any Hitachi indoor units be installed in a common outdoor unit, total DX Kit capacity cannot exceed 30% of the overall condensing unit capacity.

(5\*) Should only DX Kits be connected to the outdoor unit, total DX Kit capacity cannot exceed 100% of the overall outdoor unit capacity.

DX EXV (2.0-10.0)E1 Interface models can only be combined with air - air systems.





## KPI Series E and H

Indoor unit - enthalpy recovery system



### HEAT RECOVERY

ADJUSTMENT CAN BE COMBINED WITH STANDARD CONTROLS

With the KPI cross flow heat recovery units it is possible - depending on the type of exchange pack - to perform enthalpic heat recovery (Series E) or of sensible heat recovery only (series H).


This lets you reduce the power requirements of air conditioning systems where continuous ambient air renewal is required.

Moreover, thanks to the new internal geometrical layout, which supports linear flow between ambient air intake and extraction ducts, installation in the field is easier and above all does not feature the typical duct crossing issues of standard models.

KPI heat recovery units assure the environment has fresh, clean and pleasant air

using the combined control with the SYSTEM FREE conditioning system.

- Celluloid exchange pack for series E
- Aluminium exchange pack for series H
- Horizontal or vertical installation for series E
- Horizontal installation H
- Nominal airflow from 250 to 3000m<sup>3</sup>/h
- Direct flow exchanger
- Power input harmonised with EuP Standards
- Lot 11 in force from 2013
- Class M1 fire resistance
- Standard supplied G3 filters, F7 accessories
- Control by CO<sub>2</sub> sensor (not supplied by HITACHI)
- Maintaining the rooms in over-pressure



- External heater control (not supplied by HITACHI)
- Switch-on delay
- Total compatibility with COMMERCIAL and VRF SET FREE systems
- Control by means of PC-ART, PC-ARF, PC-ARH controllers (accessories)



# System Free Ventilation



## KPI SERIES E TECHNICAL DATA

CODE		KPI-252E3E	KPI-502E3E	KPI-802E3E	KPI-1002E3E	KPI-1502E3E	KPI-2002E3E
Power Supply	V-Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz
Nominal input power	W	50	80	210	260	470	580
Air flow (L/M/H)	m³/h	180/208/250	360/420/500	597/700/800	620/800/1000	970/1250/1500	1240/1560/2000
Static pressure (L/M/H) (1)	Pa	30/40/60	47/50/77	55/75/100	50/80/120	60/90/132	60/84/135
Sound pressure (L/M/H) (2)	dB(A)	24/26/27	27/28/30	30/31/32	30/32/35	33/35/37	35/38/39
Efficiency	thermal exchange	%	75	75	75	78	78
		%	60	61	62	62	61.5
	enthalpy exchange	cooling	%	66	65	65	68
		heating	%	66	65	65	68
Type of exchanger		celluloid					
Dimensions HxLxD	mm	270/900/750	330/1130/920	385/1210/1015	385/1600/1295	525/1800/1130	525/1800/1430
Duct diameter	mm	150	200	250	300	355	355
Weight	kg	34	46	51	79	97	106

(1) Static pressure with standard ventilation setting

(2) Sound pressure level measured at 1.5 metres below the unit with acoustically insulated duct (measured in anechoic room)

In the event of fresh outside air lower than -5°C (DB) an electrical heater must be installed (not supplied)

## KPI SERIES H TECHNICAL DATA

CODE		KPI-502H3E	KPI-802H3E	KPI-1002H3E	KPI-1502H3E	KPI-2002H3E
Power Supply	V-Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz	220V - 50Hz
Nominal input power	W	80	210	260	470	580
Air flow (L/M/H)	m³/h	360/420/500	597/700/800	620/800/1000	970/1250/1500	1240/1560/2000
Static pressure (L/M/H) (1)	Pa	47/50/77	55/75/100	50/80/120	60/90/132	60/84/135
Sound pressure (L/M/H) (2)	dB(A)	30/31/33	33/34/35	33/35/38	35/36/40	38/41/42
Efficiency	thermal exchange	%	53	50	50	49
		%	30	28	28	27
	enthalpy exchange	cooling	%	35	34	33
		heating	%	35	34	33
Type of exchanger		aluminium				
Dimensions HxLxD	mm	330/1130/920	385/1210/1015	385/1600/1295	525/1800/1130	525/1800/1430
Duct diameter	mm	200	250	300	355	355
Weight	kg	50	55	85	101	110

(1) Static pressure with standard ventilation setting

(2) Sound pressure level measured at 1.5 metres below the unit with acoustically insulated duct (measured in anechoic room)

In the event of fresh outside air lower than -5°C (DB) an electrical heater must be installed (not supplied)

Connectible with:



PC ARH

PC ART

PC ARF



## KPI Series X

Indoor unit - with DX active exchanger




TEMPERATURE CONTROL  
ON AIRFLOW

HEAT RECOVERY

ADJUSTMENT CAN BE COMBINED  
WITH STANDARD CONTROLS

Heat recovery units series X, thanks to the R410A gas heat exchanger they are fitted with, as well as recovering heat also integrate any thermal requirement after recovery with post heating/post cooling. This makes it possible to renew the ambient air without affecting the conditions and to reduce the power requirement of conditioning systems which require continuous room air exchange. Moreover, thanks to the new internal geometrical layout, which supports linear flow between ambient air intake and extraction ducts, installation in the field is easier and above all does not feature the typical duct crossing issues of standard models.

KPI heat recovery units guarantee an environment with fresh, clean and pleasant air using the combined control with the SYSTEM FREE conditioning system.



- Celluloid exchange pack
- Horizontal installation
- Nominal airflow from 500 to 1000m<sup>3</sup>/h
- Direct flow exchanger
- Power input harmonised with EuP Standards
- Lot 11 in force from 2013
- Class M1 fire resistance
- Standard supplied G3 filters, F7 accessories
- Control by CO<sub>2</sub> sensor (not supplied by HITACHI)
- Maintaining the rooms in over-pressure
- External heater control (not supplied by HITACHI)
- Switch-on delay
- Total compatibility with COMMERCIAL and VRF SET FREE systems
- Control by means of PC-ART, PC-ARF, PC-ARH controllers (accessories)

# System Free Ventilation



## KPI SERIES X TECHNICAL DATA

CODE				KPI-502X3E	KPI-802X3E	KPI-1002X3E
Nominal capacity in cooling mode with UTOPIA systems (1)			kW	-	7.4	9.7
Nominal capacity in heating mode with UTOPIA systems (2)			kW	-	9.1	11.4
Nominal capacity in cooling mode with SETFREE systems (1)			kW	5.3 (1.8)	8 (3)	10.8 (3.7)
Nominal capacity in heating mode with SETFREE systems (2)			kW	6.9 (2.1)	9.8 (3.5)	12.9 (4.4)
Coil cooling power			HP	1.5	2.0	2.5
Power Supply			V	220V - 50Hz	220V - 50Hz	220V - 50Hz
Nominal input power			W	130	240	310
Air flow (L/M/H)			m³/h	380/430/500	590/700/800	740/820/1000
Static Pressure (L/M/H) (3)			Pa	100/120/150	70/95/125	70/85/120
Sound pressure (L/M/H) (4)			dbA	26/27/29	29/30/31	31/33/34
Efficiency	thermal exchange		%	75	75	78
	enthalpy exchange	cooling	%	61	62	62
		heating	%	65	65	65
Type of exchanger				celluloid		
Dimensions HxLxD			mm	330x1630x920	385x1710x1015	385x2100x1295
Duct diameter			mm	200	250	300
Weight			kg	62	69	100
Piping section			mm	6.35/12.7	6.35/15.88	9.53/15.88
			inch	1/4 - 1/2	1/4 - 5/8	3/8 - 5/8

(1) Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

(3) Static pressure with standard ventilation setting

(2) Sound pressure level measured at 1.5 metres below the unit with acoustically insulated duct (measured in anechoic room)

In the event of fresh outside air lower than -5°C (DB) an electrical heater must be installed (not supplied)

## COMBINATION OPTIONS

Model	Mono Utopia Combination			VRF Setfree Combination			Cooling connections	
	Output Power		Outdoor Unit	Output Power		Power Equivalent		
	Cooling	Heating		Cooling	Heating		Liquid	Gas
	kW	kW		kW	kW	HP	mm (")	mm (")
KPI 502X3E	--	--	--	5.3	6.9	1.5	6.35 (1/4)	12.70 (1/2)
KPI 802X3E	7.4	9.1	RAS 2HVNP	8.0	9.8	2.0	6.35 (1/4)	15.88 (5/8)
KPI 1002X3E	9.7	11.4	RAS 2.5HVNP	10.8	12.9	2.5	9.53 (3/8)	15.88 (5/8)

### NOTE

In the event of installation inside VRF SET FREE systems, the total cooling capacity of KPI X series heat recovery units must not exceed 30% of the total condensing unit power.

Connectible with:



PC ARH

PC ART

PC ARF





# Commercial Outdoor Units

The Utopia range offers systems with high performance at interesting prices for use in small buildings and retail which require intelligent management

of ambient comfort. The series consists in 4 different models - Utopia ES Inverter, Utopia RASC IVX and Utopia IVX Standard and IVX Premium.

This means a wide variety of design options for applications that exactly address your needs.

**Utopia ES** Inverter compact design is striking.

The reduced height supports design solutions in small spaces, with an excellent quality-price ratio.

**Utopia RASC IVX** uses the IVX Series technology but for applications which call for the condensing unit to be installed inside the building with ducted connection to the outside and centrifugal fan.

the whole range of commercial outdoor units uses the SYSTEM FREE indoor units; it is highly efficient, reliable and complemented by a wide range of accessories for

utmost design flexibility and greater benefits both for installers and end users.

**Utopia IVX Standard** and **IVX Premium:** variable refrigerant flow and independent control of indoor units in the Commercial range at an even more competitive price compared to traditional VRF systems. Two - twelve HP models are available.

## Outdoor units

### Utopia Range

**Utopia ES** ( Simultaneous Indoor Unit Operation)

**Utopia IVX Standard** ( Independent Indoor Unit Operation)

**Utopia IVX Premium** ( Independent Indoor Unit Operation)

**Utopia IVX RASC** ( Independent Indoor Unit Operation)

Compatible with the same remote controllers

### Set Free Range

**FSVN2E & FSNY2E**

**FSNM VRF Side Flow**

**FSXN VRF 2 or 3 Pipes**





**FSXN1E VRF 2 or 3 Pipes**

**FSXNH VRF 2 or 3 Pipes** high efficiency

Compatible with the same remote controllers






OUTDOOR UNIT RANGE											
type	Capacity (HP)		2	2.5	3	4	5	6	8	10	12
Utopia ES	H(V)RN				■	■	■	■	■	■	
	No. of Indoor Units				2	2	2	3	4	4	
Utopia RASC IVX	H(V)RNM1E						■			■	
	No. of Indoor Units						3			4	
Utopia IVX Standard	H(V)NC(1)E				■	■	■	■	■	■	■
	No. of Indoor Units				2	4	4	4	4	4	4
Utopia IVX Premium	H(V)NP1E		■	■	■	■	■	■	■	■	■
	No. of Indoor Units		2	2	3	5	6	6	8	8	8



# Retail Solutions

## UTOPIA ES

- Available power from 3 to 10HP




### REQUIREMENT

- Very compact dimensions
- Open space
- Contained cost
- Connections from 1 to 4 indoor units in the same volume

## UTOPIA RASC IVX

- Available power: 5 and 10HP



### REQUIREMENT

- Invisible outside unit
- Treatment of separate multiple areas






## UTOPIA IVX STANDARD

■ Available power: from 3 to 12 HP

### REQUIREMENT

- Independent adjustment
- Elevated comfort
- from 1 to 4 different zones
- from 1 to 4 different temperatures
- High Performance




## UTOPIA IVX PREMIUM

■ Available power: from 3 to 12 HP

### REQUIREMENT

- Independent adjustment
- Elevated comfort
- from 1 to 8 different zones
- from 1 to 8 different temperatures
- High Performance





## UTOPIA ES

DC inverter Heat pump



UTOPIA ES TECHNICAL SPECIFICATIONS

CODE		RAS 3HVRNS3	RAS 4HVRNS3E	RAS 4HRNS3E	RAS 5HVRNS2E
Power Supply	V/Ph/Hz	1 - 220V 50Hz	1 - 220V 50Hz	3N - 400V 50Hz	1 - 220V 50Hz
Nominal cooling capacity (1)	kW	7.1 (3.2 - 8.0)	10.0 (4.5-11.2)	10.0 (4.5-11.2)	12.5 (5.7-14.0)
Nominal heating capacity (2)	kW	8.0 (3.5-10.60)	11.2 (5.0-14.0)	11.2 (5.0-14.0)	14.0 (6.0-16.0)
Nominal Power Input (Cool. / Heat.)	A	10.0/8.8	11.3/11.3	4.1/4.1	18.4/18.5
Input power at nominal Cap. (Cool. / Heat.)	kW	2.27/2.0	2.58/2.56	2.58/2.56	4.16/4.18
Max. input current	A	16	28	15	26
EER/COP (4)		3.05/3.88	3.69/4.16	3.69/4.16	2.91/3.24
SEER	W/W	5.14	4.95	4.85	*
Cooling energy efficiency class		A	B	B	*
P Design (35°C)	kW	7.1	10.0	10.0	*
AVERAGE Climate	SCOP	W/W	3.88	3.85	*
	Heating energy efficiency class		A	A	*
	P Design (-10°C)	kW	5.6	8.0	*
Min-max indoor units connected	No.	1-2	1-2	1-2	1-2
Sound Pressure Cooling/Heating (Night Mode) (3)	dB(A)	48-50 (46)	50-52 (48)	50-52 (48)	52-54 (50)
Sound Power level at nominal output	dB(A)	66	70	70	71
No. of fans	No.	1	1	1	1
Air flow rate (max.)	m³/h	2682	3720	3720	4080
Dimensions (HxLxD)	mm	600x792x300	800x950x370	800x950x370	800x950x370
Weight	kg	44	67	67	83
Cooling mode working range	°C	-5 / +43 (BS)	-5 / +43 (BS)	-5 / +43 (BS)	-5 / +43 (BS)
Heating mode working range	°C	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-10 / +15 (BU)
R-410A Refrigerant charge	kg	1.9	2.9	2.9	2.9
Minimum piping length	m	5	5	5	5
Maximum piping length without additional charge	m	30	30	30	30
Maximum piping length (required additional charge)	m (g/m)	50 (30)	50 (40)	50 (40)	50 (60)
Maximum lift (OU up - OU down)	g/m	30/20	30/20	30/20	30/20
Liquid line piping diameter	mm (inch)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)
Gas line piping diameter	mm (inch)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)


# Commercial Outdoor Units



RAS 3HVRNS3



RAS 4HVRNS3E  
RAS 5HVRNS2E  
RAS 6HVRNS2E  
RAS 4HRNS3E  
RAS 5HRNS2E  
RAS 6HRNS2E



RAS 8HRNSE  
RAS 10HRNSE

Thanks to its continuous and advanced renewal process, the Utopia ES range features very small and compact sizes.

The units are equipped with one fan only up to 6HP. With maximum width 950 mm and maximum height 800mm, (up to 6Hp) Utopia ES is ideal for installation in small spaces.

both Single Phase 230-volt and Three Phase 380-volt power supply is available starting from 4 HP.

connection to all indoor System Free units is possible with multiple combinations in accordance with the specific table, up to 4 indoor units for larger 8 and 10 HP models.

COMPACT DESIGN

MINIMUM HEIGHT

ECO-FRIENDLY

GAS R410A

DC INVERTER COMPRESSORS

The specified cooling and heating capacities refer to the outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

<sup>1</sup> Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

<sup>2</sup> Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

<sup>3</sup> Sound pressure level measured at 1.5 metres below the unit in anechoic room with no reflection

<sup>4</sup> The performance is calculated based on combination with model RCI indoor units

5 ÷ 10HP



3 ÷ 4HP



3 : 4HP

## UTOPIA ES TECHNICAL SPECIFICATIONS

CODE		RAS 5HRNS2E	RAS 6HVRNS2E	RAS 6HRNS2E	RAS 8HRNSE	RAS 10HRNSE
Power Supply	V/Ph/Hz	3N - 400V 50Hz	1 - 220V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz
Nominal cooling capacity (1)	kW	12.5 (5.7-14.0)	14.0 (6.0-16.0)	14.0 (6.0-16.0)	20.0 (9.0-22.4)	25.0 (11.2-28.0)
Nominal heating capacity (2)	kW	14.0 (6.0-16.0)	16.0 (6.0-18.0)	16.0 (6.0-18.0)	22.4 (8.3-25.0)	28.0 (9.0-31.5)
Nominal Power Input (Cool. / Heat.)	A	6.5/6.6	24.6/23.8	8.7/8.4	10.1/9.9	13.5/13.2
Input power at nominal cap. (Cool. / Heat.)	kW	4.16/4.18	5.53/5.38	5.53/5.38	6.42/6.33	8.62/8.44
Max. input current	A	13	26	13	20	23
EER/COP (4)		2.91/3.24	2.45/2.88	2.45/2.88	3.01/3.42	2.81/3.21
SEER	W/W	*	*	*	*	*
Cooling energy efficiency class		*	*	*	*	*
P Design (35°C)	kW	*	*	*	*	*
AVERAGE Climate	SCOP	W/W	*	*	*	*
	Heating energy efficiency class		*	*	*	*
	P Design (-10°C)	kW	*	*	*	*
Min-max indoor units connected	No.	1-2	1-3	1-3	1-4	1-4
Sound Pressure Cooling/Heating (Night Mode) (3)	dB(A)	52-54 (50)	55-57 (53)	55-57 (53)	53-55 (51)	60-62 (56)
Sound Power level at nominal output	dB(A)	71	72	72	71	78
No. of fans	No.	1	1	1	2	2
Air flow rate (max.)	m³/h	4080	4800	4800	7620	8760
Dimensions (HxLxD)	mm	800x950x370	800x950x370	800x950x370	1380x950x370	1380x950x370
Weight	kg	83	83	83	135	141
Cooling mode working range	°C	-5 / +43 (BS)	-5 / +43 (BS)	-5 / +43 (BS)	-5 / +43 (BS)	-5 / +43 (BS)
Heating mode working range	°C	-10 / +15 (BU)	-10 / +15 (BU)	-10 / +15 (BU)	-10 / +15 (BU)	-10 / +15 (BU)
R-410A Refrigerant charge	kg	2.9	2.9	2.9	6.0	6.2
Minimum piping length	m	5	5	5	5	5
Maximum piping length without additional charge	m	30	30	30	30	30
Maximum piping length (required additional charge)	m (g/m)	50 (60)	50 (60)	50 (60)	50 (65)	50 (120)
Maximum lift (OU up - OU down)	g/m	30/20	30/20	30/20	30/20	30/20
Liquid line piping diameter	mm (inch)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)
Gas line piping diameter	mm (inch)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	25.4 (1)	25.4 (1)

\* Data not supplied as the power levels are not covered by Lot 10 of the ErP Regulations





## UTOPIA ES

### Prices of Mono Combinations

#### RCI - 4-WAY CASSETTE SERIES i (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-3.0FSN3Ei	P-N23NA	RAS-3HVRNS3	220V-50Hz	4.70	B	3.81	A	3.0	3.7
RCI-4.0FSN3Ei	P-N23NA	RAS-4HVRNS3E	220V-50Hz	4.70	B	3.81	A	3.3	3.7
RCI-4.0FSN3Ei	P-N23NA	RAS-4HRNS3E	380V-50Hz	4.70	B	3.81	A	3.3	3.7
RCI-5.0FSN3Ei	P-N23NA	RAS-5HVRNS2E	220V-50Hz	*	*	*	*	2.9	3.2
RCI-5.0FSN3Ei	P-N23NA	RAS-5HRNS2E	380V-50Hz	*	*	*	*	2.9	3.2
RCI-6.0FSN3Ei	P-N23NA	RAS-6HVRNS2E	220V-50Hz	*	*	*	*	2.5	2.9
RCI-6.0FSN3Ei	P-N23NA	RAS-6HRNS2E	380V-50Hz	*	*	*	*	2.5	2.9

#### RCI - 4-WAY CASSETTE SERIES k (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-3.0FSN3Ek	P-AP160NA1	RAS-3HVRNS3	220V-50Hz	4.70	B	3.81	A	3.0	3.7
RCI-4.0FSN3Ek	P-AP160NA1	RAS-4HVRNS3E	220V-50Hz	4.70	B	3.81	A	3.3	3.7
RCI-4.0FSN3Ek	P-AP160NA1	RAS-4HRNS3E	380V-50Hz	4.70	B	3.81	A	3.3	3.7
RCI-5.0FSN3Ek	P-AP160NA1	RAS-5HVRNS2E	220V-50Hz	*	*	*	*	2.9	3.2
RCI-5.0FSN3Ek	P-AP160NA1	RAS-5HRNS2E	380V-50Hz	*	*	*	*	2.9	3.2
RCI-6.0FSN3Ek	P-AP160NA1	RAS-6HVRNS2E	220V-50Hz	*	*	*	*	2.5	2.9
RCI-6.0FSN3Ek	P-AP160NA1	RAS-6HRNS2E	380V-50Hz	*	*	*	*	2.5	2.9

NOTE: the unit is compatible also with cover panel fitted with motion sensor - cod. P-AP160NAE

#### RPI - DUCTED

Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPI-3.0 FSN4E		RAS-3HVRNS3	220V-50Hz	4.70	B	3.81	A	2.8	3.6
RPI-4.0 FSN4E		RAS-4HVRNS3E	220V-50Hz	4.70	B	3.83	A	3.4	3.7
RPI-4.0 FSN4E		RAS-4HRNS3E	380V-50Hz	4.70	B	3.83	A	3.4	3.7
RPI-5.0 FSN4E		RAS-5HVRNS2E	220V-50Hz	*	*	*	*	2.9	3.3
RPI-5.0 FSN4E		RAS-5HRNS2E	380V-50Hz	*	*	*	*	2.9	3.3
RPI-6.0 FSN4E		RAS-6HVRNS2E	220V-50Hz	*	*	*	*	2.8	3.2
RPI-6.0 FSN4E		RAS-6HRNS2E	380V-50Hz	*	*	*	*	2.8	3.2
RPI-8.0 FSN3E		RAS-8HRNSE	380V-50Hz	*	*	*	*	2.6	3.1
RPI-10.0 FSN3E		RAS-10HRNSE	380V-50Hz	*	*	*	*	2.4	3.0

#### RPC - CEILING

Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPC-3.0FSN3E		RAS-3HVRNS3	220V-50Hz	4.31	C	3.80	A	2.7	ND
RPC-5.0FSN3E		RAS-5HVRNS2E	220V-50Hz	*	*	*	*	2.8	3.1
RPC-5.0FSN3E		RAS-5HRNS2E	380V-50Hz	*	*	*	*	2.8	3.1
RPC-6.0FSN3E		RAS-6HVRNS2E	220V-50Hz	*	*	*	*	2.4	2.8
RPC-6.0FSN3E		RAS-6HRNS2E	380V-50Hz	*	*	*	*	2.4	2.8

#### RPC - CEILING

Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPK-3.0FSN3M		RAS-3HVRNS3	220V-50Hz	4.66	B	3.59	A	2.6	2.9
RPK-4.0FSN3M		RAS-4HVRNS3E	220V-50Hz	4.75	B	3.40	A	2.4	3.0

\* DATA NOT SUPPLIED AS THE POWER LEVELS ARE NOT COVERED BY LOT 10 OF THE ERP DIRECTIVE



## Multi Combinations

Model	Single	Twin		Triple		Quad	
CODE		Combination	Joints	Combination	Joints	Combination	Joints
RAS 3HVRNS3	3.0	1.5/1.5	TE-03N1	-	-	-	-
RAS 4H(V)RNS3E	4.0	2.0/2.5 - 1.8/2.3 - 2.0/2.3 1.8/2.5 - 2.0/2.5	TE-04N1				
RAS 5H(V)RNS2E	5.0	2.5/2.5 - 3.0/2.3 3.0/1.8 - 3.0/2.0	TE-56N1	-	-	-	-
RAS 6H(V)RNS2E	6.0	3.0/3.0 - 3.0/2.5	TE-56N1	1.8/1.8/1.8 - 2.0/2.0/2.0 - 2.0/2.0/1.8 - 1.8/1.8/2.0 - 1.5/1.5/2.5	TRE-46N1	-	-
RAS 8HRNSE	8.0	4.0/4.0	TE-08N	3.0/3.0/3.0	TRE-810N	2.0/2.0/2.0/2.0	1 x TE-08N+ 2 x TE-04N1
RAS 10HRNSE	10.0	5.0/5.0	TE-08N	-	-	2.5/2.5/2.5/2.5	1 x TE-08N+ 2 x TE-56N1

### Note

Non standard power levels can be obtained from fixed levels only by reduction, via simple configuration of two Dip switches.

- Power level 1.8 HP can only be obtained by reduction from 2 HP - Power level 2.3 HP can only be obtained by reduction from 2.5 HP

To order a MULTI UTOPIA Inverter ES system specify all the codes that make up the multi system as follows:


( Indoor units + Grilles + Outdoor U.+ Joint Kit + One Controller only + One Receiver only, in case of infra red controller).

## System sizing


Mono, dual, trial, double twin configuration

### Maximum length of refrigerant piping


**MONO System** (one indoor unit)




**DUAL System** (two indoor units)



**TRIAL System** (three indoor units)



**DOUBLE TWIN System** (four indoor units)





## UTOPIA ES

Outdoor unit		3HP	4HP	5HP	6HP	8HP	10 HP
Maximum piping length between the outdoor unit and the furthest indoor unit	Actual length (L1)	30	50				
	Equivalent length (EL)	40	70				70(*)
Maximum piping length	2 units (A+B+C)	40	60				
	3 units (A+B+C+D)	-	70				
	4 units (B+D, B+E, C+F, C+G)	-				80	
Maximum height difference between outdoor unit and indoor unit	Outdoor up	30					
	Outdoor down	20					
	Between indoor units	0.5					
Piping after the first joint	Dual (B, C)	10					
	Trial (B, C, D)	-			10		
	Double Twin B+D, B+E, C+F, C+G	-				10	

(\*) In combination with double twin: 75 metres

The refrigerant piping from the outdoor unit to the first joint must be longer than the piping between the first joint and the furthest indoor unit.

All piping must be balanced, and the difference between branches must not exceed the limits set out below:

Outdoor unit		3-5HP	6HP	8HP	10 HP
Dual	Difference between B and C	8			
Trial	Difference between B, C and D	-	8		
Double Twin	Difference between: B + (D/E) and C + (F/G); Between D and E; Between F and G	-			8

### Selection of refrigerant piping section and distribution joints

Outdoor Unit capacity	Piping section (A)		Joints		
	Gas	Liquid	Dual	Trial	Double Twin
3HP	Ø 15.88	Ø 9.52	TE-03N1	-	-
4HP	Ø 15.88	Ø 9.52	TE-04N1	-	-
5HP	Ø 15.88	Ø 9.52	TE-56N1	-	-
6HP	Ø 15.88	Ø 9.52	TE-56N1	TRE-46N1	-
8HP	Ø 25.40	Ø 9.52	TE-08N	TE-810N	TE-08N + 2 x TE-04N
10HP	Ø 25.40	Ø 9.52 (1)	TE-08N	-	TE-08N + 2 x TE-56N

(1) Use section 12.7 when piping length exceeds 30 metres.

### Piping section laid between first and second joint (only for 8 and 10HP)

Total capacity downstream of the second joint	Piping section First – Second joint (B-C)	
	Gas	Liquid
≤ 2.3HP	Ø 12.70	Ø 6.35
≤ 6.0HP	Ø 15.88	Ø 9.52





## Piping section to indoor unit

Indoor unit capacity	Piping section	
	Gas	Liquid
1.5HP	Ø 12.70	Ø 6.35
2HP	Ø 15.88	Ø 6.35
2.5-6HP	Ø 15.88	Ø 9.52
8HP	Ø 25.40	Ø 9.52
10HP	Ø 25.40	Ø 9.52 (1)

(1) Use section 12.7 when the piping length exceeds 30 metres: the relevant reducer for the indoor unit piping is supplied with it.

## Combinations of piping section/length

Capacity	Liquid	Ø6.35				Ø9.53					Ø12.7 5'					Ø12.7	
	Gas	Ø9.53	Ø12.7	Ø15.88	Ø19.05	Ø12.7	Ø15.88	Ø19.05	Ø22.20	Ø25.40	Ø15.88	Ø19.05	Ø22.20	Ø25.40	Ø28.60	Ø25.40	Ø28.60
3HP		-	20 <sup>1*2*</sup>	20 <sup>2*</sup>	-	30 <sup>1*</sup>	30	-	-	-	-	-	-	-	-	-	-
4-5-6 HP		-	-	5 <sup>2*</sup>	5 <sup>2*</sup>	40 <sup>1*</sup>	50	50 <sup>4*</sup>	-	-	30 <sup>3*</sup>	30 <sup>3*4*</sup>	-	-	-	-	-
8HP		-	-	-	-	-	-	30 <sup>1*4*</sup>	30 <sup>1*</sup>	50	-	30 <sup>1*2*4*</sup>	30 <sup>1*3*</sup>	30 <sup>3*</sup>	-	-	-
10HP		-	-	-	-	-	-	-	-	30 <sup>5*</sup>	-	-	30 <sup>1*3*</sup>	50 <sup>3*4*</sup>	50 <sup>3*</sup>	20 <sup>3*</sup>	20 <sup>3*</sup>

(1\*) If the gas line diameter is reduced, cooling performance decreases and the operative range is reduced since the line's pressure loss increases.

(2\*) If the liquid line diameter is reduced, capacity of the indoor unit's expansion valve is reduced.

(3\*) If the liquid line size is increased, refrigerant must be added.

(4\*) If the gas line diameter is Ø19.05, the JP6 jumper of the outdoor unit PCB must be cut.

(5\*) If the liquid line exceeds 30 m select liquid piping with diameter equal to Ø12.7mm.



Standard specification

Please refer to page 184 to check accessories



# Commercial Outdoor Units

## UTOPIA RASC IVX

DC INVERTER Heat pump



CUCINA TORCICODA FIRENZE - APPLICATION OF HITACHI UTOPIA RASC IVX

RASC 5HVRNM1E  
RASC 10HRNM1E



-15  
+15



-5  
+46



- INDOOR INSTALLATION
- DUCTABLE
- COMPACT SIZE
- INVERTER COMPRESSOR
- OPTIONAL INPUTS/OUTPUTS

The units of the Utopia RASC Centrifugal range may be installed in closed settings using ducts for outdoor connection, and are therefore ideal where it is required to conceal the unit or in places where the traditional type of outdoor units cannot be used.

### LOW TEMPERATURE OPERATION

Particularly wide operation range, obtained also thanks to a special fan control system which in cooling mode makes operation possible even with particularly low outside temperatures.

### MODIFICATION OF AIR INLET AND OUTLET CONFIGURATION

Four different air Inlet and Outlet configurations are available. The position of side panels and grilles is in fact easily modifiable on site to suit installation needs.

### COMPATIBILITY

With all HITACHI System Free indoor units.



# Commercial Outdoor Units



UTOPIA IVX RASC TECHNICAL SPECIFICATIONS			
CODE		RASC 5HVRNM1E	RASC 10HRNM1E
Power Supply	V/Ph/Hz	1N - 220V 50Hz	3N - 400V 50Hz
Nominal cooling capacity (1)	kW	12.5 (4.7-14.0)	23.0 (10.3-25.0)
Nominal heating capacity (2)	kW	14.0 (5.0-16.0)	25.0 (9.4-26.0)
Nominal Power Input (Cool. / Heat.)	A	21.6 / 212.0	13.0 / 13.1
Input power at nominal cap. (Cool. / Heat.)	kW	4.56 / 4.50	8.09 / 8.20
Max. input current	A	37.0	26.0
EER/COP (4)		2.77 / 3.15	2.88 / 3.09
Connectible Capacity	%	100	100
Min-max indoor units connected	No.	1-3	1-4
Sound Pressure Cooling/Heating (Night Mode) (3)	dB(A)	55-56 (51)	56-57 (52)
Sound Power level at nominal output	dB(A)	71	75
Air flow rate (max.)	m³/h	3900	6300
Useful static pressure (nominal/maximum)	Pa	50/100	63/130
Dimensions (H x L x D)	mm	430x1250x1300	640x1850x985
Weight	kg	176	269
Cooling mode working range	°C	-5 / +46 (BS)	-5 / +46 (BS)
Heating mode working range	°C	-15 / +15 (BU)	-15 / +15 (BU)
R-410A Refrigerant charge	kg	3.1	5.0
Minimum piping length	m	5	5
Maximum piping length without additional charge	m	nd	nd
Maximum piping length (required additional charge)	m (g/m)	70 (to be calculated)	50 (to be calculated)
Maximum lift (OU up - OU down)	m	30/20	30/20
Liquid line piping diameter	inches (mm)	9.53 (3/8)	12.7 (1/2)
Gas line piping diameter	inches (mm)	15.88 (5/8)	25.4 (1)

The specified cooling and heating capacities refer to the outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

<sup>1</sup> Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

<sup>2</sup> Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

<sup>3</sup> Sound pressure level measured at 1.5 metres distance and with closed air ducts in anechoic room

<sup>4</sup> COR and EER values are calculated based on the combination with model RCI indoor units





## UTOPIA RASC IVX

### Prices of Mono Combinations

RCI - 4-WAY CASSETTE SERIES i (90x90)									
Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-5.0FSN3EI	P-N23NA	RASC-5HVRNM1E	220V-50Hz	*	*	*	*	2.7	3.1

RCI - 4-WAY CASSETTE SERIES k (90x90)									
Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-5.0FSN3Ek	P-AP160NA1	RASC-5HVRNM1E	380V-50Hz	*	*	*	*	ND	ND

NOTE: the unit is compatible also with cover panel fitted with motion sensor - cod. P-AP160NAE

RCI - 4-WAY HIGH EFFICIENCY CASSETTE (90x90)									
Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-5.0FSN3	P-AP160NA1	RASC-5HVRNM1E	220V-50Hz	*	*	*	*	2.8	3.2

RPI - DUCTED									
Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPI-5.0FSN4E		RASC-5HVRNM1E	220V-50Hz	*	*	*	*	2.6	3.0
RPI-10.0FSN3E		RASC-10HRNM1E	380V-50Hz	*	*	*	*	2.5	2.8

RPC - CEILING									
Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPC-5.0FSN3E		RASC-5HVRNM1E	220V-50Hz	*	*	*	*	2.6	3.0

RPC - CEILING									
Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPC-5.0FSN3		RASC-5HVRNM1E	220V-50Hz	*	*	*	*	ND	ND

\* DATA NOT SUPPLIED AS THE POWER LEVELS ARE NOT COVERED BY LOT 10 OF THE ERP DIRECTIVE

### Multi Combinations

Model	Single	Twin		Triple		Quad	
		Combination <sup>5</sup>	Joint	Combination <sup>5</sup>	Joint	Combination <sup>5</sup>	Joint
RASC 5HVRNM1E	5.0	2.5/2.5 - 3.0/2.3 4.0/1.5	TE-56N	1.8/1.8/1.5	TRE-06N	-	-
RASC 10HRNM1E	10.0	5.0/5.0 - 4.0/6.0 2.0/8.0	TE-10N	3.0/3.0/3.0 - 4.0/3.0/3.0 - 6.0/2.0/2.0	TRE-810N	2.5/2.5/2.5/2.5 - 3.0/2.5/3.0/2.0 - 3.0/2.5/2.5/2.5 3.0/2.0/3.0/2.0 - 3.0/2.0/2.5/2.5 - 3.0/2.3/3.0/2.3 3.0/2.3/3.0/2.0 - 3.0/2.3/2.5/2.5	TE-10N + (TE-56N + TE-56N)( <sup>*6</sup> ) 2 x E-162SN3 + 1 x E-102SN3
			E-102SN	1 x E-162SN3 + 1 x E-102SN3			QE-810N

Note

5 Non standard power levels can be obtained from fixed levels only by reduction, via simple configuration of two Dip switches.

Power level 1.8 HP can only be obtained by reduction from 2 HP - Power level 2.3 HP can only be obtained by reduction from 2.5 HP

6 TE-03N if after the Joint the power is less than or equal to 1.5Hp. TE-56N if after the Joint the power is higher than 1.5 Hp.

Other measurement conditions: energy consumption / efficiency concern connection of indoor cassette units. Values may vary slightly with other types.




## System sizing

Mono, dual, trial, double twin configuration

### Maximum length of refrigerant piping


#### RASC-(5/10)HP

##### Simple System




##### Double System

$L = A + \text{the longest between B and C}$



##### Triple System

$L = A + \text{the longest among B, C and D}$




#### Only for RASC-10HP

##### Quadruple System


##### Case A

$L = A + \text{the longest between (B + the longest between D and E) and (C + the longest between F and G)}$



##### Case B

$L = A + \text{the longest among B, C, D, and E}$



L and H correspond to the length and height set out in the diagram above. For double, triple and quadruple systems, the length is the distance between RASC units and the furthest indoor unit.

Element		5HP	10HP
Maximum piping length between RASC unit and every indoor unit (L)	Actual piping length	70	50
	Equivalent piping length	90	70
Maximum height difference between RASC unit and indoor unit (H)	RASC unit higher than indoor unit	30	30
	Indoor unit higher than RASC unit	20	20
	Height difference between indoor units	3	3
Maximum piping length between multi-kit and indoor unit	Double B, C	10	15
	Triple B, C, D	10	15
	Case a) B + D, B + E, C + F, C + G	-	15
	Case b) B, C, D, E	-	15
Maximum overall piping length	Double (A + B + C)	80	60
	Triple (A + B + C + D)	80	70
	Case a) (A + B + C + D + E + F + G)	-	80
	Case b) (A + B + C + D + E)	-	80

Notes:

- The length of the RASC refrigerant line up to the first fitting must exceed the length of the line from the first fitting to the furthest indoor unit.

- All connecting pipes must be balanced and the difference between these sections cannot exceed the values set out in the following tables:

Element		5HP	10HP
Double	(B-C)	8	8
Triple	(B-C, B-D, C-D)	8	8
Quadruple	Case a) (B+(D/E)) - (C+(F/G))	-	8
	(D-E)	-	8
	(F-G)	-	8
	Case b) (B-C, B-D, B-E, C-D, C-E, D-E)	-	8



## UTOPIA RASC IVX

### Joint Selection

RASC Unit	Multikit / Distributor		
	Double	Triple	Quadruple
RASC-5HVRNME	TE-56N	TRE-06N	-
RASC-5HVRNM1E	TE-10N	TRE-810N	Case a) JOINTS (*1): TE-10N + (TE-03N + TE-03N) (*2): TE-10N + (TE-56N + TE-56N)
			Case b) HEADER QE-810N


Note:

	Total I.U. capacity after second fitting	Multikit / Distributor
(*1)	≤1.5 HP	TE-03N
(*2)	>1.5 HP	TE-56N

(m)

## Configuration in line

### Maximum length of refrigerant piping (ONLY RASC-10HRNM1E)



Element	10HP
Maximum piping length between RASC unit and every indoor unit (L)	Actual piping length
	Equivalent piping length
Maximum length of the first multi-kit and furthest indoor unit (L2)	15
Maximum piping length between the multi-kit and the indoor unit (L3 <sub>1</sub> , L3 <sub>2</sub> , L3 <sub>3</sub> , L3 <sub>4</sub> )	10
Maximum height difference between RASC unit and indoor unit (Hi-o)	RASC unit higher than indoor unit
	Indoor unit higher than RASC unit
Maximum height difference between indoor units (Hi)	3
Total piping length (L3 <sub>1</sub> , L3 <sub>2</sub> , L3 <sub>3</sub> , L3 <sub>4</sub> )	60

Notes:

All connecting pipes must be balanced and the difference between these sections cannot exceed the values set out in the following tables:

	10HP
L2-L3 <sub>1</sub>	8
L2-(x1+L3 <sub>2</sub> )	8
L2-(x1+x2+L3 <sub>3</sub> , L3 <sub>4</sub> )	8

(m)

### Selection of connecting joints (only RASC-10HP)

Sign	Multi-kit		
	Double	Triple	Quadruple
a. (First multikit)	E-102SN3	E-162SN3	E-162SN3
b. (Second multikit)	-	E-162SN3	E-162SN3
c. (Third multikit)	-	-	E-162SN3





## Connecting dimensions between RASC unit and first fitting

mm (inches)

RASC Unit	Pipe diameter (*1)	
	Liquid	Gas
RASC-5HVRNM1E	Ø 9.53 (3/8")	Ø15.88 (5/8")
RASC-10HRNM1E	Ø12.70 (1/2")	Ø 25.40 (1")

Notes:

(\*1): The dimensions of indoor units and RASC units might be different. Adjust the flared adapter (accessories) on the internal line joint.

## Diameter of connection points between first and second connecting pipe (for quadruple RASC-10HRNM1E system, case A)

Pipe diameter (Ø mm) (First ~ Second connecting pipe)	
Gas	Liquid
Ø 15.88 (5/8")	Ø 9.53 (3/8")

Notes:

(\*1): The dimensions of indoor units and RASC units might be different. Adjust the flared adapter (accessories) on the internal line joint.

## Diameter of connecting points between the connection pipe and the indoor unit

RASC Unit	Pipe diameter	
	Gas	Liquid
1.5 HP	Ø12.70	Ø 6.35
2 HP	Ø15.88	Ø 6.35
(2.5-6) HP	Ø15.88	Ø 9.53
8 HP	Ø19.05 → Ø25.40(*1)	Ø 9.53
10 HP	Ø22.2 → Ø25.40(*1)	Ø 9.53 (*2)

Notes:

If different lines are used from standard values, the installer must supply line reducers.

(\*1) Ø19.05 → Ø25.4 and Ø22.2 → Ø25.4 adapters for internal pipes are supplied in the field with the indoor unit.

(\*2) Select line dimensions with diameter Ø12.7 if the length exceeds 30m. The pipe adapter of the indoor unit is supplied in the field with the indoor unit.

Please refer to page 184 to check accessories




## Commercial Outdoor Units

# UTOPIA IVX STANDARD AND PREMIUM

HITACHI is pleased to introduce its new line of outdoor units UTOPIA IVX STANDARD and IVX PREMIUM.

### ENERGY SAVINGS


Thanks to the new compressor with DC INVERTER control, the renewed design of the cooling circuit and the use of a new exchanger with newly designed fins electrical consumption of condensing units have been reduced to achieve energy efficiency widely meeting the requirements of the new EcoDesign Directive (ErP Lot 10).



### COMFORT AND EASE OF INSTALLATION

UTOPIA IVX STANDARD and IVX PREMIUM systems are a practically perfect solution to address issues arising from the need for individual control up to 8 indoor units. Their flexibility is the same as VRF SET FREE systems but at a more affordable price.


Individual Thermo-ON and Thermo-OFF is possible even when the same remote controller is connected to several indoor units. The conditioning system is able to monitor the temperature and supply the right amount of power based on the requirements of the various zones and different needs of the premises it serves, e.g. inner or outer area of the premises.



This achieves a highly comfortable environment and great energy savings.

### EASILY RE-ADAPTABLE AND RE-CONFIGURABLE


Every indoor unit can be installed and operate in a wholly independent manner even in separate rooms. The functionality of each indoor unit can be controlled by a dedicated remote controller for each individual indoor unit. therefore operation of the indoor unit of the room occupied by people only is possible. This affords high energy savings and total flexibility in view of a possible future reorganisation of inside spaces.



### EASY INSTALLATION

up to 8 indoor units can be connected to the same condensing unit with the same refrigerant circuit. This translates into straightforward and conveniently laid piping routes and wiring.

The space requirements for placing the condensing unit are also much lower.






## HIGH COMFORT LEVEL

UTOPIA IVX STANDARD and IVX PREMIUM systems have been designed to assure the utmost comfort even during the critical defrosting phase. The defrosting operation time has been significantly reduced and the heating time has been increased thanks to an innovative system to assess the amount of frost.

The amount of frost can be estimated based on the defrosting time taken by the previous cycle. If the amount of frost detected by the condensing unit should be less than the previous cycle, the heating operation will be automatically extended until the end of the defrosting period.

Consequently, unnecessary defrosting cycles are thus eliminated in



favour of continued operation in heating mode to assure absolute comfort to the end user.

## COMPATIBILITY WITH R22 REFRIGERANT CIRCUITS

The new UTOPIA IVX STANDARD and IVX PREMIUM systems are compatible with all installations that have operated with R22 gas. the UTOPIA IVX STANDARD and IVX PREMIUM systems that use R410A refrigerant gas can be installed without needing to change the refrigerant piping already laid.

Thanks to an optional feature, standard available on all power levels, the system regulates pressure in order not to damage R22 refrigerant piping despite its thickness is lower than the ideal one for the R410A gas.

## ENERGY EFFICIENCY

Seasonal energy efficiency has been developed to meet the EcoDesign Directive, which specifies minimum requirements that manufacturers must comply with to produce and market their products.

The new calculation method uses different temperature ratings in cooling and heating mode, integrating them with the calculation of operation at partial capacity.

Since the majority of conditioning systems operates at partial capac-

ity, this new methodology to calculate energy efficiency offers a better indication of the actual performance.

The new calculation method of seasonal efficiency also takes into account the energy consumption by auxiliary devices in stand-by mode.

Index of seasonal energy efficiency in cooling (SEER) and coefficient of seasonal performance in heating (SCOP) show a value which is very similar to the actual energy consumption.

## MAIN FEATURES

IVX STANDARD	
1	Very compact size
2	Individual operation of indoor units
3	Increase of the ratio of connectible capacity indoor units - outdoor unit: from 90% minimum to 115% maximum (depending on models)
4	Up to 4 indoor units can be connected to the same condensing unit
5	Option to connect indoor units with power less than 0.8HP
6	Increase in energy performance thanks to the new compressor and a new cooling circuit design
7	Application in systems set up with R22 refrigerant gas piping

IVX PREMIUM	
1	Individual operation of indoor units
2	Increase of the ratio of connectible capacity indoor units - outdoor unit: from 50% minimum to 120% maximum (depending on models)
3	Up to 8 indoor units can be connected to the same condensing unit
4	Complete compliance with the new EcoDesign Directive (EuP Lot 10)
5	Option to connect indoor units with power less than 0.8HP
6	Increase in energy performance thanks to the new compressor and a new cooling circuit design
7	Application in systems set up with R22 refrigerant gas piping
8	Extremely high SCOP and SEER in MONO combination





## UTOPIA IVX STANDARD


BEING PHASED OUT



UTOPIA IVX STANDARD TECHNICAL SPECIFICATIONS

CODE			RAS 3HVNC	RAS 4HVNC	RAS 4HNCE	RAS 5HVNC	RAS 5HNCE
Power Supply		V/Ph/Hz	1 - 220V 50Hz	1 - 220V 50Hz	3N - 400V 50Hz	1 - 220V 50Hz	3N - 400V 50Hz
Nominal cooling capacity (1)		kW	7.1 (3.2-8.0)	10.0 (4.5-11.2)	10.0 (4.5-11.2)	12.5 (5.7-14.0)	12.5 (5.7-14.0)
Nominal heating capacity (2)		kW	8.0 (3.5-10.6)	11.2 (5.0-14.0)	11.2 (5.0-14.0)	14.0 (5.0-16.0)	14.0 (5.0-16.0)
Nominal Power Input (Cool. / Heat.)		A	9.7 / 8.5	11.0 / 10.9	4.0 / 4.0	16.8 / 15.3	6.10 / 5.60
Input power at nominal cap. (Cool. / Heat.)		kW	2.20 / 1.94	2.50 / 2.48	2.50 / 2.48	3.83 / 3.48	3.83 / 3.48
Max. input current		A	16	28	15	28	15
EER/COP (4)			3.14 / 4.00	3.80 / 4.29	3.80 / 4.29	3.16 / 3.88	3.16 / 3.88
SEER		W/W	5.31	5.16	5.07	*	*
Cooling energy efficiency class			A	A	B	*	*
P Design (35°C)		kW	ND	ND	ND	*	*
AVERAGE Climate	SCOP	W/W	4.07	3.92	3.92	*	*
	Heating energy efficiency class		A+	A	A	*	*
	P Design (-10°C)	kW	ND	ND	ND	*	*
Min-max connectible capacity		%	90 - 110	90 - 115	90 - 115	90 - 115	90 - 115
Min-max indoor units connected		No.	1 - 2	1 - 4	1 - 4	1 - 4	1 - 4
Sound Pressure Cooling/Heating (Night Mode) (3)		dB(A)	48 - 50 (46)	50 - 52 (48)	50 - 52 (48)	52 - 54 (50)	52 - 54 (50)
Sound Power level at nominal output		dB(A)	66	70	70	72	71
No. of fans		No.	1	1	1	1	1
Air flow rate (max.)		m³/h	2682	3720	3720	4080	4080
Dimensions (H x L x D)		mm	600x792x300	800x950x370	800x950x370	800x950x370	800x950x370
Weight		kg	44	67	67	79	79
Cooling mode working range		°C	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)
Heating mode working range		°C	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)
R-410A Refrigerant charge		kg	1.9	2.9	2.9	2.9	2.9
Minimum piping length		m	5	5	5	5	5
Maximum piping length without additional charge		m	30	30	30	30	30
Maximum piping length (required additional charge)		m (g/m)	50 (40)	70 (40)	70 (40)	75 (60)	75 (60)
Maximum lift (OU up - OU down)		m	30/20	30/20	30/20	30/20	30/20
Liquid line piping diameter		mm (inch)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)
Gas line piping diameter		mm (inch)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)

# Commercial Outdoor Units



## MAIN FEATURES OF THE RANGE

- Individual operation for each indoor unit
- Very compact size; one fan only up to 6HP
- Option to connect up to 4 indoor units of any type
- Indoor unit connection capacity ratio variable from 90% minimum to 115% maximum of the outdoor unit power (depending on power level)
- Option to connect indoor units with power equal to 0.8HP

- Improved energy performance and compliant with ErP Regulations Lot 10, thanks to the use of a new compressor and a new cooling circuit optimised and entirely designed by HITACHI
- Compatibility with refrigerant piping for old R22 or R407C gas circuits.



UP TO -15°C  
IN COOLING  
MODE ONLY

COMPACT AND LIGHTWEIGHT

LIMITED USE OF REFRIGERANT

WIDE SCOPE OF APPLICATION

INDIVIDUAL CONTROL  
OF THE INDOOR UNIT

HIGH ENERGY EFFICIENCY

The specified cooling and heating capacities refer to the outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

(1) Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

(3) Sound pressure level measured at 1.5 metres below the unit in anechoic room with no reflection.

(4) The performance is calculated based on combination with model RCI FSN3 indoor units

## UTOPIA IVX STANDARD TECHNICAL SPECIFICATIONS

CODE		RAS 6HVNC	RAS 6HNCE	RAS 8HNCE	RAS 10HNCE	RAS 12HNC
Power Supply	V/Ph/Hz	1 - 220V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz
Nominal cooling capacity(1)	kW	14 (6.0-16.0)	14 (6.0-16)	20.0 (8.0-22.4)	25.0 (10-28)	30.0 (11.2-33.5)
Nominal heating capacity (2)	kW	16.0 (5.0-18.0)	16.0 (5.0-18.0)	22.4 (6.3-28)	28.0 (8.0-35)	33.5 (9.0-37.5)
Nominal Power Input (Cool. / Heat.)	A	21.60 / 19.00	7.90 / 6.90	9.10 / 9.00	12.90 / 12.00	18.10 / 14.60
Input power at nominal cap. (Cool. / Heat.)	kW	4.92 / 4.33	4.92 / 4.33	5.69 / 5.62	8.02 / 7.45	9.32 / 8.39
Max. input current	A	28	15	23.2	23.2	24.3
EER/COP (4)		2.77 / 3.59	2.77 / 3.59	3.36 / 3.81	3.02 / 3.63	2.57 / 3.54
SEER	W/W	*	*	*	*	*
Cooling energy efficiency class		*	*	*	*	*
P Design (35°C)	kW	*	*	*	*	*
AVERAGE Climate	SCOP	W/W	*	*	*	*
	Heating energy efficiency class		*	*	*	*
	P Design (-10°C)	kW	*	*	*	*
Min-max connectable capacity	%	90 - 115	90 - 115	90 - 115	90 - 115	90 - 115
Min-max indoor units connected	No.	1 - 4	1 - 4	1 - 4	1 - 4	1 - 4
Sound Pressure Cooling/Heating (Night Mode) (3)	dB(A)	55 - 57 (53)	55 - 57 (53)	57 - 59 (55)	58 - 60 (56)	59 - 61 (56)
Sound Power level at nominal output	dB(A)	72	72	76	76	77
No. of fans	No.	1	1	2	2	2
Air flow rate (max.)	m³/h	4800	4800	7260	8040	9780
Dimensions (H x L x D)	mm	800x950x370	800x950x370	1,380x950x370	1,380x950x370	1,650x1,100x390
Weight	kg	79	79	136	138	168
Cooling mode working range	°C	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)
Heating mode working range	°C	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)
R-410A Refrigerant charge	kg	2.9	2.9	5.3	6.0	6.7
Minimum piping length	m	5	5	5	5	5
Maximum piping length without additional charge	m	30	30	30	30	30
Maximum piping length (required additional charge)	m (g/m)	75 (60)	75 (60)	100 (SEE TC)	100 (SEE TC)	100 (SEE TC)
Maximum lift (OU up - OU down)	m	30/20	30/20	30/20	30/20	30/20
Liquid line piping diameter	mm (inch)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	12.70 (1/2)	12.70 (1/2)
Gas line piping diameter	mm (inch)	15.88 (5/8)	15.88 (5/8)	25.40 (1)	25.40 (1)	25.40 (1)

\* Data not supplied as the power levels are not covered by Lot 10 of the ErP Regulations



## UTOPIA IVX STANDARD

### Prices of Mono Combinations

#### RCI - 4-WAY CASSETTE SERIES i (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-3.0FSN3Ei	P-N23NA	RAS-3HVNC	220V-50Hz	4.87	B	3.95	A	3.0	3.8
RCI-4.0FSN3Ei	P-N23NA	RAS-4HVNCE	220V-50Hz	4.88	B	3.83	A	3.3	3.9
RCI-4.0FSN3Ei	P-N23NA	RAS-4HNCE	380V-50Hz	4.79	B	3.83	A	3.3	3.9
RCI-5.0FSN3Ei	P-N23NA	RAS-5HVNCE	220V-50Hz	*	*	*	*	3.1	3.7
RCI-5.0FSN3Ei	P-N23NA	RAS-5HNCE	380V-50Hz	*	*	*	*	3.1	3.7
RCI-6.0FSN3Ei	P-N23NA	RAS-6HVNCE	220V-50Hz	*	*	*	*	2.6	3.4
RCI-6.0FSN3Ei	P-N23NA	RAS-6HNCE	380V-50Hz	*	*	*	*	2.6	3.4

#### RCI - 4-WAY CASSETTE SERIES k (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-3.0FSN3Ek	P-AP160NA1	RAS-3HVNC	220V-50Hz	4.87	B	3.95	A	3.0	3.8
RCI-4.0FSN3Ek	P-AP160NA1	RAS-4HVNCE	220V-50Hz	4.88	B	3.83	A	3.3	3.9
RCI-4.0FSN3Ek	P-AP160NA1	RAS-4HNCE	380V-50Hz	4.79	B	3.83	A	3.3	3.9
RCI-5.0FSN3Ek	P-AP160NA1	RAS-5HVNCE	220V-50Hz	*	*	*	*	3.1	3.7
RCI-5.0FSN3Ek	P-AP160NA1	RAS-5HNCE	380V-50Hz	*	*	*	*	3.1	3.7
RCI-6.0FSN3Ek	P-AP160NA1	RAS-6HVNCE	220V-50Hz	*	*	*	*	2.6	3.4
RCI-6.0FSN3Ek	P-AP160NA1	RAS-6HNCE	380V-50Hz	*	*	*	*	2.6	3.4

NOTE: the unit is compatible also with cover panel fitted with motion sensor - cod. P-AP160NAE

#### RCI - 4-WAY HIGH EFFICIENCY CASSETTE (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-3.0FSN3	P-AP160NA1	RAS-3HVNC	220V-50Hz	5.31	A	4.07	A+	3.1	4.0
RCI-4.0FSN3	P-AP160NA1	RAS-4HVNCE	220V-50Hz	5.16	A	3.92	A	3.8	4.3
RCI-4.0FSN3	P-AP160NA1	RAS-4HNCE	380V-50Hz	5.07	B	3.92	A	3.8	4.3
RCI-5.0FSN3	P-AP160NA1	RAS-5HVNCE	220V-50Hz	*	*	*	*	3.2	3.9
RCI-5.0FSN3	P-AP160NA1	RAS-5HNCE	380V-50Hz	*	*	*	*	3.2	3.9
RCI-6.0FSN3	P-AP160NA1	RAS-6HVNCE	220V-50Hz	*	*	*	*	2.8	3.6
RCI-6.0FSN3	P-AP160NA1	RAS-6HNCE	380V-50Hz	*	*	*	*	2.8	3.6

NOTE: the unit is compatible also with cover panel fitted with motion sensor - cod. P-AP160NAE

#### RPI - DUCTED

Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPI-3.0FSN4E		RAS-3HVNC	220V-50Hz	4.96	B	3.90	A	2.8	3.6
RPI-4.0FSN4E		RAS-4HVNCE	220V-50Hz	5.13	A	3.91	A	3.4	3.8
RPI-4.0FSN4E		RAS-4HNCE	380V-50Hz	5.03	B	3.91	A	3.4	3.8
RPI-5.0FSN4E		RAS-5HVNCE	220V-50Hz	*	*	*	*	3.1	3.6
RPI-5.0FSN4E		RAS-5HNCE	380V-50Hz	*	*	*	*	3.1	3.6
RPI-6.0FSN4E		RAS-6HVNCE	220V-50Hz	*	*	*	*	2.7	3.5
RPI-6.0FSN4E		RAS-6HNCE	380V-50Hz	*	*	*	*	2.7	3.5
RPI-8.0FSN3E		RAS-8HNCE	380V-50Hz	*	*	*	*	2.8	3.1
RPI-10.0FSN3E		RAS-10HNCE	380V-50Hz	*	*	*	*	2.7	3.0

#### RPC - HIGH EFFICIENCY CEILING

Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPC-3.0FSN3E		RAS-3HVNC	220V-50Hz	3.93	D	3.41	A	2.6	3.1
RPC-4.0FSN3E		RAS-4HVNCE	220V-50Hz	4.45	C	3.41	A	3.1	3.1
RPC-4.0FSN3E		RAS-4HNCE	380V-50Hz	4.38	C	3.41	A	3.1	3.1
RPC-5.0FSN3E		RAS-5HVNCE	220V-50Hz	*	*	*	*	2.8	3.1
RPC-5.0FSN3E		RAS-5HNCE	380V-50Hz	*	*	*	*	2.8	3.1
RPC-6.0FSN3E		RAS-6HVNCE	220V-50Hz	*	*	*	*	2.6	3.1
RPC-6.0FSN3E		RAS-6HNCE	380V-50Hz	*	*	*	*	2.6	3.1

\* DATA NOT SUPPLIED AS THE POWER LEVELS ARE NOT COVERED BY LOT 10 OF THE ERP DIRECTIVE



# Commercial Outdoor Units



## RPK - WALL

Indoor Unit		Outdoor Unit		Performance					
model	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP	
RPC-3.0FSN3	RAS-3HVNC	220V-50Hz	ND	ND	ND	ND	ND	ND	ND
RPC-4.0FSN3	RAS-4HVNC	220V-50Hz	ND	ND	ND	ND	ND	ND	ND
RPC-4.0FSN3	RAS-4HNCE	380V-50Hz	ND	ND	ND	ND	ND	ND	ND
RPC-5.0FSN3	RAS-5HVNC	220V-50Hz	*	*	*	*	ND	ND	ND
RPC-5.0FSN3	RAS-5HNCE	380V-50Hz	*	*	*	*	ND	ND	ND
RPC-6.0FSN3	RAS-6HVNC	220V-50Hz	*	*	*	*	ND	ND	ND
RPC-6.0FSN3	RAS-6HNCE	380V-50Hz	*	*	*	*	ND	ND	ND

## RPK - WALL

Indoor Unit		Outdoor Unit		Performance					
model	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP	
RPK-3.0FSN3M	RAS-3HVNC	220V-50Hz	4.88	B	3.70	A	2.7	2.9	
RPK-4.0FSN3M	RAS-4HVNC	220V-50Hz	4.91	B	3.40	A	2.4	3.0	
RPK-4.0FSN3M	RAS-4HNCE	380V-50Hz	4.83	B	3.40	A	2.4	3.0	

\* DATA NOT SUPPLIED AS THE POWER LEVELS ARE NOT COVERED BY LOT 10 OF THE ERP DIRECTIVE




## UTOPIA IVX STANDARD



UTOPIA IVX STANDARD TECHNICAL SPECIFICATIONS						
CODE		RAS 3HVNC1	RAS 4HVNC1E	RAS 4HNC1E	RAS 5HVNC1E	RAS 5HNC1E
Power Supply	V/Ph/Hz	1 - 220V 50Hz	1 - 220V 50Hz	3N - 400V 50Hz	1 - 220V 50Hz	3N - 400V 50Hz
Nominal cooling capacity(1)	kW	7.1 (3.2-8.0)	10.0 (4.5-11.2)	10.0 (4.5-11.2)	12.5 (5.7-14.0)	12.5 (5.7-14.0)
Nominal heating capacity (2)	kW	8.0 (3.5-10.6)	11.2 (5.0-14.0)	11.2 (5.0-14.0)	14.0 (5.0-18.0)	14.0 (5.0-18.0)
Nominal Power Input (Cool. / Heat.)	A	9.4 / 8.3	11.2 / 10.1	4.1 / 3.7	15.5 / 15.1	5.7 / 5.5
Input power at nominal cap. (Cool. / Heat.)	kW	2.14 / 1.88	2.55 / 2.30	2.55 / 2.30	3.54 / 3.43	3.54 / 3.43
Max. input current	A	17.8	28.5	15.5	28.5	15.5
EER/COP (4)		4.00 / 4.00	4.57 / 4.57	4.57 / 4.57	3.37 / 3.89	3.37 / 3.89
SEER	W/W	6.00	6.57	6.41	*	*
Cooling energy efficiency class		A+	A++	A++	*	*
P Design (35°C)	kW	7.1	10.0	10.0	*	*
AVERAGE Climate	SCOP	W/W	4.21	4.47	4.47	*
	Heating energy efficiency class		A+	A+	A+	*
	P Design (-10°C)	kW	5.6	8.7	8.7	*
Min-max connectible capacity	%	90-110	90-115	90-115	90-115	90-115
Min-max indoor units connected	No.	1-2	1-4	1-4	1-4	1-4
Sound Pressure Cooling/Heating (Night Mode) (3)	dB(A)	48-50 (46)	52-54 (50)	52-54 (50)	52-54 (50)	52-54 (50)
Sound Power level at nominal output	dB(A)	66	68	68	68	68
No. of fans	No.	1	1	1	1	1
Air flow rate (max.)	m³/h	2682	3720	3720	4080	4080
Dimensions	mm	600x792x300	1140x950x370	1140x950x370	1140x950x370	1140x950x370
Weight	kg	44	79	79	89	89
Cooling mode working range	°C	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)
Heating mode working range	°C	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)
R-410A Refrigerant charge	kg	1.9	3.2	3.2	3.2	3.2
Minimum piping length	m	5	5	5	5	5
Maximum piping length without additional charge	m	30	30	30	30	30
Maximum piping length (required additional charge)	m (g/m)	50 (40)	70 (40)	70 (40)	75 (60)	75 (60)
Maximum lift (OU up - OU down)	g/m	30/20	30/20	30/20	30/20	30/20
Liquid line piping diameter	mm (inch)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)
Gas line piping diameter	mm (inch)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)

# Commercial Outdoor Units



HITACHI is pleased to introduce its new range of IVX STANDARD outdoor units, today even more efficient and functional.

## MAIN FEATURES OF THE NEW RANGE

- Individual operation for each indoor unit
- Very compact size; one fan only up to 6HP
- Option to connect up to 4 indoor units of any type
- Indoor unit connection capacity ratio variable from 90% minimum to 115% maximum of the outdoor unit power (depending on power level)

- Option to connect indoor units with power equal to 0.8HP
- Compliant with the new Eco Design directive EuP lot 10 and designed to have seasonal efficiency compliant with the European Directive in seasonal efficiency lot 6/21 in force from 2015
- Compatibility with refrigerant piping for old R22 or R407C gas circuits.



COMPACT AND LIGHTWEIGHT

LIMITED USE OF REFRIGERANT

WIDE SCOPE OF APPLICATION

INDIVIDUAL CONTROL OF THE INDOOR UNIT

HIGH ENERGY EFFICIENCY

The specified cooling and heating capacities refer to outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

(1) Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

(3) Sound pressure level has been measured in an anechoic chamber, 1.5m below the unit, with no reflection

(4) Performance is calculated based on combination with indoor units model RCI

## UTOPIA IVX STANDARD TECHNICAL SPECIFICATIONS

CODE		RAS 6HVC1E	RAS 6HNC1E	RAS 8HNCE	RAS 10HNCE	RAS 12HNCE
Power Supply	V/Ph/Hz	1 - 220V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz
Nominal cooling capacity(1)	kW	13 (6.0-16.0)	13 (6.0-16)	20.0 (8.0-22.4)	25.0 (10.0-28.0)	30.0 (11.2-37.5)
Nominal heating capacity (2)	kW	16.0 (5.0-20.0)	16.0 (5.0-20.0)	22.4 (6.3-28.0)	28.0 (8.0-35.0)	33.5 (9.0-37.5)
Nominal Power Input (Cool. / Heat.)	A	18.1 / 19.0	6.6 / 6.9	9.1 / 9.0	12.9 / 12.0	17.5 / 14.2
Input power at nominal cap. (Cool. / Heat.)	kW	4.12 / 4.32	4.12 / 4.32	5.69 / 5.62	8.02 / 7.45	11.05 / 8.96
Max. input current	A	28.5	15.5	24.0	24.0	24.3
EER/COP (4)		3.26 / 3.56	3.26 / 3.56	3.36 / 3.81	3.02 / 3.63	2.57 / 3.54
SEER	W/W	*	*	*	*	*
Cooling energy efficiency class		*	*	*	*	*
P Design (35°C)	kW	*	*	*	*	*
AVERAGE Climate	SCOP	W/W	*	*	*	*
	Heating energy efficiency class		*	*	*	*
	P Design (-10°C)	kW	*	*	*	*
Min-max connectible capacity	%	90-115	90-115	90-115	90-115	90-115
Min-max indoor units connected	No.	1-4	1-4	1-4	1-4	1-4
Sound Pressure Cooling/Heating (Night Mode) (3)	dB(A)	55-57 (53)	55-57 (53)	57-59 (55)	58-60 (56)	59-61 (56)
Sound Power level at nominal output	dB(A)	71	71	76	76	77
No. of fans	No.	1	1	2	2	2
Air flow rate (max.)	m³/h	4800	4800	7620	8040	9780
Dimensions	mm	1140x950x370	1140x950x370	1380x950x370	1380x950x370	1650x1100x390
Weight	kg	89	89	136	138	168
Cooling mode working range	°C	-5 / +46 (BS)	-5 / +46 (BS)	-15 / +46 (BS)	-15 / +46 (BS)	-15 / +46 (BS)
Heating mode working range	°C	-15 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)
R-410A Refrigerant charge	kg	3.2	3.2	5.7	6.2	6.7
Minimum piping length	m	5	5	5	5	5
Maximum piping length without additional charge	m	30	30	30	30	30
Maximum piping length (required additional charge)	m (g/m)	75 (60)	75 (60)	100 (SEE TC)	100 (SEE TC)	100 (SEE TC)
Maximum lift (OU up - OU down)	g/m	30/20	30/20	30/20	30/20	30/20
Liquid line piping diameter	mm (inch)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	12.7 (1/2)	12.7 (1/2)
Gas line piping diameter	mm (inch)	15.88 (5/8)	15.88 (5/8)	25.4 (1)	25.4 (1)	25.4 (1)

\* Data not supplied as the power levels are not covered by Lot 10 of the ErP Regulations





## UTOPIA IVX STANDARD

### Prices of Mono Combinations

#### RCI - 4-WAY CASSETTE SERIES i (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-3.0FSN3Ei	P-N23NA	RAS-3HVNC1E	220V-50Hz	5.48	A	3.95	A	3.8	3.8
RCI-4.0FSN3Ei	P-N23NA	RAS-4HVNC1E	220V-50Hz	5.75	A+	4.21	A+	4.1	4.1
RCI-4.0FSN3Ei	P-N23NA	RAS-4HNC1E	380V-50Hz	5.63	A+	4.21	A+	4.1	4.1
RCI-5.0FSN3Ei	P-N23NA	RAS-5HVNC1E	220V-50Hz	*	*	*	*	3.3	3.7
RCI-5.0FSN3Ei	P-N23NA	RAS-5HNC1E	380V-50Hz	*	*	*	*	3.3	3.7
RCI-6.0FSN3Ei	P-N23NA	RAS-6HVNC1E	220V-50Hz	*	*	*	*	3.1	3.4
RCI-6.0FSN3Ei	P-N23NA	RAS-6HNC1E	380V-50Hz	*	*	*	*	3.1	3.4

#### RCI - 4-WAY CASSETTE SERIES k (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-3.0FSN3Ek	P-AP160NA1	RAS-3HVNC1E	220V-50Hz	5.48	A	3.95	A	3.8	3.8
RCI-4.0FSN3Ek	P-AP160NA1	RAS-4HVNC1E	220V-50Hz	5.75	A+	4.21	A+	4.1	4.1
RCI-4.0FSN3Ek	P-AP160NA1	RAS-4HNC1E	380V-50Hz	5.63	A+	4.21	A+	4.1	4.1
RCI-5.0FSN3Ek	P-AP160NA1	RAS-5HVNC1E	220V-50Hz	*	*	*	*	3.3	3.7
RCI-5.0FSN3Ek	P-AP160NA1	RAS-5HNC1E	380V-50Hz	*	*	*	*	3.3	3.7
RCI-6.0FSN3Ek	P-AP160NA1	RAS-6HVNC1E	220V-50Hz	*	*	*	*	3.1	3.4
RCI-6.0FSN3Ek	P-AP160NA1	RAS-6HNC1E	380V-50Hz	*	*	*	*	3.1	3.4

NOTE: the unit is compatible also with cover panel fitted with motion sensor - cod. P-AP160NAE

#### RCI - 4-WAY HIGH EFFICIENCY CASSETTE (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-3.0FSN3	P-AP160NA1	RAS-3HVNC1E	220V-50Hz	6.00	A+	4.21	A+	4.0	4.0
RCI-4.0FSN3	P-AP160NA1	RAS-4HVNC1E	220V-50Hz	6.57	A++	4.47	A+	4.6	4.6
RCI-4.0FSN3	P-AP160NA1	RAS-4HNC1E	380V-50Hz	6.41	A++	4.47	A+	4.6	4.6
RCI-5.0FSN3	P-AP160NA1	RAS-5HVNC1E	220V-50Hz	*	*	*	*	3.4	3.9
RCI-5.0FSN3	P-AP160NA1	RAS-5HNC1E	380V-50Hz	*	*	*	*	3.4	3.9
RCI-6.0FSN3	P-AP160NA1	RAS-6HVNC1E	220V-50Hz	*	*	*	*	3.3	3.6
RCI-6.0FSN3	P-AP160NA1	RAS-6HNC1E	380V-50Hz	*	*	*	*	3.3	3.6

NOTE: the unit is compatible also with cover panel fitted with motion sensor - cod. P-AP160NAE

#### RPI - DUCTED

Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPI-3.0FSN4E		RAS-3HVNC1E	220V-50Hz	5.35	A	3.91	A	3.6	3.6
RPI-4.0FSN4E		RAS-4HVNC1E	220V-50Hz	5.97	A+	4.31	A+	4.0	4.0
RPI-4.0FSN4E		RAS-4HNC1E	380V-50Hz	5.84	A+	4.31	A+	4.0	4.0
RPI-5.0FSN4E		RAS-5HVNC1E	220V-50Hz	*	*	*	*	3.3	3.6
RPI-5.0FSN4E		RAS-5HNC1E	380V-50Hz	*	*	*	*	3.3	3.6
RPI-6.0FSN4E		RAS-6HVNC1E	220V-50Hz	*	*	*	*	3.2	3.0
RPI-6.0FSN4E		RAS-6HNC1E	380V-50Hz	*	*	*	*	3.2	3.0

#### RPC - CEILING

Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPC-3.0FSN3E		RAS-3HVNC1E	220V-50Hz	4.68	B	3.80	A	3.1	3.1
RPC-4.0FSN3E		RAS-4HVNC1E	220V-50Hz	4.61	B	3.80	A	3.3	3.3
RPC-4.0FSN3E		RAS-4HNC1E	380V-50Hz	4.53	C	3.80	A	3.3	3.3
RPC-5.0FSN3E		RAS-5HVNC1E	220V-50Hz	*	*	*	*	3.0	3.1
RPC-5.0FSN3E		RAS-5HNC1E	380V-50Hz	*	*	*	*	3.0	3.1
RPC-6.0FSN3E		RAS-6HVNC1E	220V-50Hz	*	*	*	*	3.0	3.6
RPC-6.0FSN3E		RAS-6HNC1E	380V-50Hz	*	*	*	*	3.0	3.6

\* DATA NOT SUPPLIED AS THE POWER LEVELS ARE NOT COVERED BY LOT 10 OF THE ERP DIRECTIVE

# Commercial Outdoor Units



## RPC - HIGH EFFICIENCY CEILING

Indoor Unit		Outdoor Unit		Performance				
model	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPC-3.0FSN3	RAS-3HVNC1E	220V-50Hz	5.29	A	4.13	A+	3.4	3.4
RPC-4.0FSN3	RAS-4HVNC1E	220V-50Hz	5.02	B	3.90	A	3.9	3.9
RPC-4.0FSN3	RAS-4HNC1E	380V-50Hz	4.93	B	3.90	A	3.9	3.9
RPC-5.0FSN3	RAS-5HVNC1E	220V-50Hz	*	*	*	*	2.7	3.6
RPC-5.0FSN3	RAS-5HNC1E	380V-50Hz	*	*	*	*	2.7	3.6
RPC-6.0FSN3	RAS-6HVNC1E	220V-50Hz	*	*	*	*	2.6	3.4
RPC-6.0FSN3	RAS-6HNC1E	380V-50Hz	*	*	*	*	2.6	3.4

## RPK - WALL



Indoor Unit		Outdoor Unit		Performance				
model	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPK-3.0FSN3M	RAS-3HVNC1E	220V-50Hz	5.35	A	3.80	A	2.9	2.9
RPK-4.0FSN3M	RAS-4HVNC1E	220V-50Hz	5.56	A	3.83	A	3.2	3.2
RPK-4.0FSN3M	RAS-4HNC1E	380V-50Hz	5.45	A	3.83	A	3.2	3.2

\* DATA NOT SUPPLIED AS THE POWER LEVELS ARE NOT COVERED BY LOT 10 OF THE ERP DIRECTIVE









## UTOPIA IVX STANDARD

### Multi Combinations

UTOPIA IVX STANDARD 2-6HP														
CODE	Power level minimum unit names indoor connectible	Maximum number of indoor units connectible	1 unit	2 units		3 units				4 units				
					TRIAL CONFIGURATION		IN LINE CONFIGURATION		QUAD CONFIGURATION		IN LINE CONFIGURATION			
			Comb.	Comb.	Joints	Comb.	Joints	Comb.	Joints	Comb.	Joints	Comb.	Joints	
RAS 3H(V)NC1	0,8HP	2	90-110% FROM 2.7 TO 3.3HP	90-100% FROM 2.7 TO 3HP	TE-03N1	NOT POSSIBLE				NOT POSSIBLE				
RAS 4H(V)NC(1)E	0.8HP	4	90-115% FROM 3.6 TO 4.6HP	90-115% FROM 3.6 TO 4.6HP	TE-04N1	90-100% FROM 3.6 TO 4HP	TRE-46N1	90-100% FROM 3.6 TO 4HP	2 x E-102SN3	90-100% FROM 3.6 TO 4HP	(*) First joint: TE-04N1 Second joint: If power downstream ≤ 1.5HP: TE-03N1 If power downstream ≥ 1.8HP AND < 4HP: TE-03N1 If power downstream = 4HP: TE-04N1 If power downstream > 4HP: TE-56N1		90-100% FROM 3.6 TO 4HP	3xE-102SN3
RAS 5H(V)NC(1)E	0,8HP	4	90-115% FROM 4.5 TO 5.75HP	90-115% FROM 4.5 TO 5.75HP	TE-56N1	90-100% FROM 4.5 TO 5HP	TRE-46N1	90-100% FROM 4.5 TO 5HP	2 x E-102SN3	90-100% FROM 4.5 TO 5HP	(*) First joint: TE-56N1 Second joint: If power downstream ≤ 1.5HP: TE-03N1 If power downstream ≥ 1.8HP AND < 4HP: TE-03N1 If power downstream = 4HP: TE-04N1 If power downstream > 4HP: TE-56N1		90-100% FROM 4.5 TO 5HP	3xE-102SN3
RAS 6H(V)NC(1)E	0,8HP	4	90-115% FROM 5.4 TO 6.9HP	90-115% FROM 5.4 TO 6.9HP	TE-56N1	90-100% FROM 5.4 TO 6HP	TRE-46N1	90-100% FROM 5.4 TO 6HP	2xE-102SN3	90-100% FROM 5.4 TO 6HP	(*) First joint: TE-56N1 Second joint: If power downstream ≤ 1.5HP: TE-03N1 If power downstream ≥ 1.8HP AND < 4HP: TE-03N1 If power downstream = 4HP: TE-04N1 If power downstream > 4HP: TE-56N1		90-100% FROM 5.4 TO 6HP	3xE-102SN3

(\*) If the capacity ratio between the two branches downstream of the first joint, is higher than 60/40%, use installation with in line configuration.

UTOPIA IVX STANDARD 8-12HP														
CODE	Power level minimum indoor unit connectible	Maximum number of indoor units connectible	1 unit	2 units		3 units				4 units				
						TRIAL CONFIGURATION 		CONFIGURATION IN LINE 		QUAD CONFIGURATION 		CONFIGURATION IN LINE 		
			Comb.	Comb.	Joints	Combination	Joints	Combination	Joints	Combination	Joints	Combination	Joints	
RAS 8HNCE	1.8HP	4	90-115% FROM 7.2 TO 9.2HP	90-115% FROM 7.2 TO 9.2HP	TE-08N	90-115% FROM 7.2 TO 9.2HP	TRE-812N1	90-115% FROM 7.2 TO 9.2HP	1 x E-162SN3 + 1 x E- 102SN3	90-115% FROM 7.2 TO 9.2HP	(*) First joint: TE-08N Second joint: If power downstream ≤ 1.5HP: TE-03N1 If power downstream ≥ 1.8HP AND < 4HP: TE-03N1 If power downstream = 4HP: TE-04N1 If power downstream ≥ 5HP: TE-56N1 IT IS POSSIBLE TO USE HEADER: QE-812N1		90-115% FROM 7.2 TO 9.2HP	2 x E-162SN3 + 1 x E-102SN3
RAS 10HNCE	1.8HP	4	90-115% FROM 9 TO 11.5HP	90-115% FROM 9 TO 11.5HP	TE-10N	90-115% FROM 9 TO 11.5HP	TRE-812N1	90-115% FROM 9 TO 11.5HP	1 x E-162SN3 + 1 x E- 102SN3	90-115% FROM 9 TO 11.5HP	(*) First joint: TE-10N Second joint: If power downstream ≤ 1.5HP: TE-03N1 If power downstream ≥ 1.8HP AND < 4HP: TE-03N1 If power downstream = 4HP: TE-04N1 If power downstream ≥ 5HP: TE-56N1 IT IS POSSIBLE TO USE HEADER: QE-812N1		90-115% FROM 9 TO 11.5HP	2 x E-162SN3 + 1 x E-102SN3
RAS 12HNC	1.8HP	4	90-115% FROM 10.8 TO 13.8HP	6.0/6.0 FROM 10.8 TO 13.8HP	TE-10N	90-115% FROM 10.8 TO 13.8HP	TRE-812N1	90-115% FROM 10.8 TO 13.8HP	1 x E-162SN3 + 1 x E- 102SN3	90-115% FROM 10.8 TO 13.8HP	(*) First joint: TE-10N Second joint: If power downstream ≤ 1.5HP: TE-03N1 If power downstream ≥ 1.8HP AND < 4HP: TE-03N1 If power downstream = 4HP: TE-04N1 If power downstream ≥ 5HP: TE-56N1 IT IS POSSIBLE TO USE HEADER: QE-812N1		90-115% FROM 10.8 TO 13.8HP	2 x E-162SN3 + 1 x E-102SN3

(\*) If the capacity ratio between the two branches downstream of the first joint is higher than 60/40%, use installation with in line configuration.





## Remarks

<sup>1</sup> **TABLE 1:** In systems where indoor units are all RCI-FSN3 models, the maximum allowed capacity ratio is 100% and the maximum number of indoor units is as follows:

Outdoor unit model	HP	3	4	5	6	8	10	12
UTOPIA IVX	No.	1	2				4	

<sup>2</sup> When installing model RCIM 2.0FSN3, RPF(I) 2.0FSN2E or RPF(I) 2.5FSN2E indoor units, the MONO combination with UTOPIA IVX and IVX PREMIUM outdoor units is not allowed

<sup>3</sup> In case of installation in cold areas (where the outside temperature might reach -5°C) or in areas with high heating demands, do not install a higher number of indoor units than recommended and assure a capacity ratio lower than 100%.

## System sizing


Mono, dual, trial, double twin configuration

### Maximum length of refrigerant piping

Outdoor unit		3HP	4HP	5HP	6HP	8HP	10HP	12HP
Maximum piping length between the outdoor unit and the furthest indoor unit	Actual length (L1)	50	70	75		100		
	Equivalent length (EL)	70	90	95		125		
Maximum piping length	2 units (A+B+C)	60	80	85		100	115	
	3 units (A+B+C+D)	-	90	85		100		
	4 units (B+D, B+E, C+F, C+G)	-	90	95		100	145	
Maximum piping length after the first joint	2 and 3 units (B,C,D)	10				15		
	4 units (B+D, B+E, C+F, C+G)	-	10			15		
Main piping length (A)		A > B, C, D, E, F, G						
Maximum height difference between outdoor unit and indoor unit	Outdoor up	30						
	Outdoor down	20						
Maximum height difference between indoor units		3						
Maximum height difference Joint/indoor unit (2, 3 and 4 indoor units) Joint/joint (4 indoor units)		3						
(B-C)/(B-D)/(C-D)/(C+G)-(B+E)/(C+G)-(B+D)/(C+F)-(B+E)/(C+F)-(B+D)		< 8						

### Selection of refrigerant piping section and distribution joints

#### MONO System (one indoor unit)




Outdoor unit capacity HP	Piping section (L)	
	Gas	Liquid
3/4/5/6	Ø 15.88	Ø 9.52
8	Ø 25.40	Ø 9.52
10/12	Ø 25.40	Ø 12.70



## UTOPIA IVX STANDARD

**DUAL System** (two indoor units)




Outdoor Unit capacity HP	Piping section (A)		Joints
	Gas	Liquid	
3	Ø 15.88	Ø 9.52	TE-03N1
4	Ø 15.88	Ø 9.52	TE-04N1
5/6	Ø 15.88	Ø 9.52	TE-56N1
8	Ø 25.40	Ø 9.52 (1)	TE-08N
10/12	Ø 25.40	Ø 12.70	TE-10N

(1) In the event the total piping length should exceed 70 metres for 8HP outdoor unit, use liquid piping with section 12.7.

Indoor Unit capacity HP	Piping section (B, C)	
	Gas	Liquid
≤ 1.5HP	Ø 12.70	Ø 6.35
1.8/2.0HP	Ø 15.88	Ø 6.35
≥ 2.3HP	Ø 15.88	Ø 9.52

**TRIAL System** (three indoor units)




Outdoor unit capacity HP	Piping section (A)		Joints
	Gas	Liquid	
4/5/6	Ø 15.88	Ø 9.52	TRE-46N1
8	Ø 24.40	Ø 9.52 (1)	TRE-812N1
10/12	Ø 24.40	Ø 12.70	TRE-812N1

(1) In the event the piping length (A+B or A+C or A+D) should exceed 70 metres for the 8HP outdoor unit, use liquid piping with section 12.7.

Indoor Unit capacity HP	Piping section (B, C, D)	
	Gas	Liquid
≤ 1.5HP	Ø 12.70	Ø 6.35
1.8/2.0HP	Ø 15.88	Ø 6.35
≥ 2.3HP	Ø 15.88	Ø 9.52

**DOUBLE TWIN System** (four indoor units)



Outdoor unit capacity HP	Piping section (A)		Joint 1	Header
	Gas	Liquid		
4	Ø 15.88	Ø 9.52	TE-04N1	-
5/6	Ø 15.88	Ø 9.52	TE-56N1	-
8	Ø 25.40	Ø 9.52 (1)	TE-08N	QE-812N1
10/12	Ø 25.40	Ø 12.70	TE-10N	QE-812N1

(1) In the event the piping length (A+B+D or A+B+E or A+C+F or A+C+G) should exceed 70 metres for the 8HP outdoor unit, use liquid piping with section 12.7.

Total capacity of indoor units 1+2 or 3+4	Piping section (B, C)		Joint 2
	Gas	Liquid	
≤ 1.5HP	Ø 12.70	Ø 6.35	TE-03N1
1.8/2.0HP	Ø 15.88	Ø 6.35	TE-03N1
≥ 2.3HP	Ø 15.88	Ø 9.52	< 4HP: TE-03N1 = 4HP: TE-04N1 ≥ 5HP: TE-56N1

Outdoor unit capacity HP	Piping section (D, E, F, G)	
	Gas	Liquid
≤ 1.5HP	Ø 12.70	Ø 6.35
1.8/2.0HP	Ø 15.88	Ø 6.35
≥ 2.3HP	Ø 15.88	Ø 9.52

If the capacity ratio between the sets of indoor units 1+2 and 3+4 exceeds 60/40% make an installation with "in line configuration".




## Configuration in line

### Maximum length of refrigerant piping

Outdoor unit		4HP	5HP	6HP	8HP	10HP	12HP
Maximum piping length between the outdoor unit and the furthest indoor unit	Actual length (L1)	70	75			100	
	Equivalent length (EL)	90	95			125	
Maximum piping length between the first joint and every indoor unit (L2)		20			25		
Maximum piping length from joint to indoor unit (L3)		10			15		
Total piping length L4+(L3 <sub>1</sub> +L3 <sub>2</sub> +L3 <sub>3</sub> ...)		70	75		100	145	
Maximum height difference between outdoor unit and indoor unit	Outdoor up	30					
	Outdoor down	20					
Maximum height difference between indoor units		3					
Maximum height difference	Joint/indoor unit (2, 3 and 4 indoor units)	3					
	Joint/joint (4 indoor units)	3					

### Selection of refrigerant piping section and distribution joints



Outdoor unit capacity HP	Piping section (C, D) (L4)		Joints A	Joints B
	Gas	Liquid		
3/4/5/6	Ø 15.88	Ø 9.52	E-102SN3	E-102SN3
8	Ø 25.40	Ø 9.52 (1)	E-162SN3	E-102SN3
10/12	Ø 25.40	Ø 12.70	E-162SN3	E-102SN3

(1) In the event the total piping length from outdoor unit to the furthest indoor unit should exceed 70 metres for the 8HP outdoor unit, use liquid piping with section 12.70.

Indoor Unit capacity HP	Piping section (L3)	
	Gas	Liquid
≤ 1.5HP	Ø 12.70	Ø 6.35
1.8/2.0HP	Ø 15.88	Ø 6.35
≥ 2.3HP	Ø 15.88	Ø 9.52

### Combinations of piping section/length

Capacity	Liquid	Ø6.35				Ø9.53					Ø12.70					Ø15.88		
	Gas	Ø9.53	Ø12.70	Ø15.88	Ø19.05	Ø12.70	Ø15.88	Ø19.05	Ø22.20	Ø25.40	Ø15.88	Ø19.05	Ø22.20	Ø25.40	Ø28.60	Ø22.30	Ø25.40	Ø28.60
3HP		-	30 <sup>(1)(2)</sup>	30 <sup>(2)</sup>	-	30 <sup>(1)</sup>	50	-	-	-	-	-	-	-	-	-	-	-
4HP		-	-	5 <sup>(2)</sup>	5 <sup>(2)</sup>	40 <sup>(1)</sup>	70	50 <sup>(4)</sup>	-	-	30 <sup>(3)</sup>	30 <sup>(3)(4)</sup>	-	-	-	-	-	-
5-6HP		-	-	5 <sup>(2)</sup>	5 <sup>(2)</sup>	40 <sup>(1)</sup>	75	50 <sup>(4)</sup>	-	-	30 <sup>(3)</sup>	30 <sup>(3)(4)</sup>	50 <sup>(1)(3)</sup>	-	-	-	-	-
8HP		-	-	-	-	-	-	50 <sup>(1)(4)</sup>	50 <sup>(1)</sup>	70 <sup>(5)</sup>	-	50 <sup>(1)(3)(4)</sup>	50 <sup>(1)</sup>	100	-	50 <sup>(1)(3)</sup>	50 <sup>(3)</sup>	-
10HP		-	-	-	-	-	-	-	-	-	-	-	-	100	50	50 <sup>(1)(3)</sup>	50 <sup>(3)</sup>	50 <sup>(3)</sup>

- (1) If the gas line diameter is reduced, cooling performance decreases and the operative range is reduced since the line's pressure loss increases.
- (2) If the liquid line diameter is reduced, capacity of the indoor unit's expansion valve is reduced.
- (3) If the liquid line size is increased, refrigerant must be added.
- (4) In the event the gas piping section is 19.05, move to the ON position pin no. 4 of switch DSW2 on the electronic board of the outdoor unit.
- (5) In the event the piping length should exceed 70m for the 8HP power level, use section 12.7 for the liquid piping



Standard specification

Please refer to page 184 to check accessories



## UTOPIA IVX PREMIUM




UTOPIA IVX PREMIUM TECHNICAL SPECIFICATIONS

CODE			RAS 2HVN1P	RAS 2.5HVN1P	RAS 3HVN1E	RAS 4HVN1E	RAS 4HNP1E
Power Supply		V/Ph/Hz	1 - 220V 50Hz	1 - 220V 50Hz	1 - 220V 50Hz	1 - 220V 50Hz	3N - 400V 50Hz
Nominal cooling capacity (1)		kW	5.0 (2.2-5.6)	5.6 (2.2-6.3)	7.1 (3.2-8.0)	10.0 (4.5-11.2)	10.0 (4.5-11.2)
Nominal heating capacity (2)		kW	5.6 (2.2-7.1)	6.3 (2.2-8.0)	8.0 (3.5-10.6)	11.2 (5.5-14.0)	11.2 (5.0-14.0)
Nominal Power Input (Cool. / Heat.)		A	5.1 / 4.9	5.4 / 5.7	6.4 / 6.7	8.7 / 8.9	3.2 / 3.2
Input power at nominal cap. (Cool. / Heat.)		kW	1.17 / 1.13	1.22 / 1.30	1.46 / 1.52	1.99 / 2.02	1.99 / 2.02
Max. input current		A	13.8	15.8	21.5	30.5	14.0
EER/COP (4)			4.03 / 4.68	4.18 / 4.92	4.49 / 4.88	4.68 / 5.16	4.68 / 5.16
SEER		W/W	6.49	6.05	7.42	7.88	7.66
Cooling energy efficiency class			A++	A+	A++	A++	A++
P Design (35°C)		kW	5.0	5.6	7.1	10.0	10.0
AVERAGE Climate	SCOP	W/W	4.67	4.77	4.37	4.68	4.68
	Heating energy efficiency class		A++	A++	A+	A++	A++
	P Design (-10°C)	kW	5.0	5.2	6.4	11.5	11.5
Min-max connectible capacity		%	90-110	90-110	50-120	50-120	50-120
Min-max indoor units connected		No.	1-2	1-2	1-3	1-5	1-5
Sound Pressure Cooling/Heating (Night Mode) (3)		dB(A)	44-46 (42)	45-47 (43)	45-47 (41)	47-49 (43)	47-49 (43)
Sound power level at nominal output		dB(A)	62	63	63	63	63
No. of fans		No.	1	1	1	2	2
Air flow rate (max.)		m³/h	2436	2436	2700	4800	4800
Dimensions (HxLxD)		mm	600x792x300	600x792x300	800x950x370	1380x950x370	1380x950x370
Weight		kg	41	41	66	103	103
Cooling mode working range		°C	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)
Heating mode working range		°C	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)
R-410A Refrigerant charge		kg	1.6	1.6	2.3	4.1	4.1
Minimum piping length		m	5	5	5	5	5
Maximum piping length without additional charge		m	30 (**)	30 (**)	30	30	30
Maximum piping length (required additional charge)		m (g/m)	50 (30)	50 (30) (***)	50 (40)	75 (60)	75 (60)
Maximum lift (OU up - OU down)		g/m	30/20	30/20	30/20	30/20	30/20
Liquid line piping diameter		inches (mm)	6.35 (1/4)	6.35 (1/4)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)
Gas line piping diameter		inches (mm)	12.7 (1/2)	12.7 (1/2)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)



# Commercial Outdoor Units



HITACHI is pleased to introduce its new range of IXV PREMIUM SERIES 1 outdoor units, today even more efficient and functional.

## MAIN FEATURES OF THE NEW RANGE

- Individual operation for each indoor unit
- Option to connect up to 8 indoor units of any type
- Indoor unit connection capacity ratio variable from 50% minimum to 120% maximum of the outdoor unit power (depending on power level)

- Option to connect indoor units with power equal to 0.8 HP
- Compliant with the new Eco Design directive EuP lot 10 and designed to have seasonal efficiency compliant with the European Directive in seasonal efficiency lot 6/21 in force from 2015.
- Compatibility with refrigerant piping for old R22 gas circuits.



UP TO -15°C  
IN COOLING  
MODE ONLY



COMPACT AND LIGHTWEIGHT

WIDE SCOPE OF APPLICATION

INDIVIDUAL CONTROL  
OF THE INDOOR UNIT

HIGH ENERGY EFFICIENCY

The specified cooling and heating capacities refer to outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

(1) Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

(2) Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

(3) Sound pressure level measured at 1.5 metres below the unit in anechoic room with no reflection.

(4) Performance is calculated based on combination with model RCI indoor units

(\*) Data not supplied as they are not covered by Lot 10 of ErP regulations

(\*\*) 0 metres in the event of two indoor units

(\*\*\*) In the event of two indoor units, additional charge must be equal to 24g/m

## UTOPIA IXV PREMIUM TECHNICAL SPECIFICATIONS

CODE		RAS 5HVN1P1E	RAS 5HNP1E	RAS 6HVN1P1E	RAS 6HNP1E	RAS 8HNPE	RAS 10HNPE	RAS 12HNPE
Power Supply	V/Ph/Hz	1 - 220V 50Hz	3N - 400V 50Hz	1 - 220V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz	3N - 400V 50Hz
Nominal cooling capacity (1)	kW	12.5 (5.7-14.0)	12.5 (5.7-14.0)	14 (6.0-16)	14.0 (6.0-16.0)	20.0 (8.0-22.4)	25.0 (10.0-28.0)	30.0 (11.2-33.5)
Nominal heating capacity (2)	kW	14.0 (5.0-18.0)	14.0 (5.0-18.0)	16.0 (5.0-20.0)	16.0 (5.0-20.0)	22.4 (6.3-28.0)	28.0 (8.0-35.0)	33.5 (9.0-37.5)
Nominal Power Input (Cool. / Heat.)	A	13.7 / 12.8	5.0 / 4.7	17.3 / 15.9	6.3 / 5.8	8.6 / 8.1	12.6 / 11.3	17.5 / 14.2
Input power at nominal cap. (Cool. / Heat.)	kW	3.11 / 2.91	3.11 / 2.91	3.94 / 3.61	3.94 / 3.61	5.36 / 5.06	7.88 / 7.03	11.05 / 8.96
Max. input current	A	30.5	14.0	30.5	16.0	24	24	24.3
EER/COP (4)		3.81 / 4.55	3.81 / 4.55	3.41 / 4.23	3.41 / 4.23	3.56 / 4.21	3.07 / 3.84	2.65 / 3.64
SEER	W/W	*	*	*	*	*	*	*
Cooling energy efficiency class		*	*	*	*	*	*	*
P Design (35°C)	kW	*	*	*	*	*	*	*
AVERAGE Climate	SCOP	W/W	*	*	*	*	*	*
	Heating energy efficiency class		*	*	*	*	*	*
	P Design (-10°C)	kW	*	*	*	*	*	*
Min-max connectible capacity	%	50-120	50-120	50-120	50-120	50-120	50-120	50-120
Min-max indoor units connected	No.	1-6	1-6	1-6	1-6	1-8	1-8	1-8
Sound Pressure Cooling/Heating (Night Mode) (3)	dB(A)	48-50 (44)	48-50 (44)	48-50 (45)	48-50 (45)	57-59 (55)	58-60 (56)	59-61 (57)
Sound power level at nominal output	dB(A)	64	64	65	65	76	76	77
No. of fans	No.	2	2	2	2	2	2	2
Air flow rate (max.)	m³/h	5400	5400	6000	6000	7620	8040	9780
Dimensions (HxLxD)	mm	1380x950x370	1380x950x370	1380x950x370	1380x950x370	1380x950x370	1380x950x370	1650x1100x390
Weight	kg	103	103	103	103	136	138	168
Cooling mode working range	°C	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)
Heating mode working range	°C	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)
R-410A Refrigerant charge	kg	4.2	4.2	4.2	4.2	5.7	6.2	6.7
Minimum piping length	m	5	5	5	5	5	5	5
Maximum piping length without additional charge	m	30	30	30	30	30	30	30
Maximum piping length (required additional charge)	m (g/m)	75 (60)	75 (60)	75 (60)	75 (60)	100 (SEE TC)	100 (SEE TC)	100 (SEE TC)
Maximum lift (OU up - OU down)	g/m	30/20	30/20	30/20	30/20	30/20	30/20	30/20
Liquid line piping diameter	inches (mm)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	9.53 (3/8)	12.7 (1/2)	12.7 (1/2)
Gas line piping diameter	inches (mm)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	25.4 (1)	25.4 (1)	25.4 (1)

\* Data not supplied as the power levels are not covered by Lot 10 of the ErP Regulations



## IVX PREMIUM

### Prices of Mono Combinations

#### RCI - 4-WAY CASSETTE SERIES i (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-2.0FSN3Ei	P-N23NA	RAS-2HVNP1	220V-50Hz	5.82	A+	4.01	A+	3.6	4.1
RCI-2.5FSN3Ei	P-N23NA	RAS-2.5HVNP1	220V-50Hz	5.64	A+	4.36	A+	3.5	4.0
RCI-3.0FSN3Ei	P-N23NA	RAS-3HVNP1E	220V-50Hz	6.63	A++	4.00	A+	4.0	4.4
RCI-4.0FSN3Ei	P-N23NA	RAS-4HVNP1E	220V-50Hz	7.16	A++	4.25	A+	4.0	4.5
RCI-4.0FSN3Ei	P-N23NA	RAS-4HNP1E	380V-50Hz	6.98	A++	4.25	A+	4.0	4.5
RCI-5.0FSN3Ei	P-N23NA	RAS-5HVNP1E	220V-50Hz	*	*	*	*	3.5	3.9
RCI-5.0FSN3Ei	P-N23NA	RAS-5HNP1E	380V-50Hz	*	*	*	*	3.5	3.9
RCI-6.0FSN3Ei	P-N23NA	RAS-6HVNP1E	220V-50Hz	*	*	*	*	3.3	3.7
RCI-6.0FSN3Ei	P-N23NA	RAS-6HNP1E	380V-50Hz	*	*	*	*	3.3	3.7

#### RCI - 4-WAY CASSETTE SERIES k (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-2.0FSN3Ek	P-AP160NA1	RAS-2HVNP1	220V-50Hz	5.82	A+	4.01	A+	3.6	4.1
RCI-2.5FSN3Ek	P-AP160NA1	RAS-2.5HVNP1	220V-50Hz	5.64	A+	4.36	A+	3.5	4.0
RCI-3.0FSN3Ek	P-AP160NA1	RAS-3HVNP1E	220V-50Hz	6.63	A++	4.00	A+	4.0	4.4
RCI-4.0FSN3Ek	P-AP160NA1	RAS-4HVNP1E	220V-50Hz	7.16	A++	4.25	A+	4.0	4.5
RCI-4.0FSN3Ek	P-AP160NA1	RAS-4HNP1E	380V-50Hz	6.98	A++	4.25	A+	4.0	4.5
RCI-5.0FSN3Ek	P-AP160NA1	RAS-5HVNP1E	220V-50Hz	*	*	*	*	3.5	3.9
RCI-5.0FSN3Ek	P-AP160NA1	RAS-5HNP1E	380V-50Hz	*	*	*	*	3.5	3.9
RCI-6.0FSN3Ek	P-AP160NA1	RAS-6HVNP1E	220V-50Hz	*	*	*	*	3.3	3.7
RCI-6.0FSN3Ek	P-AP160NA1	RAS-6HNP1E	380V-50Hz	*	*	*	*	3.3	3.7

NOTE: the unit is compatible also with cover panel fitted with motion sensor - cod. P-AP160NAE

#### RCI - 4-WAY HIGH EFFICIENCY CASSETTE (90x90)

Indoor Unit		Outdoor Unit		Performance					
model	panel	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RCI-2.0FSN3	P-AP160NA1	RAS-2HVNP1	220V-50Hz	6.49	A++	4.67	A++	4.0	4.7
RCI-2.5FSN3	P-AP160NA1	RAS-2.5HVNP1	220V-50Hz	6.05	A+	4.77	A++	4.2	4.9
RCI-3.0FSN3	P-AP160NA1	RAS-3HVNP1E	220V-50Hz	7.42	A++	4.37	A+	4.5	4.9
RCI-4.0FSN3	P-AP160NA1	RAS-4HVNP1E	220V-50Hz	7.88	A++	4.68	A++	4.7	5.2
RCI-4.0FSN3	P-AP160NA1	RAS-4HNP1E	380V-50Hz	7.66	A++	4.68	A++	4.7	5.2
RCI-5.0FSN3	P-AP160NA1	RAS-5HVNP1E	220V-50Hz	*	*	*	*	3.8	4.6
RCI-5.0FSN3	P-AP160NA1	RAS-5HNP1E	380V-50Hz	*	*	*	*	3.8	4.6
RCI-6.0FSN3	P-AP160NA1	RAS-6HVNP1E	220V-50Hz	*	*	*	*	3.4	4.2
RCI-6.0FSN3	P-AP160NA1	RAS-6HNP1E	380V-50Hz	*	*	*	*	3.4	4.2

NOTE: the unit is compatible also with cover panel fitted with motion sensor - cod. P-AP160NAE

#### RPI - DUCTED

Indoor Unit		Outdoor Unit		Performance					
model		model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPI-2.0FSN4E		RAS-2HVNP1	220V-50Hz	5.83	A+	4.01	A+	3.5	3.8
RPI-2.5FSN4E		RAS-2.5HVNP1	220V-50Hz	5.60	A+	4.41	A+	3.5	3.8
RPI-3.0FSN4E		RAS-3HVNP1E	220V-50Hz	6.54	A++	4.04	A+	3.6	4.0
RPI-4.0FSN4E		RAS-4HVNP1E	220V-50Hz	7.21	A++	4.47	A+	4.2	4.2
RPI-4.0FSN4E		RAS-4HNP1E	380V-50Hz	7.02	A++	4.47	A+	4.2	4.2
RPI-5.0FSN4E		RAS-5HVNP1E	220V-50Hz	*	*	*	*	3.6	4.0
RPI-5.0FSN4E		RAS-5HNP1E	380V-50Hz	*	*	*	*	3.6	4.0
RPI-6.0FSN4E		RAS-6HVNP1E	220V-50Hz	*	*	*	*	3.2	3.7
RPI-6.0FSN4E		RAS-6HNP1E	380V-50Hz	*	*	*	*	3.2	3.7
RPI-8.0FSN3E		RAS-8HNPE	380V-50Hz	*	*	*	*	3.1	3.3
RPI-10.0FSN3E		RAS-10HNPE	380V-50Hz	*	*	*	*	2.9	3.2

\* DATA NOT SUPPLIED AS THE POWER LEVELS ARE NOT COVERED BY LOT 10 OF THE ERP DIRECTIVE

# Commercial Outdoor Units



## RPC - CEILING

Indoor Unit		Outdoor Unit		Performance				
model	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPC-2.0FSN3E	RAS-2HVNP1	220V-50Hz	5.05	B	3.80	A	3.5	2.9
RPC-2.5FSN3E	RAS-2.5HVNP1	220V-50Hz	4.66	B	3.80	A	3.0	2.9
RPC-3.0FSN3E	RAS-3HVNP1E	220V-50Hz	5.33	A	3.80	A	3.4	3.4
RPC-4.0FSN3E	RAS-4HVNP1E	220V-50Hz	5.92	A+	3.81	A	3.6	3.6
RPC-4.0FSN3E	RAS-4HNP1E	380V-50Hz	5.80	A+	3.81	A	3.6	3.6
RPC-5.0FSN3E	RAS-5HVNP1E	220V-50Hz	*	*	*	*	3.1	3.5
RPC-5.0FSN3E	RAS-5HNP1E	380V-50Hz	*	*	*	*	3.1	3.5
RPC-6.0FSN3E	RAS-6HVNP1E	220V-50Hz	*	*	*	*	2.8	3.3
RPC-6.0FSN3E	RAS-6HNP1E	380V-50Hz	*	*	*	*	2.8	3.3

## RPC - HIGH EFFICIENCY CEILING

Indoor Unit		Outdoor Unit		Performance				
model	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPC-2.0FSN3	RAS-2HVNP1	220V-50Hz	5.63	A+	4.44	A+	3.7	4.1
RPC-2.5FSN3	RAS-2.5HVNP1	220V-50Hz	5.49	A	4.49	A+	4.0	4.1
RPC-3.0FSN3	RAS-3HVNP1E	220V-50Hz	5.87	A+	4.00	A+	3.7	4.2
RPC-4.0FSN3	RAS-4HVNP1E	220V-50Hz	6.53	A++	4.23	A+	4.5	4.4
RPC-4.0FSN3	RAS-4HNP1E	380V-50Hz	6.38	A++	4.23	A+	4.5	4.4
RPC-5.0FSN3	RAS-5HVNP1E	220V-50Hz	*	*	*	*	3.4	4.1
RPC-5.0FSN3	RAS-5HNP1E	380V-50Hz	*	*	*	*	3.4	4.1
RPC-6.0FSN3	RAS-6HVNP1E	220V-50Hz	*	*	*	*	3.1	3.9
RPC-6.0FSN3	RAS-6HNP1E	380V-50Hz	*	*	*	*	3.1	3.9

## RPK - WALL









Indoor Unit		Outdoor Unit		Performance				
model	model	power supply	SEER	SEER Class	SCOP	SCOP Class	EER	COP
RPK-2.0FSN3M	RAS-2HVNP1	220V-50Hz	5.47	A	4.01	A+	2.9	3.2
RPK-2.5FSN3M	RAS-2.5HVNP1	220V-50Hz	5.24	A	4.14	A+	3.0	3.2
RPK-3.0FSN3M	RAS-3HVNP1E	220V-50Hz	6.40	A++	3.91	A	3.3	3.4
RPK-4.0FSN3M	RAS-4HVNP1E	220V-50Hz	6.81	A++	3.81	A	3.6	3.4
RPK-4.0FSN3M	RAS-4HNP1E	380V-50Hz	6.64	A++	3.81	A	3.6	3.4

\* DATA NOT SUPPLIED AS THE POWER LEVELS ARE NOT COVERED BY LOT 10 OF THE ERP DIRECTIVE



## UTOPIA IVX PREMIUM

### Multi Combinations

IVX PREMIUM									
CODE	Minimum power level indoor unit connectible	Maximum number of indoor units connectible	1 unit	2 units	3 units				
					TRIAL CONFIGURATION		IN LINE CONFIGURATION		
									
Combination	Combination	Joints	Combination	Joints	Combination	Joints			
RAS 2HVPN1E (**)	0,8HP	2	90-110% FROM 1.8 TO 2.2HP	90-100% (*) FROM 1.8 TO 2HP	TW-22AN	NOT POSSIBLE			
RAS 2.5HVPN1E (***)	0,8HP	2	90-110% FROM 2.25 TO 2.75HP	90-100% (*) FROM 2.25 TO 2.5HP	TW-22AN	NOT POSSIBLE			
RAS 3HVPN1E	0,8HP	3	50-120% FROM 1.5 TO 3.6HP	50-120% FROM 1.5 TO 3.6HP	TW-52AN	50-100% (*) FROM 1.5 TO 3HP	TG-53AN	50-100% (*) FROM 1.5 TO 3HP	2 x E-102SN3
RAS 4H(V)NP1E	0,8HP	5	50-120% FROM 2 TO 4.8HP	50-120% FROM 2 TO 4.8HP	TW-52AN	50-120% FROM 2 TO 4.8HP	TG-53AN	50-120% FROM 2 TO 4.8HP	2 x E-102SN3
RAS 5H(V)NP1E	0,8HP	6	50-120% FROM 2.5 TO 6.6HP	50-120% FROM 2.5 TO 6.6HP	TW-52AN	50-120% FROM 2.5 TO 6.6HP	TG-53AN	50-120% FROM 2.5 TO 6.6HP	2 x E-102SN3
RAS 6H(V)NP1E	0,8HP	6	50-120% FROM 3 TO 7.2HP	50-120% FROM 3 TO 7.2HP	TW-52AN	50-120% FROM 3 TO 7.2HP	TG-53AN	50-120% FROM 3 TO 7.2HP	2 x E-102SN3
RAS 8HNPE	0,8HP	8	50-120% FROM 4 TO 9.6HP	50-120% FROM 4 TO 9.6HP	TW-102AN	50-120% FROM 4 TO 9.6HP	TG-103AN	50-120% FROM 4 TO 9.6HP	1 x E-162SN3 + 1 x E-102SN3
RAS 10HNPE	0,8HP	8	50-120% FROM 5 TO 12HP	50-120% FROM 5 TO 12HP	TW-102AN	50-120% FROM 5 TO 12HP	TG-103AN	50-120% FROM 5 TO 12HP	1 x E-162SN3 + 1 x E-102SN3
RAS 12HNP	0,8HP	8	50-120% FROM 6 TO 14.4HP	50-120% FROM 6 TO 14.4HP	TW-102AN	50-120% FROM 6 TO 14.4HP	TG-103AN	50-120% FROM 6 TO 14.4HP	1 x E-162SN3 + 1 x E-102SN3

IVX PREMIUM								
CODE	Minimum power level indoor unit connectible	Maximum number of indoor units connectible	4 units				5 units	
			QUAD CONFIGURATION		IN LINE CONFIGURATION		IN LINE CONFIGURATION	
			Combination	Joints	Combination	Joints	Combination	Joints
RAS 2HVPN1E (**)	0.8HP	2	NOT POSSIBLE				NOT POSSIBLE	
	0.8HP	2	NOT POSSIBLE				NOT POSSIBLE	
	0.8HP	3	NOT POSSIBLE				NOT POSSIBLE	
RAS 2.5HVPN1E (***)	0.8HP	5	50-120% FROM 2 TO 4.8HP	First joint: TW-52AN Second joint: If power downstream ≤ 1.5HP: TW-22AN If power downstream ≥ 1.8HP: TW-52AN	50-120% FROM 2 TO 4.8HP	3 x E-102SN3	50-100% (*) FROM 2 TO 4HP	4 x E 102SN3
RAS 5H(V)NP1E	0.8HP	6	50-120% FROM 2.5 TO 6.6HP	First joint: TW-52AN Second joint: If power downstream ≤ 2.0HP: TW-22AN If power downstream ≥ 1.8HP: TW-52AN	50-120% FROM 2.5 TO 6.6HP	3 x E-102SN3	50-100% (*) FROM 2.5 TO 5HP	4 x E 102SN3
RAS 6H(V)NP1E	0.8HP	6	50-120% FROM 3 TO 7.2HP	First joint: TW-52AN Second joint: If power downstream ≤ 2.0HP: TW-22AN If power downstream ≥ 1.8HP: TW-52AN	50-120% FROM 3 TO 7.2HP	3 x E-102SN3	50-100% (*) FROM 3 TO 6HP	4 x E 102SN3
RAS 8HNPE	0.8HP	8	50-120% FROM 4 TO 9.6HP	First joint: TW-102AN Second joint: If power downstream ≤ 2.0HP: TW-22AN If power downstream ≥ 1.8HP: TW-52AN	50-120% FROM 4 TO 9.6HP	2 x E-162SN3 + 1 x E-102SN3	50-100% (*) FROM 4 TO 8HP	3 x E-162SN3 + 1 x E-102SN3
RAS 10HNPE	0.8HP	8	50-120% FROM 5 TO 12HP	First joint: TW-102AN Second joint: If power downstream ≤ 2.0HP: TW-22AN If power downstream ≥ 1.8HP: TW-52AN	50-120% FROM 5 TO 12HP	2 x E-162SN3 + 1 x E-102SN3	50-100% (*) FROM 5 TO 10HP	3 x E-162SN3 + 1 x E-102SN3
RAS 12HNP	0.8HP	8	50-120% FROM 6 TO 14.4HP	First joint: TW-102AN Second joint: If power downstream ≤ 2.0HP: TW-22AN If power downstream ≥ 1.8HP: TW-52AN	50-120% FROM 6 TO 14.4HP	2 x E-162SN3 + 1 x E-102SN3	50-100% (*) FROM 6 TO 12HP	3 x E-162SN3 + 1 x E-102SN3

IVX PREMIUM								
CODE	Minimum power level indoor unit connectible	Maximum number of indoor units connectible	6 units		7 units		8 units	
			IN LINE CONFIGURATION		IN LINE CONFIGURATION		IN LINE CONFIGURATION	
			Combination	Joints	Combination	Joints	Combination	Joints
RAS 2HVPN1E (**)	0.8HP	2	NOT POSSIBLE		NOT POSSIBLE		NOT POSSIBLE	
	0.8HP	2	NOT POSSIBLE		NOT POSSIBLE		NOT POSSIBLE	
RAS 2.5HVPN1E (***)	0.8HP	3	NOT POSSIBLE		NOT POSSIBLE		NOT POSSIBLE	
	0.8HP	5	NOT POSSIBLE		NOT POSSIBLE		NOT POSSIBLE	
RAS 5H(V)NP1E	0.8HP	6	50-100% (*) FROM 2.5 TO 5HP	5 x E102SN3	50-100% (*) FROM 2.5 TO 5HP	6 x E102SN3	50-100% (*) FROM 2.5 TO 5HP	7 x E102SN3
RAS 6H(V)NP1E	0.8HP	6	50-100% (*) FROM 3 TO 6HP	5 x E102SN3	50-100% (*) FROM 3 TO 6HP	6 x E102SN3	50-100% (*) FROM 3 TO 6HP	7 x E102SN3
RAS 8HNPE	0.8HP	8	50-100% (*) FROM 4 TO 8HP	4 x E-162SN3 + 1 x E-102SN3	50-100% (*) FROM 4 TO 8HP	5 x E-162SN3 + 1 x E-102SN3	50-100% (*) FROM 4 TO 8HP	6 x E-162SN3 + 1 x E-102SN3
RAS 10HNPE	0.8HP	8	50-100% (*) FROM 5 TO 10HP	4 x E-162SN3 + 1 x E-102SN3	50-100% (*) FROM 5 TO 10HP	5 x E-162SN3 + 1 x E-102SN3	50-100% (*) FROM 5 TO 10HP	6 x E-162SN3 + 1 x E-102SN3
RAS 12HNP	0.8HP	8	50-100% (*) FROM 6 TO 12HP	4 x E-162SN3 + 1 x E-102SN3	50-100% (*) FROM 6 TO 12HP	5 x E-162SN3 + 1 x E-102SN3	50-100% (*) FROM 6 TO 12HP	6 x E-162SN3 + 1 x E-102SN3

(\*) See options in table 1 - (\*\*) In the event of using RCI-FSN3 or RCI-FSN3Ei indoor units, only the MONO combination is allowed

(\*\*\*) In the event of installing indoor units in combination with RCI-FSN3 or RCI-FSN3Ei units, the minimum installed capacity must not be less than 1.5HP





## Remarks

<sup>1</sup> **TABLE 1:** In case of multiple systems, refer to the table below concerning connection of minimum power indoor units with indoor units.

Maximum power level indoor unit in the system	HP	0.8	1.0	1.3	1.5	1.8	2.0	2.3	2.5	3.0	4.0	5.0	6.0
Minimum power level indoor unit allowed in the system	HP	0.8				1.0			1.3		1.5	1.8	2.0

<sup>2</sup> **TABLE 2:** In systems where indoor unit are all RCI-FSN3 models, the maximum allowed capacity ratio is 100% and the maximum number of indoor units is as follows:

Outdoor unit model	HP	2	2.5	3	4	5	6	8	10	12
IVX PREMIUM	No.	1		2	4			4		

<sup>3</sup> When installing model RCIM 2.0FSN3, RPF(I) 2.0FSN2E or RPF(I) 2.5FSN2E indoor units, the MONO combination with UTOPIA IVX and IVX PREMIUM outdoor units is not allowed

<sup>4</sup> In case of installation in cold areas (where the outside temperature might reach -10°C) or in areas with high heating demands, do not install a higher number of indoor units than recommended and assure a capacity ratio lower than 100%.

## System sizing

Mono, dual, trial, double twin configuration

### Maximum length of refrigerant piping


Outdoor unit		2HP	2.5HP	3HP	4HP	5HP	6HP	8HP	10HP	12HP
Maximum piping length between the outdoor unit and the furthest indoor unit	Actual length (L1)	50			75			100		
	Equivalent length (EL)	70			95			125		
Maximum piping length	2 units (A+B+C)	50	60		85			100	115	
	3 units (A+B+C+D)	-			95			100	130	
	4 units (B+D, B+E, C+F, C+G)	-			95			100	145	
Maximum piping length after the first joint	2 e 3 units (B,C,D)	10						15		
	4 units (B+D, B+E, C+F, C+G)	-			10			15		
Main piping length (A)		A > B, C, D, E, F, G								
Maximum height difference between outdoor unit and indoor unit	Outdoor up	30								
	Outdoor down	20								
Maximum height difference between indoor units		3			10					
Maximum height difference Joint/indoor unit (2, 3 and 4 indoor units) Joint/joint (4 indoor units)		3								
(B-C)/(B-D)/(C-D)/(C+G)-(B+E)/(C+G)-(B+D)/(C+F)-(B+E)/(C+F)-(B+D)		< 8								



## UTOPIA IVX PREMIUM


### Selection of refrigerant piping section and distribution joints

**MONO System** (one indoor unit)



Outdoor unit capacity HP	Piping section (L)	
	Gas	Liquid
2/2.5	Ø 12.70	Ø 6.35
3/4/5/6	Ø 15.88	Ø 9.52
8	Ø 25.40	Ø 9.52
10/12	Ø 25.40	Ø 12.70


**DUAL System** (two indoor units)



Outdoor unit capacity HP	Piping section (A)		Joints
	Gas	Liquid	
2/2.5	Ø 12.70	Ø 6.35	TW-22AN
3	Ø 15.88	Ø 9.52	TW-52AN
4	Ø 15.88	Ø 9.52	TW-52AN
5/6	Ø 15.88	Ø 9.52	TW-52AN
8	Ø 25.40	Ø 9.52 (1)	TW-102AN
10/12	Ø 25.40	Ø 12.70	TW-102AN

(1) In the event the total piping length should exceed 70 metres for 8HP outdoor unit, use liquid piping with section 12.7.

**TRIAL System** (three indoor units)



Outdoor unit capacity HP	Piping section (A)		Joints
	Gas	Liquid	
4/5/6	Ø 15.88	Ø 9.52	TG-53AN
8	Ø 24.40	Ø 9.52 (1)	TG-103AN
10/12	Ø 24.40	Ø 12.70	TG-103AN


(1) In the event the piping length (A+B or A+C or A+D) should exceed 70 metres for the 8HP outdoor unit, use liquid piping with section 12.7.

Indoor unit capacity HP	Piping section (B, C, D)	
	Gas	Liquid
≤ 1.5HP	Ø 12.70	Ø 6.35
1.8/2.0HP	Ø 15.88	Ø 6.35
≥ 2.3HP	Ø 15.88	Ø 9.52

# Commercial Outdoor Units



**DOUBLE TWIN System**(four indoor units)



Outdoor unit capacity HP	Piping section (A)		Joint 1
	Gas	Liquid	
4	Ø 15.88	Ø 9.52	TW-52AN
5/6	Ø 15.88	Ø 9.52	TW-52AN
8	Ø 25.40	Ø 9.52 (1)	TW-102AN
10/12	Ø 25.40	Ø 12.70	TW-102AN

(1) In the event the piping length (A+B+D or A+B+E or A+C+F or A+C+G) should exceed 70 metres for the 8HP outdoor unit, use liquid piping with section 12.7.

Total capacity of indoor units 1+2 or 3+4	Piping section (B, C)		Joint 2
	Gas	Liquid	
≤ 1.5HP	Ø 12.70	Ø 6.35	TW-22AN
1.8/2.0HP	Ø 15.88	Ø 6.35	TW-52AN
≥ 2.3HP	Ø 15.88	Ø 9.52	TW-52AN

If the capacity ratio between the sets of indoor units 1+2 and 3+4 exceeds 60/40% make an installation with "in line configuration".

Indoor unit capacity HP	Piping section (D, E, F, G)	
	Gas	Liquid
≤ 1.5HP	Ø 12.70	Ø 6.35
1.8/2.0HP	Ø 15.88	Ø 6.35
≥ 2.3HP	Ø 15.88	Ø 9.52

## Configuration in line

### Maximum length of refrigerant piping


Outdoor unit		3HP	4HP	5HP	6HP	8HP	10HP	12HP
Maximum piping length between the outdoor unit and the furthest indoor unit	Actual length (L1)	50	75			100		
	Equivalent length (EL)	70	95			125		
Maximum piping length between the first joint and every indoor unit (L2)		20	30			40		
Maximum piping length from joint to indoor unit (L3)		10				15		
Total piping length L4+(L3 <sub>1</sub> +L3 <sub>2</sub> +L3 <sub>3</sub> ...)		60	95			100	145	
Maximum height difference between outdoor unit and indoor unit	Outdoor up	30						
	Outdoor down	20						
Maximum height difference between indoor units		10						
Maximum height difference	Joint/Indoor unit	3						
	Joint/joint	3						



# Commercial Outdoor Units

## UTOPIA IVX PREMIUM

### Selection of refrigerant piping section and distribution joints



Outdoor unit capacity HP	Piping section (C, D) (L4)		Joints A	Joints B
	Gas	Liquid		
3/4/5/6	Ø 15.88	Ø 9.52	E-102SN3	E-102SN3
8	Ø 25.40	Ø 9.52 (1)	E-162SN3	E-102SN3
10/12	Ø 25.40	Ø 12.70	E-162SN3	E-102SN2

(1) In the event the total piping length from outdoor unit to the furthest indoor unit should exceed 70 metres for the 8HP outdoor unit, use liquid piping with section 12.70.

Indoor unit capacity HP	Piping section (L3)	
	Gas	Liquid
≤ 1.5HP	Ø 12.70	Ø 6.35
1.8/2.0HP	Ø 15.88	Ø 6.35
≥ 2.3HP	Ø 15.88	Ø 9.52

### Combinations of piping section/length

Capacity	Liquid Gas	Ø6.35				Ø9.53					Ø12.70					Ø15.88		
		Ø9.53	Ø12.70	Ø15.88	Ø19.05	Ø12.70	Ø15.88	Ø19.05	Ø22.20	Ø25.40	Ø15.88	Ø19.05	Ø22.20	Ø25.40	Ø28.60	Ø22.30	Ø25.40	Ø28.60
2HP		15 <sup>(1)</sup>	50	30	-	15 <sup>(3)</sup>	15 <sup>(3)</sup>	-	-	-	-	-	-	-	-	-	-	-
2.5HP		-	50	30	-	20 <sup>(3)</sup>	20 <sup>(3)</sup>	-	-	-	-	-	-	-	-	-	-	-
3HP		-	30 <sup>(1)(2)</sup>	30 <sup>(2)</sup>	-	30 <sup>(1)</sup>	50	-	-	-	-	-	-	-	-	-	-	-
4-5-6HP		-	-	5 <sup>(2)</sup>	5 <sup>(2)</sup>	40 <sup>(1)</sup>	75	50 <sup>(4)</sup>	-	-	30 <sup>(3)</sup>	30 <sup>(3)(4)</sup>	-	-	-	-	-	-
8HP		-	-	-	-	-	-	50 <sup>(1)(4)(6)</sup>	50 <sup>(1)(6)</sup>	70 <sup>(5)</sup>	-	50 <sup>(1)(3)(4)</sup>	50 <sup>(1)(3)</sup>	100	-	50 <sup>(1)(3)</sup>	50 <sup>(3)</sup>	-
10HP		-	-	-	-	-	-	-	-	-	-	-	-	100	50	50 <sup>(1)(3)</sup>	50 <sup>(3)</sup>	50 <sup>(3)</sup>

(1) If the gas line diameter is reduced, cooling performance decreases and the operative range is reduced since the line's pressure loss increases.

(2) If the liquid line diameter is reduced, capacity of the indoor unit's expansion valve is reduced.

(3) If the liquid line size is increased, refrigerant must be added.

(4) In the event the gas piping section is 19.05, move to the ON position pin no. 4 of switch DSW2 on the electronic board of the outdoor unit.

(5) In the event the piping length should exceed 70m for the 8HP power level, use section 12.7 for the liquid piping

(6) In the event more than 5 indoor units should be connected for the 8HP power level, use section 12.7 for liquid piping



Standard specification

Please refer to page 184 to check accessories



# Commercial Outdoor Units







# VRF Set Free outdoor units

## Outdoor units

### Utopia Range

**Utopia ES** ( Simultaneous Indoor Unit Operation)

**Utopia IVX STANDARD** ( Independent Indoor Unit Operation)

**Utopia IVX PREMIUM** ( Independent Indoor Units)

**Utopia RASC IVX** ( Independent Indoor Unit Operation)

Compatible with the same remote controllers

### Set Free Range

**IVX PREMIUM** Independent Indoor Unit Operation)






**FSVN2E & FSNY2E**

**FSNM VRF Side Flow**

**FSXN VRF 2 or 3 Pipes**

**FSXNH VRF 2 or 3 Pipes** high efficiency

Compatible with the same remote controllers

OUTDOOR UNIT RANGE										
type	Capacity (HP)		4	5	6	8	10	12	14	16
Set Free Mini	<b>FS(V)N(Y)2E</b>		■	■	■					
	No. of Indoor Units		8	10	12					
Set Free Side Flow	<b>FSNM</b>					■	■	■		
	No. of Indoor Units					10	10	10		
Set Free 2 & 3 Pipes	<b>FSXN</b>					■	■	■	■	■
	No. of Indoor Units					14	18	21	26	29
Set Free 2 & 3 Pipes	<b>NEW FSXN1E</b>					■	■	■	■	■
	No. of Indoor Units					14	18	21	26	29
High efficiency Set Free 2 & 3 Pipes	<b>FSXNH</b>			■	■	■	■	■	■	■
	No. of Indoor Units			10	13	17	21	26	30	34






# VRF Set Free outdoor units

## SET FREE

It is difficult to do the simple things.  
SetFREE gives you freedom to decide,  
simply.



Often it is not necessary to know how a device works from the technical point of view, but it is often interesting to measure its value by noticing its performance as a positive influence in our everyday life and any work condition so that the people who **live in the environment**, always feel comfortable.

Therefore, it often happens that discussing **target frequencies, control and number of pulses for controlling the expansion valve, power input management might seem a mere exercise in style.**

Loyal to the history and origins of the first SetFREE systems, even today we assure the required thermal performance thanks to the adoption of some important features:

### ADAPTIVE CONTROL

The flexibility that Hitachi has chosen to give to its conditioning systems lies in the ability to set a variety of parameters by accessing adaptive functions which are programmed in the boards of outdoor units and in all indoor units. It is therefore possible to control up to 25 different operation parameters on the outdoor unit, or 17 external INPUT/OUTPUT signals.

On each indoor unit, on the other hand, are 31 selectable parameters and 11 external INPUT/OUTPUT signals.

### FOUR PROBES

Each indoor unit uses four probes for controlling its performance by measuring the temperature. Two of these are dedicated to measuring air temperature, the other two to measuring refrigerant temperature, the only solution on the market.

### EFFICIENCY AND PERFORMANCE

Choosing the "best route" to travel to reach the desired performance focusing either on speed in reaching the performance or system efficiency

### 2,000 POINT MODULATING LOGIC

Electronic expansion valve of the indoor unit adjusted by single pulse with modulating PID logic on 2,000 points for each indoor unit.

Two electronic expansion valves for each outdoor unit module

Primary battery: adjusted with single pulse and modulating on 2,950 points

Double pipe for liquid sub-cooling: adjusted in single and modulating on 480 points

### CONSTANT COMFORT

Monitoring the compressor's target frequency with independent mode for both operation modes (distinct strategies between hot and cold modes) to assure constant comfort when the outside temperature changes





## Why decide to have one thing only when you can have all of them at the same time?


Being loyal to the need for **service continuity, solidity of the products and technological innovation, represents the direction of technological development that HITACHI** has chosen to travel over the years and which has led it to introduce one model only of outdoor unit, installable either in Heat Pump or Heat Recovery systems.

### SEASONAL PERFORMANCE


The constant evolution of products, needed to address the requirements of the various Directives, regulations and Standards, makes it more and more necessary to provide constantly updated assessment instruments. From this point of view, being able to use online software makes it possible to always have timely, up-to-date assessments, aligned with the products launched on the market.

Hitachi's new Seasonal Efficiency calculation makes it immediately possible to quickly obtain SEER / SCOP parameters of the system, access the online list of already implemented projects, make a new one, obtain the technical-economic assessment of the designed system, know its thermal and electrical performance, etc.....

We would like to draw your attention to the high efficiency levels, among the highest on the market, and the possibility to make variable flow systems with an extremely wide range of required power, from 12.5 to 150,0 kW (cooling).



ESEER (1): Seasonal efficiency value in standard cooling





ESEER (2): Seasonal efficiency value in cooling mode with optimised system operation based on seasonal demand

### SOLIDITY AND EFFICIENCY

the use of the individual High Pressure Scroll Inverter compressor produced by HITACHI, which has marked the whole SetFREE range since 1982, has today been updated and has evolved.

The solidity of the electro-mechanical coupling makes it possible to use direct expansion systems also with significant height differences, up to 90 m height difference between outdoor and indoor units and up to 30m between indoor units.

Maintaining constant performance over time also stems from adopting an original control method of compressor oil recovery (trochoidal pump) which makes continuous lubrication possible even during low rotation speed operation.



**= +7% (efficiency)**




# VRF Set Free outdoor units

## SET FREE


- + Quality
- + Efficiency
- + Quietness
- = **3 year warranty after testing**
- +**3% (efficiency)**

The oil circuit is internal in each module, i.e. it does not need connections between outdoor units, and does not interfere in any way with the continuous 'thermal' requirement of the user. This fundamental function is also independent of the compressor's rotation speed and makes it possible to reach high reliability levels.



## MODULATION

With minimum compressor modulation of just 30 Hz, extended to all outdoor unit power levels, it is possible to manage the thermal demand of large and complex systems even when only one unit demands performance. This combination of individual thermal demand and frequent actual application for modern buildings needs to have small volume rooms, even the smallest 0.6 HP unit (1.7 kW) may be switched on and managed with no need to convey refrigerant to other units.




## REFRIGERANT CIRCUIT PERFORMANCE


Regulate, activate, control, why can't the system freely adapt to performance requirements?

In heating mode, in cooling mode, in other words, when it is required... Based on these considerations, Hitachi makes it possible to activate flexibility parameters for the electronics to adapt system performance to the specific demand, bypassing standard working settings.

This is why it is possible for the compressor to work in cooling mode, in heating mode or in both modes, in a more "decisive" manner to quickly reach the desired response.




The two adjustments (1 and 2) allow you to obtain the desired performance when it is needed.





## A MEASURE OF THE VALUE OF THESE FIGURES:

- The smallest connectible unit is the 0.6 HP (equivalent to 1.7 kW)
- Connected to a general 30 HP outdoor unit (equivalent to 85.0 kW)
- To obtain minimum modulation equal to 2% of the outdoor unit power




## TREATMENT OF OUTDOOR UNIT BATTERIES AGAINST WEATHERING

In compliance with Standard JRA 9002 which defines the Criteria and tests for protection against weather corrosion of outdoor units, in addition to standard protection, Hitachi offers two more surface treatments (defined ANTI-CORROSIVE and HEAVY ANTI-CORROSIVE) which increase the degree of resistance of cooling parts and relevant structural metal parts.

Tests performed at the following conditions

1. 35°C with salt solution 5% at 95%RH  
Duration: 480 hours  
In compliance with regulation DIN50021-SS
2. Humidity resistance: 50°C at 98%RH  
Duration: 500 hours



The following diagram lets you choose the most suitable protection degree depending on the features of the unit's installation site

Type of Treatment	Protected components			
	metal work and load bearing structure	heat exchanger	motor fastening	screws
Standard	covered with Zinc Sulphate and polyester resin $\geq 20 \mu\text{m}$	standard	-	GEOMET ® treatment
ANTI-CORROSION	covered with Zinc Sulphate thickness $\geq 30 \mu\text{m}$	covered with clear synthetic acrylic resin $\geq 10 \mu\text{m}$	covered with Zinc Sulphate thickness $\geq 30 \mu\text{m}$	GEOMET ® treatment
HEAVY ANTI-CORROSION	covered with Zinc Sulphate thickness $\geq 45 \mu\text{m}$	covered with clear synthetic acrylic resin $\geq 10 \mu\text{m}$ + covered with Zinc Sulphate thickness $\geq 45 \mu\text{m}$ of the bundle	covered with Zinc Sulphate thickness $\geq 45 \mu\text{m}$	GEOMET ® treatment



## SET FREE

### Winter comfort


The modules of Set Free units help you manage the defrosting phases in a differentiated way depending on the type of system, Heat Pump or Heat Recovery.

In the Heat Recovery application with several modules, these behave independently from each other, that is to say there is continuity of operation.

For both types of systems the response of the system and the indoor units can be tailored to different environmental conditions, both in terms of indoor and outdoor temperatures, choosing whether to enable or disable the following settings:

- Activate the modification function of defrost thermal areas
  - Defrosting is thus bound to outside temperatures other than standard
- Activate the selection function of indoor unit ventilation speed during defrosting
  - It lets you manage the "superlow" speed function of indoor units in order to avoid negative effects on uniform distribution of ambient temperature
- Activate the selection function of indoor unit ventilation speed when going back to heating mode
  - It allows you to prevent stratification phenomena detectable when going back to heating mode of indoor units
  - The indoor units restart at the speed defined as "superlow" avoiding undesired phenomena


### AUTOMATIC CONTROL OF REFRIGERANT CHARGE



### AUTOMATIC CONTROL OF REFRIGERANT CHARGE

Checking the correct amount of refrigerant in the system can be done in an extremely wide range of temperatures:

- Outside temperature: from 0 to 43°C
- Inside temperature: from 10 to 32°C









## OUTCOME OF AUTOMATIC TEST

The procedure is activated by accessing the electronic board of the outdoor unit and may have a duration between 30 min and 40 min. At the end of the test a synthetic message is provided to allow the support service to have the certainty that the amount of refrigerant is correct, low or exceeding the required amount.



## AIR FLOW MANAGEMENT

Very often it is necessary to adapt the performance of the outdoor unit to the external environment in which the unit is operating. In actual applications it is very useful to have significant static head pressure, 60 Pa available with 130% load index, in order to size suitable discharge hoods.





# VRF Set Free outdoor units

## SET FREE MINI

### DC inverter Heat pump



RAS 4FSVN2E  
RAS 4FSNY2E  
RAS 5FSVN2E  
RAS 5FSNY2E  
RAS 6FSVN2E  
RAS 6FSNY2E



SMALL SIZE  
HORIZONTAL EJECTION  
2 PIPE SYSTEM  
OPTIONAL INPUTS/OUTPUTS

Multi heat pump systems with scroll compressor DC Inverter 2 pipes.



- Cooling capacity from 11.2kW (4HP) to 15.5kW (6HP)
- 3 available power levels
- Up to 9 connectible indoor units, controlled independently
- Compact size
- Minimum Sound Pressure: 42dB(A)
- High energy efficiency
- Cooling up to -5°C, heating up to -20°C
- New DC Scroll Inverter Compressor

### Features and advantages

- Improved reliability.
- Leaks in intake and delivery greatly reduced by means of new asymmetric scroll profile.
- Heat loss greatly reduced by means of the new oil return structure.
- Accurate lubrication to the compressor through a new oil distribution system.

- Thanks to compressor DC power supply, performance improves around the frequency range 30-40Hz, where the operation time of the inverter compressor is normally the longest. Moreover, to eliminate interference of electromagnetic noise and achieve lower noise, the motor has been divided into two and the electric pole has been moved.

- High efficiency heat exchanger, it recovers the residual heat of the refrigerant, increasing the useful area of the cooling cycle and improving efficiency.



# VRF Set Free outdoor units



## TECHNICAL SPECIFICATIONS

CODE		RAS 4 FSVNE	RAS 4 FSNY2E	RAS 5 FSNV2E	RAS 5 FSNY2E	RAS 6 FSNV2E	RAS 6 FSNY2E
Power supply	V/Ph/Hz	1F 230V 50Hz	3N 380/415 50Hz	1F 230V 50Hz	3N 380/415 50Hz	1F 230V 50Hz	3N 380/415 50Hz
Cooling nominal capacity (1)	kW	11.2 (5.60-11.2)	11.2 (5.60-11.2)	14.0 (7.00-14.0)	14.0 (7.00-14.0)	15.5 (7.8-15.5)	15.5 (7.8-15.5)
Heating nominal capacity (2)	kW	12.5 (6.3-12.5)	12.5 (6.3-12.5)	16.0 (8.00-16.0)	16.0 (8.00-16.0)	18.0 (9.00-18.0)	18.0 (9.00-18.0)
Cooling operating current	A	12.2	4.1	17.2	5.8	20.7	7.0
Heating operating current	A	13.4	4.6	18.6	6.3	21.7	7.44
Power consumption at nominal cap. (Cool. / Heat.)	kW	2.75/3.03	2.72/3.00	3.88/4.20	3.84/4.16	4.67-4.90	4.62/4.85
Max current consumption	A	26	13	26	13	26	13
EER / COP	W/W	4.07/4.13	4.12/4.17	3.61/3.81	3.65/3.85	3.32/3.67	3.35/3.71
Energy class		A/A	A/A	A/A	A/A	A/A	A/A
Min – max connectable capacity		50-130	50-130	50-130	50-130	50-130	50-130
No. min – max inside	N.	1-6	1-6	1-8	1-8	1-9	1-9
Sound Pressure Cooling/Heating (Night Mode) (3)	dB(A)	49/___ (45)	49/___ (45)	51/___ (47)	51/___ (47)	51/___ (48)	51/___ (48)
Sound Pressure at nominal output (Cool. / Heat.)	dB(A)	51	51	53	53	53	53
Number of fans	n.	2	2	2	2	2	2
	m³/h	5400	5400	5400	5400	6000	6000
Fan static pressure	Pa	ND	ND	ND	ND	ND	ND
Dimensions (H x W x D)	mm	1380x950x370	1380x950x370	1380x950x370	1380x950x370	1380x950x370	1380x950x370
Weight	kg	100	102	100	102	100	102
Cooling working range	°C	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)	-5 / +46 (BS)
Heating working range	°C	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)
Refrigerant R-410A charge	kg	3.6	3.6	3.6	3.6	3.6	3.6
Maximum piping length	m	75	75	75	75	75	75
Maximum level difference (high OU – low OU)	g/m	30/30	30/30	30/30	30/30	30/30	30/30
Max length refrigerant lines (joint – inside u.)	m	10/15 (manifold)	10/15 (manifold)	10/15 (manifold)	10/15 (manifold)	10/15 (manifold)	10/15 (manifold)
Liquid line dimension	mm/inch	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8	9.53 - 3/8
Gas line dimension	mm/inch	15.88 - 5/8	15.88 - 5/8	15.88 - 5/8	15.88 - 5/8	15.88 - 5/8	15.88 - 5/8

The specified cooling and heating capacities refer to the outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

<sup>1</sup> Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

<sup>2</sup> Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

<sup>3</sup> The sound pressure level has been measured in the following conditions:

a. 1 metre from the surface of the unit's service hatch and 1.5 metres from the floor level

b. In anechoic chamber without reflection

<sup>4</sup> The EER and COP value corresponds to the outdoor unit, input power of the indoor unit is not considered.

The outdoor unit performance has been established in combination with RCI indoor units.

\*In the event the power level of all connected indoor units is equal to 0.6HP. Otherwise the maximum limit of connectable indoor units is as follows:

6 for 4HP

8 for 5HP

9 for 6HP



# VRF Set Free outdoor units

## SET FREE SIDE FLOW

### DC inverter Heat pump



RAS 8FSNM  
RAS 10FSNM  
RAS 12FSNM




SMALL SIZE  
HORIZONTAL EJECTION  
2 PIPE SYSTEM  
UP TO 10 INDOOR  
OPTIONAL INPUTS/OUTPUTS

Multi heat pump systems with Scroll compressor DC Inverter 2 pipes.


- Three-phase only
- Capacity of connectible indoor units variable from minimum 50 to maximum 130%
- 3 available power levels: 8, 10, 12 HP
- Up to 10 connectible indoor units, controlled independently
- Compact size with 40% reduction
- Minimum Sound Pressure: 42dB(A)
- High energy efficiency
- Cooling up to -5°C, heating up to -20°C
- Maximum piping length: 250m.
- Maximum height difference: 40m.

### Features and advantages

The SET FREE Side Flow range consists of medium power VRF systems (8HP, 10HP, 12HP) with three-phase power supply. These units are suitable for applications such as offices or retail spaces, by combining all VRF qualities in a decidedly more compact volume!



- 1 The refrigerant lines can be designed and implemented up to maximum distance of **100 m** (total extension: **250 m**).
- 2 Maximum length after the first joint: **40 m**.
- 3 Maximum length after one joint: **15 m**.
- 4 Height difference between indoor units: **15 m**.
- 5 Height difference between indoor units and outdoor unit:  
Lower indoor unit: **40 m** from outdoor unit.  
Higher indoor unit: **30 m** from outdoor unit.





# VRF Set Free outdoor units



## TECHNICAL SPECIFICATIONS

CODE		RAS 8FSNM	RAS 10FSNM	RAS 12FSNM
Power supply	V/Ph/Hz	3N 380/415 50Hz	3N 380/415 50Hz	3N 380/415 50Hz
Cooling nominal capacity (1)	kW	22.4	28	33.5
Heating nominal capacity (2)	kW	25	31.5	37.5
Cooling operating current	A	10.3/9.4	13.6/12.4	17.3/15.8
Heating operating current	A	9.6/8.8	12.7/11.7	16.0/14.7
Power consumption at nominal cap. (Cool. / Heat.)	kW	6.3/5.9	8.3/7.8	10.7/9.9
Max current consumption		ND	ND	ND
EER / COP (4)	W/W	3.56 / 4.24	3.37 / 4.04	3.13 / 3.79
Energy class		A/A	A/A	B/A
Min – max connectable capacity		50-130	50-130	50-130
No. min – max inside	N.	1-10	1-10	1-10
Sound Pressure Cooling/Heating (Night Mode) (3)	dB(A)	53/55	56/58	59/61
Sound Pressure at nominal output (Cool. / Heat.)	dB(A)	ND	ND	ND
Number of fans	n.	2	2	2
Air flow	m³/h	7260	9000	9780
Dimensions (H × W × D)	mm	1650x1100x390	1650x1100x390	1650x1100x390
Weight	kg	170	170	173
Cooling working range	°C	-5 / +43 (BS)	-5 / +43 (BS)	-5 / +43 (BS)
Heating working range	°C	-20 / +15 (BU)	-20 / +15 (BU)	-20 / +15 (BU)
Refrigerant R-410A charge	kg	5	5.5	6.5
Maximum piping length	m	250	250	250
Maximum piping distance (actual/equivalent)	m/m	100/120	100/120	100/120
Maximum level difference (high OU – low OU)	m/m	40/30	40/30	40/30
Maximum piping length after the first joint	m	40	40	40
Liquid line dimension	mm/inch	9.53 - 3/8	12.7 - 1/2	12.7 - 1/2
Gas line dimension	mm/inch	19.05 - 3/4	22.2 - 7/8	25.4/28.6 - (1)-(1-1/8)

The specified cooling and heating capacities refer to the outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

<sup>1</sup> Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

<sup>2</sup> Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

<sup>3</sup> The sound pressure level has been measured in the following conditions:

a. 1 metre from the surface of the unit's service hatch and 1.5 metres from the floor level

b. In the night mode the noise level is reduced by 5dBA

c. The specified data have been obtained in an anechoic chamber

<sup>4</sup> The EER and COP value corresponds to the outdoor unit, input power of the indoor unit is not considered.

The outdoor unit performance has been established in combination with RCI indoor units.



## VRF Set Free outdoor units

# SET FREE FSXN 2 & 3 PIPES

DC inverter Heat pump



GRAND HOTEL MINARETO - SIRACUSA - APPLICATION OF HITACHI VRF SET FREE



-20  
+15



-5  
+43



UP TO 64 INDOOR UNITS

PIPING UP TO 1000M

1HZ STEP CONTROL

INDOOR UNIT POWERING OFF

OPTIONAL INPUTS/OUTPUTS

- Compatibility with all System Free indoor units and HITACHI Heat recovery Units
- Wide range available FSXN (from 8 to 54 Hp)
- Energy savings
  - Heat recovery and use of Compressors with IPM DC Inverter Control
- Flexibility of installation
  - Compact, lightweight and connecting flexibility to cooling lines
- Comfort and reliability
  - Possibility to achieve exceptionally low sound levels thanks to the Noise Reduction function (optional)
- Control System H-LINK II

# VRF Set Free outdoor units



TECHNICAL SPECIFICATIONS									
CODE				RAS 8FSXN	RAS 10FSXN	RAS 12FSXN	RAS 14FSXN	RAS 16FSXN	RAS 18FSXN
cooling capacity			kW	22.4	28.0	33.5	40.0	45.0	50.0
heating capacity			kW	25.0	31.5	37.5	45.0	50.0	56.0
EER				3.85	3.79	3.41	3.25	3.23	3.37
COP				4.17	4.11	3.60	3.89	3.90	3.81
ESEER (1)				4.45	4.38	3.94	3.76	3.74	3.90
ESEER (2)				ND	ND	ND	ND	ND	ND
electrical input	nominal	cooling	kW	5.82	7.39	9.82	12.31	13.93	14.84
		heating	kW	6.00	7.66	10.42	11.57	12.82	14.70
	maximum input		A	12	16	22	26	29	31
scroll compressors			type/no.	Inverter x 1	Inverter x 1	Inverter x 1	Inverter x 1 On-Off x 1	Inverter x 1 + On-Off x 1	Inverter x 1 + On-Off x 1
cooling con- nections with distribution to:	2 pipes	gas	mm (inch)	19.05 (3/4)	22.2 (7/8)	25.4 (1)	25.4 (1)	28.58 (1-1/8)	28.58 (1-1/8)
		liquid	mm (inch)	9.52 (3/8)	9.52 (3/8)	12.7 (1/2)	12.7 (1/2)	12.7 (1/2)	15.88 (5/8)
	3 pipes	HP gas	mm (inch)	15.88 (5/8)	19.05 (3/4)	22.2 (7/8)	22.2 (7/8)	22.2 (7/8)	22.2 (7/8)
		LP gas	mm (inch)	19.05 (3/4)	22.2 (7/8)	25.4 (1)	25.4 (1)	28.58 (1-1/8)	28.58 (1-1/8)
		liquid	mm (inch)	9.52 (3/8)	9.52 (3/8)	12.7 (1/2)	12.7 (1/2)	12.7 (1/2)	15.88 (5/8)
maximum number of indoor units			no.	14	18	21	26	29	29
sound pressure level (night mode)			dB(A)	58 (53)	58 (53)	60 (55)	62 (57)	62 (57)	63 (58)
dimensions (H x L x D)			mm	1720x950x765	1720x950x765	1720x950x765	1720x1210x765	1720x1210x765	1720x1210x765
Weight			kg	210	210	210	295	295	315
CODE				RAS 20FSXN (RAS 8FSXN + RAS 12FSXN)	RAS 22FSXN (RAS 8FSXN + RAS 14FSXN)	RAS 24FSXN (RAS 10FSXN + RAS14FSXN)	RAS 26FSXN (RAS 12FSXN + RAS 14FSXN)	RAS 28FSXN (RAS 14FSXN + RAS 14FSXN)	RAS 30FSXN (RAS 14FSXN + RAS 16FSXN)
cooling capacity			kW	56.0	61.5	69.0	73.0	80.0	85.0
heating capacity			kW	63.0	69.0	77.5	82.5	90.0	95.0
EER				3.58	3.62	3.37	3.38	3.25	3.24
COP				3.81	4.04	3.89	3.75	3.89	3.90
ESEER (1)				4.14	4.19	3.90	3.91	3.76	3.75
ESEER (2)				ND	ND	ND	ND	ND	ND
electrical input	nominal	cooling	kW	15.64	17.00	20.47	21.58	24.62	26.24
		heating	kW	16.54	17.06	19.94	21.99	23.14	24.39
	maximum input		A	34	36	43	46	53	56
scroll compressors			type/no.	Inverter x 2	Inverter x 2 + On-Off x 1	Inverter x 2 + On-Off x 1	Inverter x 2 + On-Off x 1	Inverter x 2 + On-Off x 2	Inverter x 2 + On-Off x 2
cooling con- nections with distribution to:	2 pipes	gas	mm (inch)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		liquid	mm (inch)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
	3 pipes	HP gas	mm (inch)	22.2 (7/8)	25.4 (1)	25.4 (1)	25.4 (1)	28.58 (1-1/8)	28.58 (1-1/8)
		LP gas	mm (inch)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		liquid	mm (inch)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
maximum number of indoor units			no.	37	40	45	48	52	56
sound pressure level (night mode)			dB(A)	62 (57)	63 (58)	63 (58)	64 (59)	65 (60)	65 (60)
dimensions (H x L x D)			mm	1720x1920x765	1720x2180x765	1720x2180x765	1720x2180x765	1720x2440x765	1720x2440x765
Weight			kg	210+210	210+295	210+295	210+295	295+295	295+295

The specified cooling and heating capacities refer to outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

The sound pressure level has been measured in the following conditions:

a. 1 metre from the unit's service hatch cover and 1.5 metres from floor level

b. The specified data are based on the cooling mode. In the case of the heating mode, the pressure level increases from 1 to 2dB.

c. The specified data have been obtained in an anechoic chamber

Only the combinations shown in the table are possible (20-54HP)

The width specified in outer dimensions takes into account the specific 20mm distance between outdoor units (20-54HP)

ESEER (1): Seasonal efficiency value in standard cooling

ESEER (2): Seasonal efficiency value in cooling with optimised system operation depending on seasonal demand



# VRF Set Free outdoor units

## SET FREE FSXN 2 & 3 PIPES

### DC inverter Heat pump



#### TECHNICAL SPECIFICATIONS

CODE					RAS 32FSXN (RAS 16FSXN + RAS 16FSXN)	RAS 34FSXN (RAS 16FSXN + RAS 18FSXN)	RAS 36FSXN (RAS 18FSXN + RAS 18FSXN)	RAS 38FSXN (RAS 12FSXN + RAS 12FSXN + RAS 14FSXN)	RAS 40FSXN (RAS 12FSXN + RAS 12FSXN + RAS 16FSXN)	RAS 42FSXN (RAS 12FSXN + RAS 14FSXN + RAS 18FSXN)
cooling capacity				kW	90.0	95.0	100.0	109.0	112.0	118.0
heating capacity				kW	100.0	106.0	112.0	118.0	125.0	132.0
EER					3.23	3.30	3.37	3.29	3.34	3.32
COP					3.90	3.85	3.81	3.87	3.71	3.65
ESEER (1)					3.74	3.82	3.90	3.81	3.86	3.84
ESEER (2)					ND	ND	ND	ND	ND	ND
electrical input	nominal	cooling	kW	27.86	28.77	29.68	33.12	33.57	35.52	
		heating	kW	25.64	27.52	29.40	30.47	33.66	36.20	
	maximum input		A	595	61	63	70	70	76	
scroll compressors				type/no.	Inverter x 2 + On-Off x 2	Inverter x 2 + On-Off x 2	Inverter x 2 + On-Off x 2	Inverter x 3 + On-Off x 1	Inverter x 3 + On-Off x 1	Inverter x 3 + On-Off x 1
cooling con- nections with distribution to:	2 pipes	gas	mm (inch)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
	3 pipes	HP gas	mm (inch)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		LP gas	mm (inch)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
maximum number of indoor units				no.	60	63	64	64	64	64
sound pressure level (night mode)				dB(A)	65 (60)	66 (61)	66 (61)	66 (61)	66 (61)	66 (61)
dimensions (H x L x D)				mm	1720x2440x765	1720x2440x765	1720x2440x765	1720x3150x765	1720x3150x765	1720x3150x765
Weight				kg	295+295	295+315	315+315	210+210+295	210+210+295	210+210+315

CODE					RAS 44FSXN (RAS 12FSXN + RAS 14FSXN + RAS 18FSXN)	RAS 46FSXN (RAS 12FSXN + RAS 16FSXN + RAS 18FSXN)	RAS 48FSXN (RAS 12FSXN + RAS 18FSXN + RAS 18FSXN)	RAS 50FSXN (RAS 14FSXN + RAS 18FSXN + RAS 18FSXN)	RAS 52FSXN (RAS 16FSXN + RAS 18FSXN + RAS 18FSXN)	RAS 54FSXN (RAS 18FSXN + RAS 18FSXN + RAS 18FSXN)
cooling capacity				kW	125.0	132.0	136.0	140.0	145.0	150.0
heating capacity				kW	140.0	145.0	150.0	155.0	160.0	165.0
EER					3.27	3.16	3.24	3.33	3.32	3.37
COP					3.75	3.71	3.74	3.98	3.98	4.01
ESEER (1)					3.78	3.66	3.75	3.85	3.84	3.90
ESEER (2)					ND	ND	ND	ND	ND	ND
electrical input	nominal	cooling	kW	38.20	41.78	41.93	41.99	43.61	44.52	
		heating	kW	37.35	39.04	40.15	38.97	40.22	41.10	
	maximum input		A	81	88	88	89	92	94	
scroll compressors				type/no.	Inverter x 3 + On-Off x 2	Inverter x 3 + On-Off x 2	Inverter x 3 + On-Off x 2	Inverter x 3 + On-Off x 3	Inverter x 3 + On-Off x 3	Inverter x 3 + On-Off x 3
cooling con- nections with distribution to:	2 pipes	gas	mm (inch)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
	3 pipes	HP gas	mm (inch)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		LP gas	mm (inch)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
maximum number of indoor units				no.	64	64	64	64	64	64
sound pressure level (night mode)				dB(A)	67 (62)	67 (62)	67 (62)	67 (62)	67 (62)	68 (63)
dimensions (H x L x D)				mm	1720x3410x765	1720x3410x765	1720x3410x765	1720x3670x765	1720x3670x765	1720x3670x765
Weight				kg	210+295+335	210+295+315	210+315+315	295+315+315	295+315+315	315+315+315

The specified cooling and heating capacities refer to outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard  
Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

The sound pressure level has been measured in the following conditions:

a. 1 metre from the unit's service hatch cover and 1.5 metres from floor level

b. The specified data are based on the cooling mode. In the case of the heating mode, the pressure level increases from 1 to 2dB.

c. The specified data have been obtained in an anechoic chamber

Only the combinations shown in the table are possible (20-54HP)

The width specified in outer dimensions takes into account the specific 20mm distance between outdoor units (20-54HP)

ESEER (1): Seasonal efficiency value in standard cooling

ESEER (2): Seasonal efficiency value in cooling with optimised system operation depending on seasonal demand



# VRF Set Free outdoor units







## VRF Set Free outdoor units

# SET FREE FSXN 2 & 3 PIPES SERIES 1

DC inverter Heat pump



NEW



-20  
+15



-5  
+43



UP TO 64 INDOOR UNITS

PIPING UP TO 1000 M

EXTREMELY HIGH ENERGY EFFICIENCY

COMPATIBILITY WITH 0.6HP INDOOR UNITS

GREATER FLEXIBILITY OF  
REFRIGERANT DEVELOPMENT

OPTIONAL INPUTS/OUTPUTS

- Compatibility with all System Free indoor units including new 0.6HP power levels and heat recovery units HITACHI
- Wide range available (from 8 to 54 Hp)
- Improved seasonal efficiency at partial loads
- New compressors with enhances performance compared to the previous version
- Optimisation of the refrigerant cycle system
- Increase of piping height difference up to 90 metres with no modification of the cooling circuiting

# VRF Set Free outdoor units



TECHNICAL SPECIFICATIONS										
CODE				RAS 8FSXN1E	RAS 10FSXN1E	RAS 12FSXN1E	RAS 14FSXN1E	RAS 16FSXN1E		
cooling capacity			kW	22.4	28.0	33.5	40.0	45.0		
heating capacity			kW	25.0	31.5	37.5	45.0	50.0		
EER				4.12	3.98	3.16	3.30	3.24		
COP				4.08	4.07	3.79	3.62	3.12		
ESEER (1)				6.07	5.86	5.54	4.86	4.77		
ESEER (2)				7.71	7.45	7.08	6.17	6.06		
electrical input	nominal	cooling	kW	5.44	7.04	10.60	12.11	13.87		
		heating	kW	6.13	7.73	9.89	12.44	16.03		
	maximum input		A	15	20	26.5	29.2	33		
scroll compressors			type/no.	Inverter x 1	Inverter x 1	Inverter x 1	Inverter x 1 On-Off x 1	Inverter x 1 On-Off x 1		
cooling connections with distribution to:	2 pipes	gas	mm (inch)	19.05 (3/4)	22.2 (7/8)	25.4 (1)	25.4 (1)	28.58 (1-1/8)		
		liquid	mm (inch)	9.52 (3/8)	9.52 (3/8)	12.7 (1/2)	12.7 (1/2)	12.7 (1/2)		
	3 pipes	HP gas	mm (inch)	15.88 (5/8)	19.05 (3/4)	22.2 (7/8)	22.2 (7/8)	22.2 (7/8)		
		LP gas	mm (inch)	19.05 (3/4)	22.2 (7/8)	25.4 (1)	25.4 (1)	28.58 (1-1/8)		
		liquid	mm (inch)	9.52 (3/8)	9.52 (3/8)	12.7 (1/2)	12.7 (1/2)	12.7 (1/2)		
maximum number of indoor units			no.	14	18	21	26	29		
sound pressure level (night mode)			dB(A)	58 (53)	58 (53)	60 (55)	62 (57)	64 (57)		
dimensions (H x L x D)			mm	1720x950x765	1720x950x765	1720x950x765	1720x1210x765	1720x1210x765		
Weight			kg	215	230	230	310	310		
CODE					RAS 16FSXN1E-P (RAS 8FSXN1E + RAS 10FSXN1E)	RAS 18FSXN1E (RAS 8FSXN1E + RAS 10FSXN1E)	RAS 20FSXN1E (RAS 8FSXN1E + RAS 12FSXN1E)	RAS 22FSXN1E (RAS 8FSXN1E + RAS 14FSXN1E)	RAS 24FSXN1E (RAS 10FSXN1E + RAS 14FSXN1E)	
cooling capacity			kW	45.0	50.0	56.0	61.5	69.0		
heating capacity			kW	50.0	56.0	63.0	69.0	77.5		
EER				4.10	4.04	3.48	3.58	3.52		
COP				4.15	4.08	3.90	3.80	3.77		
ESEER (1)				5.95	5.95	5.66	5.27	5.18		
ESEER (2)				7.56	7.56	7.22	6.70	6.59		
electrical input	nominal	cooling	kW	10.97	12.37	16.07	17.17	19.58		
		heating	kW	12.05	13.72	16.17	18.17	20.57		
	maximum input		A	35	35	41.5	44.2	49.2		
scroll compressors			type/no.	Inverter x 2	Inverter x 2	Inverter x 2	Inverter x 2 + On-Off x 1	Inverter x 2 + On-Off x 1		
cooling connections with distribution to:	2 pipes	gas	mm (inch)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)		
		liquid	mm (inch)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)		
	3 pipes	HP gas	mm (inch)	22.2 (7/8)	22.2 (7/8)	22.2 (7/8)	25.4 (1)	22.2 (7/8)		
		LP gas	mm (inch)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)		
		liquid	mm (inch)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)	15.88 (5/8)		
maximum number of indoor units			no.	29	29	37	40	45		
sound pressure level (night mode)			dB(A)	61 (56)	61 (56)	63 (58)	64 (59)	64 (59)		
dimensions (H x L x D)			mm	1720x1920x765	1720x1920x765	1720x1920x765	1720x2180x765	1720x2180x765		
Weight			kg	215+230	215+230	215+230	215+310	230+310		

The specified cooling and heating capacities refer to outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

The sound pressure level has been measured in the following conditions:

a. 1 metre from the unit's service hatch cover and 1.5 metres from floor level

b. The specified data are based on the cooling mode. In the case of the heating mode, the pressure level increases from 1 to 2dB.

c. The specified data have been obtained in an anechoic chamber

Only the combinations shown in the table are possible (16-54HP)

The width given in outer dimensions takes into account a specific distance of 20mm between outdoor units (16-54HP)

ESEER (1): Seasonal efficiency value in standard cooling

ESEER (2): Seasonal efficiency value in cooling with optimised system operation depending on seasonal demand



# VRF Set Free outdoor units

## SET FREE FSXN 2 & 3 PIPES SERIES

TECHNICAL SPECIFICATIONS								
CODE				RAS 26FSXN1E (RAS 12FSXN1E + RAS 14FSXN1E)	RAS 28FSXN1E (RAS 14FSXN1E + RAS 14FSXN1E)	RAS 30FSXN1E (RAS 14FSXN1E + RAS 16FSXN1E)	RAS 32FSXN1E (RAS 16FSXN1E + RAS 16FSXN1E)	RAS 32FSXN1E-P (RAS 10FSXN1E + RAS 12FSXN1E + RAS 12FSXN1E)
cooling capacity			kW	73.0	80.0	85.0	90.0	90.0
heating capacity			kW	82.5	90.0	95.0	100.0	100.0
EER				3.25	3.30	3.27	3.24	3.40
COP				3.69	3.62	3.34	3.12	3.95
ESEER (1)				5.16	4.86	4.81	4.77	5.62
ESEER (2)				6.58	6.17	6.12	6.06	7.17
electrical input	nominal	cooling	kW	22.43	24.22	25.98	27.74	26.40
		heating	kW	22.33	24.88	28.47	32.06	25.32
	maximum input		A	55.7	58.4	62.2	66	73
scroll compressors			type/no.	Inverter x 2 + On-Off x 1	Inverter x 2 + On-Off x 2	Inverter x 2 + On-Off x 2	Inverter x 2 + On-Off x 2	Inverter x 3
cooling con- nections with distribution to:	2 pipes	gas	mm (inch)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
	3 pipes	HP gas	mm (inch)	25.4 (1)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)
		LP gas	mm (inch)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
maximum number of indoor units			no.	48	52	56	60	60
sound pressure level (night mode)			dB(A)	65 (60)	65 (60)	66 (61)	66 (61)	65 (60)
dimensions (H x L x D)			mm	1720x2180x765	1720x2440x765	1720x2440x765	1720x2440x765	1720x2890x765
Weight			kg	230+310	310+310	310+310	310+310	230+230+230
CODE				RAS 34FSXN1E (RAS 10FSXN1E + RAS 12FSXN1E + RAS 12FSXN1E)	RAS 36FSXN1E (RAS 12FSXN1E + RAS 12FSXN1E + RAS 12FSXN1E)	RAS 38FSXN1E (RAS 12FSXN1E + RAS 12FSXN1E + RAS 14FSXN1E)	RAS 40FSXN1E (RAS 12FSXN1E + RAS 12FSXN1E + RAS 16FSXN1E)	RAS 42FSXN1E (RAS 12FSXN1E + RAS 14FSXN1E + RAS 16FSXN1E)
cooling capacity			kW	95.0	100.0	109.0	112.0	118.0
heating capacity			kW	106.0	112.0	118.0	125.0	132.0
EER				3.36	3.17	3.16	3.19	3.25
COP				3.88	3.81	3.78	3.49	3.47
ESEER (1)				5.58	5.56	5.17	5.19	5.01
ESEER (2)				7.11	7.10	6.59	6.62	6.38
electrical input	nominal	cooling	kW	28.24	31.53	34.44	35.07	36.30
		heating	kW	27.30	29.43	31.25	35.81	38.07
	maximum input		A	73	79.5	82.2	86	88.7
scroll compressors			type/no.	Inverter x 3	Inverter x 3	Inverter x 3 + On-Off x 1	Inverter x 3 + On-Off x 1	Inverter x 3 + On-Off x 2
cooling con- nections with distribution to:	2 pipes	gas	mm (inch)	31.75 (1-1/4)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
	3 pipes	HP gas	mm (inch)	28.58 (1-1/8)	28.58 (1-1/8)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		LP gas	mm (inch)	31.75 (1-1/4)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
maximum number of indoor units			no.	63	64	64	64	64
sound pressure level (night mode)			dB(A)	65 (60)	65 (60)	66 (61)	67 (61)	67 (62)
dimensions (H x L x D)			mm	1720x2890x765	1720x2890x765	1720x3150x765	1720x3150x765	1720x3410x765
Weight			kq	230+230+230	230+230+230	230+230+310	230+230+310	230+310+310

The specified cooling and heating capacities refer to outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard  
Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

The sound pressure level has been measured in the following conditions:

a. 1 metre from the unit's service hatch cover and 1.5 metres from floor level

b. The specified data are based on the cooling mode. In the case of the heating mode, the pressure level increases from 1 to 2dB.

c. The specified data have been obtained in an anechoic chamber

Only the combinations shown in the table are possible (16-54HP)

The width given in outer dimensions takes into account a specific distance of 20mm between outdoor units (16-54HP)

ESEER (1): Seasonal efficiency value in standard cooling

ESEER (2): Seasonal efficiency value in cooling with optimised system operation depending on seasonal demand



# VRF Set Free outdoor units



TECHNICAL SPECIFICATIONS						
CODE				RAS 44FSXN1E (RAS 12FSXN1E + RAS 16FSXN1E + RAS 16FSXN1E)	RAS 46FSXN1E (RAS 14FSXN1E + RAS 16FSXN1E + RAS 16FSXN1E)	RAS 48FSXN1E (RAS 16FSXN1E + RAS 16FSXN1E + RAS 16FSXN1E)
cooling capacity			kW	125.0	132.0	136.0
heating capacity			kW	140.0	145.0	150.0
EER				3.19	3.22	3.23
COP				3.23	3.26	3.12
ESEER (1)				4.70	4.74	4.76
ESEER (2)				5.97	6.02	6.04
electrical input	nominal	cooling	kW	39.19	40.96	42.12
		heating	kW	43.35	44.50	48.09
	maximum input		A	92.5	95.2	99
scroll compressors			type/no.	Inverter x 3 + On-Off x 2	Inverter x 3 + On-Off x 3	Inverter x 3 + On-Off x 3
cooling connections with distribution to:	2 pipes	gas	mm (inch)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
	3 pipes	HP gas	mm (inch)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		LP gas	mm (inch)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
maximum number of indoor units			no.	64	64	64
sound pressure level (night mode)			dB(A)	68 (62)	68 (63)	69 (63)
dimensions (H x L x D)			mm	1720x3410x765	1720x3670x765	1720x3670x765
Weight			kg	230+310+310	310+310+310	310+310+310

CODE					RAS 50FSXN1E (RAS 10FSXN1E + RAS 12FSXN1E + RAS 14FSXN1E + RAS 14FSXN1E)	RAS 52FSXN1E (RAS 12FSXN1E + RAS 12FSXN1E + RAS 14FSXN1E + RAS 14FSXN1E)	RAS 54FSXN1E (RAS 12FSXN1E + RAS 12FSXN1E + RAS 14FSXN1E + RAS 16FSXN1E)
cooling capacity				kW	140.0	145.0	150.0
heating capacity				kW	155.0	160.0	165.0
EER					3.41	3.27	3.26
COP					3.81	3.78	3.61
ESEER (1)					5.22	5.20	5.16
ESEER (2)					6.64	6.62	6.58
electrical input	nominal	cooling	kW	41.04	44.32	46.07	
		heating	kW	40.68	42.28	45.68	
	maximum input		A	104.9	111.4	115.2	
scroll compressors				type/no.	Inverter x 4 + On-Off x 2	Inverter x 4 + On-Off x 2	Inverter x 4 + On-Off x 2
cooling connections with distribution to:	2 pipes	gas	mm (inch)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	
	3 pipes	HP gas	mm (inch)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	
		LP gas	mm (inch)	38.1 (1-1/2)	38.1 (1-1/2)	38.1 (1-1/2)	
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	
maximum number of indoor units				no.	64	64	64
sound pressure level (night mode)				dB(A)	67 (62)	68 (63)	68 (63)
dimensions (H x L x D)				mm	1720x4380x765	1720x4380x765	1720x4380x765
Weight				kq	230+230+310+310	230+230+310+310	230+230+310+310

The specified cooling and heating capacities refer to outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

The sound pressure level has been measured in the following conditions:

a. 1 metre from the unit's service hatch cover and 1.5 metres from floor level

b. The specified data are based on the cooling mode. In the case of the heating mode, the pressure level increases from 1 to 2dB.

c. The specified data have been obtained in an anechoic chamber

Only the combinations shown in the table are possible (16-54HP)

The width given in outer dimensions takes into account a specific distance of 20mm between outdoor units (16-54HP)

ESEER (1): Seasonal efficiency value in standard cooling

ESEER (2): Seasonal efficiency value in cooling with optimised system operation depending on seasonal demand



## VRF Set Free outdoor units

# SET FREE FSXNH 2 & 3 PIPES

High efficiency heat pump



- UP TO 64 INDOOR UNITS
- PIPING UP TO 1000M
- 1HZ STEP CONTROL
- INDOOR UNIT POWERING OFF
- OPTIONAL INPUTS/OUTPUTS

- The new high efficiency FSXNH outdoor units belong to the System Free range and thus assure total compatibility with the same indoor units, the same controls and communication interfaces as the commercial range.
- Wide range available from 5 to 36HP  
Extremely high efficiency with COP up to 4.80 (5HP level)
- All models, already starting from the minimum 5HP level, are ready to work in 3 pipe simultaneous hot and cold systems
- Optional inputs/outputs

# VRF Set Free outdoor units



TECHNICAL SPECIFICATIONS								
CODE				RAS 5FSXNH	RAS 6FSXNH	RAS 8FSXNH	RAS 10FSXNH	RAS 12FSXNH
cooling capacity			kW	14.0	16.0	22.4	28.0	33.5
heating capacity			kW	16.0	18.0	25.0	31.5	37.5
EER				4.49	4.56	4.66	4.34	3.93
COP				4.80	4.58	4.67	4.67	4.11
ESEER (1)				6.61	6.71	6.86	6.39	5.79
ESEER (2)				8.40	8.53	8.72	8.12	7.35
electrical input	nominal	cooling	kW	3.1	3.5	4.8	6.5	8.5
		heating	kW	3.3	3.9	5.3	6.7	9.1
	maximum input		A	13	13	15	18.7	20
scroll compressors			type/no.	Inverter x 1	Inverter x 1	Inverter x 1	Inverter x 1	Inverter x 1
cooling connections with distribution to:	2 pipes	gas	mm (inch)	15.88 (5/8)	19.05 (3/4)	19.05 (3/4)	22.2 (7/8)	25.4 (1)
		liquid	mm (inch)	9.52 (3/8)	9.52 (3/8)	9.52 (3/8)	9.52 (3/8)	12.7 (1/2)
	3 pipes	HP gas	mm (inch)	12.7 (1/2)	15.88 (5/8)	15.88 (5/8)	19.05 (3/4)	22.2 (7/8)
		LP gas	mm (inch)	15.88 (5/8)	19.05 (3/4)	19.05 (3/4)	22.2 (7/8)	25.4 (1)
		liquid	mm (inch)	9.52 (3/8)	9.52 (3/8)	9.52 (3/8)	9.52 (3/8)	12.7 (1/2)
maximum number of indoor units			no.	8	9	13	16	19
sound pressure level (night mode)			dB(A)	55 (52)	56 (52)	58 (53)	59 (54)	61 (56)
dimensions (H x L x D)			mm	1720x950x765	1720x950x765	1720x1210x765	1720x1210x765	1720x1210x765
Weight			kg	215	215	260	260	260
CODE				RAS 12FSXNH-P (RAS 6FSXNH + RAS 8FSXNH)	RAS 14FSXNH (RAS 6FSXNH + RAS 8FSXNH)	RAS 16FSXNH (RAS 8FSXNH + RAS 8FSXNH)	RAS 18FSXNH (RAS 8FSXNH + RAS 10FSXNH)	RAS 20FSXNH (RAS 8FSXNH + RAS 12FSXNH)
cooling capacity			kW	33.5	40.0	45.0	50.0	56.0
heating capacity			kW	37.5	45.0	50.0	56.0	63.0
EER				4.70	4.58	4.65	4.48	4.19
COP				4.73	4.59	4.67	4.68	4.31
ESEER (1)				6.92	6.74	6.85	6.60	6.17
ESEER (2)				8.79	8.57	8.70	8.38	7.84
electrical input	nominal	cooling	kW	7.1	8.7	9.7	11.2	13.4
		heating	kW	7.9	9.8	10.7	12.0	14.6
	maximum input		A	20	28	30	33.7	35
scroll compressors			type/no.	Inverter x 2	Inverter x 2	Inverter x 2	Inverter x 2	Inverter x 2
cooling connections with distribution to:	2 pipes	gas	mm (inch)	25.4 (1)	25.4 (1)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)
		liquid	mm (inch)	12.7 (1/2)	12.7 (1/2)	12.7 (1/2)	15.88 (5/8)	15.88 (5/8)
	3 pipes	HP gas	mm (inch)	22.2 (7/8)	22.2 (7/8)	22.2 (7/8)	22.2 (7/8)	22.2 (7/8)
		LP gas	mm (inch)	25.4 (1)	25.4 (1)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)
		liquid	mm (inch)	12.7 (1/2)	12.7 (1/2)	12.7 (1/2)	15.88 (5/8)	15.88 (5/8)
maximum number of indoor units			no.	19	23	26	26	33
sound pressure level (night mode)			dB(A)	61 (56)	61 (56)	61 (56)	62 (57)	63 (58)
dimensions (H x L x D)			mm	1720x2160x765	1720x2160x765	1720x2420x765	1720x2420x765	1720x2420x765
Weight			kq	215+260	215+260	260+260	260+260	260+260

The specified cooling and heating capacities refer to outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard  
Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

The sound pressure level has been measured in the following conditions:

a. 1 metre from the unit's service hatch cover and 1.5 metres from floor level

b. The specified data are based on the cooling mode. In the case of the heating mode, the pressure level increases from 1 to 2dB.

c. The specified data have been obtained in an anechoic chamber

Only the combinations shown in the table are possible (12-36HP)

The width specified in outer dimensions takes into account the specific 20mm distance between outdoor units (12-36HP)

ESEER (1): Seasonal efficiency value in standard cooling

ESEER (2): Seasonal efficiency value in cooling with optimised system operation depending on seasonal demand



# VRF Set Free outdoor units

## SET FREE FSXNH 2 & 3 PIPES

high efficiency 

TECHNICAL SPECIFICATIONS								
CODE				RAS 22FSXNH (RAS 10FSXNH + RAS 12FSXNH)	RAS 24FSXNH (RAS 12FSXNH + RAS12FSXNH)	RAS 24FSXNH (RAS 8FSXNH + RAS 8FSXNH + RAS 10FSXNH)	RAS 26FSXNH (RAS 8FSXNH + RAS 8FSXNH + RAS 10FSXNH)	RAS 28FSXNH (RAS 8FSXNH + RAS 8FSXNH + RAS 12FSXNH)
cooling capacity			kW	61.5	69.0	69.0	73.0	80.0
Heating capacity			kW	69.0	77.5	77.5	82.5	90.0
EER				4.11	3.91	4.64	4.53	4.30
COP				4.35	4.09	4.64	4.66	4.39
ESEER (1)				6.05	5.76	6.83	6.67	6.33
ESEER (2)				7.69	7.32	8.68	8.48	8.05
electrical input	nominal	cooling	kW	15.0	17.7	14.8	16.1	18.6
		heating	kW	15.9	19.0	16.7	17.7	20.5
	maximum input		A	38.7	40	40	40	48.7
scroll compressors			type/no.	Inverter x 2	Inverter x 2	Inverter x 3	Inverter x 3	Inverter x 3
cooling connections with distribution to:	2 pipes	gas	mm (inch)	28.58 (1-1/8)	28.58 (1-1/8)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		liquid	mm (inch)	15.88 (5/8)	15.88 (5/8)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
	3 pipes	HP gas	mm (inch)	25.4 (1)	25.4 (1)	25.4 (1)	25.4 (1)	28.58 (1-1/8)
		LP gas	mm (inch)	28.58 (1-1/8)	28.58 (1-1/8)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)
		liquid	mm (inch)	15.88 (5/8)	15.88 (5/8)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
maximum number of indoor units			no.	36	40	40	43	47
sound pressure level (night mode)			dB(A)	64 (59)	64 (59)	64 (59)	64 (59)	64 (59)
dimensions (H x L x D)			mm	1720x2420x765	1720x2420x765	1720x3630x765	1720x3630x765	1720x3630x765
Weight			kg	260+260	260+260	260+260+260	260+260+260	260+260+260

CODE				RAS 30FSXNH (RAS 8FSXNH + RAS 10FSXNH + RAS 12FSXNH)	RAS 32FSXNH (RAS 8FSXNH + RAS 12FSXNH + RAS 12FSXNH)	RAS 34FSXNH (RAS 10FSXNH + RAS 12FSXNH + RAS 12FSXNH)	RAS 36FSXNH (RAS 12FSXNH + RAS 12FSXNH + RAS 12FSXNH)
cooling capacity			kW	85.0	90.0	95.0	100.0
Heating capacity			kW	95.0	100.0	106.0	112.0
EER				4.24	4.09	4.05	3.93
COP				4.42	4.24	4.27	4.11
ESEER (1)				6.24	6.02	5.96	5.79
ESEER (2)				7.93	7.65	7.58	7.35
electrical input	nominal	cooling	kW	20.0	22.0	23.4	25.4
		heating	kW	21.5	23.6	24.8	27.2
	maximum input		A	53.7	55	58.7	60
scroll compressors			type/no.	Inverter x 3	Inverter x 3	Inverter x 3	Inverter x 3
cooling con- nections with distribution to:	2 pipes	gas	mm (inch)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
	3 pipes	HP gas	mm (inch)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)	28.58 (1-1/8)
		LP gas	mm (inch)	31.75 (1-1/4)	31.75 (1-1/4)	31.75 (1-1/4)	38.1 (1-1/2)
		liquid	mm (inch)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)	19.05 (3/4)
maximum number of indoor units			no.	50	53	56	59
sound pressure level (night mode)			dB(A)	65 (60)	65 (60)	66 (61)	66 (61)
dimensions (H x L x D)			mm	1720x3630x765	1720x3630x765	1720x3630x765	1720x3630x765
Weight			kg	260+260+260	260+260+260	260+260+260	260+260+260

The specified cooling and heating capacities refer to outdoor unit operating with indoor units at 100% capacity and are based on the EN14511 standard

Cooling: indoor ambient temp. 27°C (19°C WB) - outdoor ambient temp. 35°C; refrigerant piping length 7.5m; level difference 0m.

Heating: indoor ambient temp. 20°C - outdoor ambient temp. 7°C (6°C WB); refrigerant piping length 7.5m; level difference 0m.

The sound pressure level has been measured in the following conditions:

a. 1 metre from the unit's service hatch cover and 1.5 metres from floor level

b. The specified data are based on the cooling mode. In the case of the heating mode, the pressure level increases from 1 to 2dB.

c. The specified data have been obtained in an anechoic chamber

Only the combinations shown in the table are possible (12-36HP)

The width specified in outer dimensions takes into account the specific 20mm distance between outdoor units (12-36HP)

ESEER (1): Seasonal efficiency value in standard cooling

ESEER (2): Seasonal efficiency value in cooling with optimised system operation depending on seasonal demand



# VRF Set Free outdoor units

